


Datasheet

Item No. 70.357.2435.1

Hood BAS GOT GF 24 M25 50 A1

revos BASIC 500V size 24 hood with threaded collar M25, top cable entry, with double locking levers



Item No.	70.357.2435.1
EAN	4015573606227
order unit	1 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	24
Model	male
Locking mechanism	Double locking levers
Cable entry	Above
Type of cable	Thread
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No