

Datasheet

Item No. 72.710.1658.0

Male insert BAS STC 16 69

revos BASIC 690V 16 pole + ground, male insert 690V/16A, crimp connection



Item No.	72.710.1658.0
EAN	4015573228795
order unit	10 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Model	Pin insert
Size (in accordance with DIN 43880)	16
Inflammability class of insulation material acc. with UL94	V0
Colour	Grey
Mating cycles	200
Pollution degree	3
Modular version	No
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Connection Data

Connection type	Crimp
Number of poles	14
Plus switching contacts	2
Number of pole for rated current 2	0
Number of pole for rated current 3	0
Total number of poles (without ground contact)	16
With wire protection	No
Protective contact	Yes

Technical Data UL/CSA

Rated voltage according to UL/CSA	600
Rated current according CSA	16

Min. conductor cross section flexible wire	0.5
Max. conductor cross section flexible wire	4
Conductor cross section flexible AWG wire	20-12 AWG

Model

With housing	No
--------------	----

Contacts

Contact material	See contacts
Surface	See contacts
Contact resistance	1.5 mOhm
Wire strip length	7 mm

Screws head design/recomm. Torque

Mounting screws	H1/0.5-0.7 Nm
Ground conductor screws	H2/1.2-1.6 Nm

Technical Data DIN EN 61984

Nominal voltage	690
Rated voltage face/ground	690
Nominal current	16
Rated impulse voltage	8 kV

Drawings