

Datasheet

Item No. 76.331.4035.1

Bottom BAS GUT GM 40HM25 50 A1

revos BASIC 500V size 16H closed-bottom base with threaded collar M25, left, high design, single locking lever



Item No.	76.331.4035.1
EAN	4015573623972
order unit	1 Piece(s)

Approvals



Technical data

**General**

ArticlePrice	udp_no_price
Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

**Model**

DIN-size	16H
Model	Surface mounting (base)
Locking mechanism	Single locking lever
Cable entry	Sideways
Type of cable	Thread
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No