

## Datasheet

Item No. 76.333.4035.0

Bottom BAS GUT GO 40HM25 50 A0

revos BASIC 500V size 16H closed-bottom base with cable gland M25, bottom, high design, single locking lever



|            |               |
|------------|---------------|
| Item No.   | 76.333.4035.0 |
| EAN        | 4015573623989 |
| order unit | 1 Piece(s)    |

## Approvals



## Technical data

### General

|  |                     |
|--|---------------------|
| ArticlePrice   | udp_no_price        |
| Nominal voltage  | 500                 |
| Housing material   | Aluminium           |
| Colour   | Grey                |
| Surface  | With powder coating |
| Degree of protection (IP)                                  | IP54                |
| UV resistant   | Yes                 |
| Inflammability class of insulation material acc. with UL94 | Other               |
| Operating temperature range min.                           | -40 °C              |
| Operating temperature range max.                           | 120 °C              |

### Model

|                        |                         |
|------------------------|-------------------------|
| DIN-size               | 16H                     |
| Model                  | Surface mounting (base) |
| Locking mechanism      | Single locking lever    |
| Cable entry            | Below                   |
| Type of cable          | Gland nut               |
| With cable screw gland | Yes                     |
| Thread size M          | 25                      |
| Hinged lid             | No                      |
| EMC-version            | No                      |