

EQUES® 60Classic - Busbar adapters 25 A - 80 A

universal version



Busbar adapter, 25 A, with leads AWG 12 (4 mm²)

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
1 adjustable mounting rail	45	200	4	32.5	05	32430
2 adjustable mounting rails			4	32.6	05	32431
2 adjustable mounting rails	90		2	57.1	05	32432
2 adjustable mounting rails	45	260	4	35.7	05	32433

Busbar adapter, 25 A, without leads, with screw terminals 6 mm² from rear

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
2 adjustable mounting rails	45	200	4	32.2	05	32436
		260	4	35.2	05	32439

UL terminal cap

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
for busbar adapters 32436 and 32439	45	15	4	0.7	05	32973

Busbar adapter, 32 A, with leads AWG 10 (6 mm²)

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
1 adjustable mounting rail	45	200	4	33.3	05	32655
1 adjustable mounting rail	54		4	36.6	05	32441
2 adjustable mounting rails			4	38.0	05	32442
1 adjustable mounting rail	63		4	44.5	05	32443
1 adjustable mounting rail	72		4	44.3	05	32444
2 adjustable mounting rails	81		4	49.5	05	32446
2 adjustable mounting rails	54	260	4	43.3	05	32449

Busbar adapter, 63 A, with leads AWG 8 (10 mm²)

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
1 adjustable mounting rail	54	200	4	39.2	05	32454
2 adjustable mounting rails			4	41.0	05	32455
1 adjustable mounting rail	63		4	44.9	05	32456
1 adjustable mounting rail	72		4	47.6	05	32457
2 adjustable mounting rails	81		4	51.3	05	32459
2 adjustable mounting rails	54		260	4	43.0	05

Busbar adapter, 80 A, without leads, with screw terminals 16 mm² from rear

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
1 adjustable mounting rail	54	200	4	37.3	05	32466
2 adjustable mounting rails			4	38.9	05	32467
1 adjustable mounting rail	72		4	45.0	05	32469
2 adjustable mounting rails	54	260	4	43.8	05	32472

UL terminal cap

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
for busbar adapters 32466, 32467, 32469 and 32472	54	15	4	0.8	05	32974

all devices can be mounted directly on busbars 12, 15, 20, 25, 30 x 5, 10 and section busbars



EQUES® 60Classic - Busbar adapters 32 A - 80 A

universal version



Busbar adapter, 32 A, without leads, with spring terminal 1.5 - 6 mm² from front

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
1 adjustable mounting rail	45	200	4	32.5	05	32486
2 adjustable mounting rails		260	4	35.5	05	32487

Busbar adapter, 80 A, without leads, with screw terminals 1.5 - 16 mm² from front

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
1 adjustable mounting rail	54	200	4	37.3	05	32464
2 adjustable mounting rails		260	4	41.2	05	32465

Busbar component support, without electrical connection

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
2 adjustable mounting rails	45	200	4	24.8	05	32477
2 adjustable mounting rails			4	27.7	05	32478
for direct starter Siemens 3RA6	45		4	24.8	05	32589
2 adjustable mounting rails	54	260	4	27.9	05	32484
2 adjustable mounting rails			4	38.5	05	32485
1 adjustable mounting rail and 1 positioner for Siemens S00	45	200	4	24.8	05	32635
1 adjustable mounting rail and 1 positioner for Siemens S00 and S0		260	4	27.9	05	32636

Side-mounted module, for busbar adapter

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
attachable to both sides	9	200	10	2.3	05	32963

PE/N adapter module, with connection terminals 16 mm² top and bottom

Type	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
attachable to busbar adapter on both sides	18	242	4	14.1	05	32146

Accessories, for adapter

Type	Pack size	Weight kg/100 u.	PG	Part No.
mounting rail 45 mm	10	1.4	05	32947
mounting rail 54 mm	10	1.5	05	32948
mounting rail 63 mm	10	1.8	05	32949
mounting rail 72 mm	10	2.0	05	32950
mounting rail 81 mm	10	2.1	05	32951
mounting rail end stop	50	0.1	05	32969
connecting element, universal	50	0.1	05	32954
8-pole connector, with support, 250 V	10	3.4	05	32511
10-pole connector, with support, 250 V	10	4.0	05	32513
lead AWG 14 (2.5 mm ²), 105 mm long	* 24	0.3	05	32921
lead AWG 10 (6 mm ²), 130 mm long	* 24	0.7	05	32907
lead AWG 4 (25 mm ²), 210 mm long	* 24	5.1	05	32914
double-lead 2x AWG 10 (2x 6 mm ²), 130 / 280 mm long	* 24	2.5	05	32915

* ultrasonic-welded lead ends

all devices can be mounted directly on busbars 12, 15, 20, 25, 30 x 5, 10 and section busbars

