

60Classic - Busbar systems

1-, 2-, 3-, 4-pole systems, system height 200 mm



Universal busbar support, without end cover

Type	Busbar	Pack size	Weight kg/100 u.	PG	Part No.
2-pole with internal screw holes	12, 20, 30 x 5, 10	1	8.3	06	01602
3-pole with internal screw holes	12, 15, 20, 25, 30 x 5, 10	10	12.7	06	01495
3-pole with additional external screw holes		10	13.7	06	01500
4-pole with internal screw holes		10	26.6	06	01485

UL busbar support, without end cover

3-pole, with internal screw holes	12, 20, 30 x 5, 10	10	14.0	06	01508
4-pole, with internal screw holes		10	19.7	06	01357

UL spacer, for UL busbar supports

suitable for 01508	10	9.1	06	01358
suitable for 01357	10	13.1	06	01359

Base plate, for UL busbar supports 01508, 01231, 01232

240 x 1100	2	73.7	06	01518
240 x 700	2	46.9	06	01515

PE/N busbar support, incl. PE and N labels

Type	Busbar	Pack size	Weight kg/100 u.	PG	Part No.
2-pole, indiv. mountable	* 12, 15, 20, 25, 30 x 5, 10	10	9.5	06	01356
1-pole, indiv. mountable	12, 20, 30 x 5, 10	1	5.9	06	01601

* stepped busbars



BROOME10®60Classic power supply, with CrossLink®Technology

Type	Nominal output current	Width	Height	Pack size	Weight kg/100 u.	PG	Part No.
24 V DC, with push-in terminals	10 A	45	200	1	71.8	21	36202

parallel connection for increased current and series connection for increased voltage possible



60Classic - Busbar systems with section busbars

1-, 3-, 4-pole systems



Busbar support, for double-T section, without end cover

Type	Pack size	Weight kg/100 u.	PG	Part No.
1-pole, to be attached to 01231 and individually mountable	4	13.0	06	01116
3-pole, with internal screw holes	3	59.1	06	01231

Busbar support, for triple-T section, without end cover

1-pole, to be attached to 01232 and individually mountable	4	15.0	06	01132
3-pole, with internal screw holes	2	69.7	06	01232

Busbar support, for TCC section, without end cover

3-pole, with internal screw holes	2	69.7	06	01422
-----------------------------------	---	------	----	--------------

End cover, for busbar support for section busbars

for busbar supports 01116 and 01132	4	1.8	06	01373
for busbar supports 01231 and 01232	4	4.8	06	01234
for busbar support 01422	4	5.3	06	01425



Connection busbar support, without end cover

Type	Busbar	Pack size	Weight kg/100 u.	PG	Part No.
3-pole, with integrated terminals 1.5 - 16 mm ²	12, 15, 20, 25, 30 x 5, 10	10	25.6	06	01484

End cover, for universal busbar supports, to cover the busbar ends

Type	Pack size	Weight kg/100 u.	PG	Part No.
for busbar support 01356 and 01601	10	0.7	06	01325
for busbar support 01602	1	1.5	06	01363
for busbar supports 01484, 01495, 01500, 01508 and 01603	10	2.0	06	01573
for busbar supports 01357 and 01485 (1x 01131 = 1 left + 1 right cover)	5	5.6	06	01131

