

CAPUS®Panel - Switch-disconnectors 3-pole + N, 16 A - 160 A

type SD1, SD2, SD3; clip-on mounting on rail TH 35 mm to EN 60715



Switch-disconnector, 3-pole + N, with rotary handle graphite-grey

Article	Type	Rated current	Dimensions	Pack size	Weight kg/100 u.	PG	Part No.
box terminal 2.5 - 16 mm ² , graphite grey handle	SD1-4-16	16 A	51 x 81 x 79	1	20.5	14	33809
box terminal 2.5 - 16 mm ² , graphite grey handle	SD1-4-25	25 A		1	20.5	14	33813
box terminal 2.5 - 16 mm ² , graphite grey handle	SD1-4-32	32 A		1	20.5	14	33817
box terminal 2.5 - 16 mm ² , graphite grey handle	SD1-4-40	40 A		1	20.5	14	33821
box terminal 2.5 - 16 mm ² , graphite grey handle	SD1-4-63	63 A		1	20.5	14	33825
box terminal 16 - 50 mm ² , graphite grey handle	SD2-4-63	63 A	69 x 100 x 80	1	40.5	14	33869
box terminal 16 - 50 mm ² , graphite grey handle	SD2-4-80	80 A		1	40.5	14	33873
box terminal 16 - 50 mm ² , graphite grey handle	SD2-4-100	100 A		1	40.5	14	33877
box terminal 50 - 70 mm ² , graphite grey handle	SD3-4-125	125 A	88 x 113 x 81	1	53.5	14	33028
box terminal 50 - 70 mm ² , graphite grey handle	SD3-4-160	160 A		1	53.5	14	33032



Switch-disconnector, 3-pole + N, with rotary handle red-yellow

box terminal 2.5 - 16 mm ² , yellow-red handle	SD1-4-16	16 A	51 x 81 x 79	1	20.5	14	33839
box terminal 2.5 - 16 mm ² , yellow-red handle	SD1-4-25	25 A		1	20.5	14	33843
box terminal 2.5 - 16 mm ² , yellow-red handle	SD1-4-32	32 A		1	20.5	14	33847
box terminal 2.5 - 16 mm ² , yellow-red handle	SD1-4-40	40 A		1	20.5	14	33851
box terminal 2.5 - 16 mm ² , yellow-red handle	SD1-4-63	63 A		1	20.5	14	33855
box terminal 16 - 50 mm ² , yellow-red handle	SD2-4-63	63 A	69 x 100 x 80	1	40.5	14	33885
box terminal 16 - 50 mm ² , yellow-red handle	SD2-4-80	80 A		1	40.5	14	33889
box terminal 16 - 50 mm ² , yellow-red handle	SD2-4-100	100 A		1	40.5	14	33893
box terminal 50 - 70 mm ² , yellow-red handle	SD3-4-125	125 A	88 x 113 x 81	1	53.5	14	33037
box terminal 50 - 70 mm ² , yellow-red handle	SD3-4-160	160 A		1	53.5	14	33041



CAPUS®Panel - Handles and accessories

for switch-disconnector type SD1, SD2, SD3



Rotary handle, for door coupling drive, without shaft

Type	Usable for version	Pack size	Weight kg/100 u.	PG	Part No.
black, with door inter-locking	SD1-3, SD1-4, SD2-3, SD2-4, SD3-3, SD3-4	1	5.5	14	33665
red-yellow, with door inter-locking	SD1-3, SD1-4, SD2-3, SD2-4, SD3-3, SD3-4	1	5.5	14	33666
black, with defeatable door inter-locking	SD1-3, SD1-4, SD2-3, SD2-4, SD3-3, SD3-4	1	10.5	14	33669
red-yellow, with defeatable door inter-locking	SD1-3, SD1-4, SD2-3, SD2-4, SD3-3, SD3-4	1	10.5	14	33670



Extension shaft

extension shaft, length 100 mm	SD1-3, SD1-4, SD2-3, SD2-4, SD3-3, SD3-4	1	2.0	14	33680
extension shaft, length 200 mm	SD1-3, SD1-4, SD2-3, SD2-4, SD3-3, SD3-4	1	3.6	14	33681
extension shaft, length 300 mm	SD1-3, SD1-4, SD2-3, SD2-4, SD3-3, SD3-4	1	5.4	14	33682



Pilot switch, for monitoring the switch position

1 n/c + 1 n/o, screw terminal		1	4.3	14	33692
-------------------------------	--	---	-----	----	--------------



Terminal space cover

set connection space cover 3-pole	SD1-3, SD1-4	1	1.8	14	33694
set connection space cover 3-pole	SD2-3, SD2-4	1	2.2	14	33695
set connection space cover 3-pole	SD3-3, SD3-4	1	3.4	14	33696
set connection space cover for 4th pole	SD1-4	1	1.2	14	33697
set connection space cover for 4th pole	SD2-4	1	1.4	14	33698
set connection space cover for 4th pole	SD3-4	1	1.6	14	33699

