

**ebm-papst St. Georgen GmbH & Co. KG**

Hermann-Papst-Straße 1

74673 St. Georgen

Phone: +49 7724 81-0

Fax: +49 7724 81-1309

www.ebmpapst.cominfo2@de.ebmpapst.com**Nominal data**


Type	5606 S	
Nominal voltage	[VAC]	115
Frequency	[Hz]	60
Speed	[min ⁻¹]	3100
Power input	[W]	26.0
Min. ambient temperature	[°C]	-35
Max. ambient temperature	[°C]	80
Air flow	[m ³ /h]	270
Sound power level	[B]	6.2
Sound pressure level	[dB(A)]	50

ml = max. load · me = max. efficiency · rfa = running at free air · cs = customer specs · cu = customer unit
Subject to alterations

Technical features

Dimensions	135 x 135 x 38 mm
General description	AC fan with external rotor shaded-pole motor.
Connection line	2 flat plugs 2.8 x 0.5 mm. Housing with grounding lug and tapping screw M4 x 8 (TORX).
Direction of protection	Left, looking at rotor
Direction of air flow	Air exhaust over bars
Bearing	Ball bearings
Lifetime L10 at 40 °C	47500 h
Lifetime L10 at maximum temperature	20000 h
Mass	0.800 kg
Material of impeller	Metal
Motor protection	Protected from overload by a thermal cutout switch
Approval	VDE, CSA, UL, CE

Product drawing



Charts: Air flow

