



METAL HALIDE/METAL HALIDE PULSE, 50-175W MEDIUM BASE HID

Class I, Div. 2, Groups A,B,C,D
 Class I, Zone 2, Groups IIC, IIB, IIA
 Class II, Div. 1 & 2, Groups E,F,G
 Class III
 Suitable for wet locations
 NEMA 3, 4, 4X
 IP66

UL LISTED - File E10514 (Hazardous & Marine)

SP Certified - File LR11713

NR Restricted Breathing Option

Class I, Zone 2 AEx nAnR
 Class I, Zone 2 Ex nR



VM1 Pendant
w/5-1/2"
Globe & Guard



VM2 Pendant
w/7-3/4"
Globe & Guard



VM1 Flexible Pendant
w/5-1/2"
Refractor & Guard



VM2 Flexible Pendant
w/7-3/4"
Refractor & Guard

VM 50 - 175 METAL HALIDE (PULSE **) - PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE			7-3/4" OPTIC THREAD SIZE			
WATTS	ANSI	HUB SIZE	VOLTAGE	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	3/4"	Quad Tri	VM1H050A2GLG	VM1H050A2R1G	VM1H050A2R5G	VM2H050A2GLG	VM2H050A2R1G	VM2H050A2R5G	VM2H050A2S5G
				VM1H056A2GLG	VM1H056A2R1G	VM1H056A2R5G	VM2H056A2GLG	VM2H056A2R1G	VM2H056A2R5G	VM2H056A2S5G
70	M98	3/4"	Quad Tri 480	VM1H070A2GLG	VM1H070A2R1G	VM1H070A2R5G	VM2H070A2GLG	VM2H070A2R1G	VM2H070A2R5G	VM2H070A2S5G
				VM1H076A2GLG	VM1H076A2R1G	VM1H076A2R5G	VM2H076A2GLG	VM2H076A2R1G	VM2H076A2R5G	VM2H076A2S5G
				VM1H075A2GLG	VM1H075A2R1G	VM1H075A2R5G	VM2H075A2GLG	VM2H075A2R1G	VM2H075A2R5G	VM2H075A2S5G
100	M90	3/4"	Quad Tri 480	VM1H100A2GLG	VM1H100A2R1G	VM1H100A2R5G	VM2H100A2GLG	VM2H100A2R1G	VM2H100A2R5G	VM2H100A2S5G
				VM1H106A2GLG	VM1H106A2R1G	VM1H106A2R5G	VM2H106A2GLG	VM2H106A2R1G	VM2H106A2R5G	VM2H106A2S5G
				VM1H105A2GLG	VM1H105A2R1G	VM1H105A2R5G	VM2H105A2GLG	VM2H105A2R1G	VM2H105A2R5G	VM2H105A2S5G
150	M102 M142	3/4"	Quad Tri 480	VM1P150A2GLG	VM1P150A2R1G	VM1P150A2R5G	VM2P150A2GLG	VM2P150A2R1G	VM2P150A2R5G	VM2P150A2S5G
				VM1P156A2GLG	VM1P156A2R1G	VM1P156A2R5G	VM2P156A2GLG	VM2P156A2R1G	VM2P156A2R5G	VM2P156A2S5G
				VM1P155A2GLG	VM1P155A2R1G	VM1P155A2R5G	VM2P155A2GLG	VM2P155A2R1G	VM2P155A2R5G	VM2P155A2S5G
175	M137 M152	3/4"	Quad Tri 480	VM1P170A2GLG	VM1P170A2R1G	VM1P170A2R5G	VM2P170A2GLG	VM2P170A2R1G	VM2P170A2R5G	VM2P170A2S5G
				VM1P176A2GLG	VM1P176A2R1G	VM1P176A2R5G	VM2P176A2GLG	VM2P176A2R1G	VM2P176A2R5G	VM2P176A2S5G
				VM1P175A2GLG	VM1P175A2R1G	VM1P175A2R5G	VM2P175A2GLG	VM2P175A2R1G	VM2P175A2R5G	VM2P175A2S5G

VM 50 - 175 METAL HALIDE (PULSE **) - FLEX PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE			7-3/4" OPTIC THREAD SIZE			
WATTS	ANSI	HUB SIZE	VOLTAGE	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	3/4"	Quad Tri	VM1H050F2GLG	VM1H050F2R1G	VM1H050F2R5G	VM2H050F2GLG	VM2H050F2R1G	VM2H050F2R5G	VM2H050F2S5G
				VM1H056F2GLG	VM1H056F2R1G	VM1H056F2R5G	VM2H056F2GLG	VM2H056F2R1G	VM2H056F2R5G	VM2H056F2S5G
70	M98	3/4"	Quad Tri 480	VM1H070F2GLG	VM1H070F2R1G	VM1H070F2R5G	VM2H070F2GLG	VM2H070F2R1G	VM2H070F2R5G	VM2H070F2S5G
				VM1H076F2GLG	VM1H076F2R1G	VM1H076F2R5G	VM2H076F2GLG	VM2H076F2R1G	VM2H076F2R5G	VM2H076F2S5G
				VM1H075F2GLG	VM1H075F2R1G	VM1H075F2R5G	VM2H075F2GLG	VM2H075F2R1G	VM2H075F2R5G	VM2H075F2S5G
100	M90	3/4"	Quad Tri 480	VM1H100F2GLG	VM1H100F2R1G	VM1H100F2R5G	VM2H100F2GLG	VM2H100F2R1G	VM2H100F2R5G	VM2H100F2S5G
				VM1H106F2GLG	VM1H106F2R1G	VM1H106F2R5G	VM2H106F2GLG	VM2H106F2R1G	VM2H106F2R5G	VM2H106F2S5G
				VM1H105F2GLG	VM1H105F2R1G	VM1H105F2R5G	VM2H105F2GLG	VM2H105F2R1G	VM2H105F2R5G	VM2H105F2S5G
150	M102 M142	3/4"	Quad Tri 480	VM1P150F2GLG	VM1P150F2R1G	VM1P150F2R5G	VM2P150F2GLG	VM2P150F2R1G	VM2P150F2R5G	VM2P150F2S5G
				VM1P156F2GLG	VM1P156F2R1G	VM1P156F2R5G	VM2P156F2GLG	VM2P156F2R1G	VM2P156F2R5G	VM2P156F2S5G
				VM1P155F2GLG	VM1P155F2R1G	VM1P155F2R5G	VM2P155F2GLG	VM2P155F2R1G	VM2P155F2R5G	VM2P155F2S5G
175	M137 M152	3/4"	Quad Tri 480	VM1P170F2GLG	VM1P170F2R1G	VM1P170F2R5G	VM2P170F2GLG	VM2P170F2R1G	VM2P170F2R5G	VM2P170F2S5G
				VM1P176F2GLG	VM1P176F2R1G	VM1P176F2R5G	VM2P176F2GLG	VM2P176F2R1G	VM2P176F2R5G	VM2P176F2S5G
				VM1P175F2GLG	VM1P175F2R1G	VM1P175F2R5G	VM2P175F2GLG	VM2P175F2R1G	VM2P175F2R5G	VM2P175F2S5G

See hazardous location data pages L131 - L140 for application suitability.

Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1H050A2GLN.

Catalog numbers shown are with 3/4" conduit openings; change "2" to "3" for 1" e.g. VM1H050A3GLG.

Consult catalog logic for other available voltage & lamp combinations.

Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (UL only)

** 50, 70, & 100 Watt "Traditional Metal Halide" ballasts include a Pulse Ignitor, as do 150 & 175W Metal Halide Pulse models.

LIGHTING

CERTILITE® V SERIES



METAL HALIDE/METAL HALIDE PULSE, 50-175W MEDIUM BASE HID



VM1 Ceiling
w/5-1/2"
Globe & Guard



VM2 Ceiling
w/7-3/4"
Globe & Guard



VM1 Wall
w/5-1/2"
Refractor & Guard



VM2 Wall
w/7-3/4"
Refractor & Guard

VM 50 - 175 METAL HALIDE (PULSE **) - CEILING										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	3/4"	Quad Tri	VM1H050X2GLG	VM1H050X2R1G	VM1H050X2R5G	VM2H050X2GLG	VM2H050X2R1G	VM2H050X2R5G	VM2H050X2S5G
				VM1H056X2GLG	VM1H056X2R1G	VM1H056X2R5G	VM2H056X2GLG	VM2H056X2R1G	VM2H056X2R5G	VM2H056X2S5G
70	M98	3/4"	Quad Tri 480	VM1H070X2GLG	VM1H070X2R1G	VM1H070X2R5G	VM2H070X2GLG	VM2H070X2R1G	VM2H070X2R5G	VM2H070X2S5G
				VM1H076X2GLG	VM1H076X2R1G	VM1H076X2R5G	VM2H076X2GLG	VM2H076X2R1G	VM2H076X2R5G	VM2H076X2S5G
				VM1H075X2GLG	VM1H075X2R1G	VM1H075X2R5G	VM2H075X2GLG	VM2H075X2R1G	VM2H075X2R5G	VM2H075X2S5G
100	M90	3/4"	Quad Tri 480	VM1H100X2GLG	VM1H100X2R1G	VM1H100X2R5G	VM2H100X2GLG	VM2H100X2R1G	VM2H100X2R5G	VM2H100X2S5G
				VM1H106X2GLG	VM1H106X2R1G	VM1H106X2R5G	VM2H106X2GLG	VM2H106X2R1G	VM2H106X2R5G	VM2H106X2S5G
				VM1H105X2GLG	VM1H105X2R1G	VM1H105X2R5G	VM2H105X2GLG	VM2H105X2R1G	VM2H105X2R5G	VM2H105X2S5G
150	M102 M142	3/4"	Quad Tri 480	VM1P150X2GLG	VM1P150X2R1G	VM1P150X2R5G	VM2P150X2GLG	VM2P150X2R1G	VM2P150X2R5G	VM2P150X2S5G
				VM1P156X2GLG	VM1P156X2R1G	VM1P156X2R5G	VM2P156X2GLG	VM2P156X2R1G	VM2P156X2R5G	VM2P156X2S5G
				VM1P155X2GLG	VM1P155X2R1G	VM1P155X2R5G	VM2P155X2GLG	VM2P155X2R1G	VM2P155X2R5G	VM2P155X2S5G
175	M137 M152	3/4"	Quad Tri 480	VM1P170X2GLG	VM1P170X2R1G	VM1P170X2R5G	VM2P170X2GLG	VM2P170X2R1G	VM2P170X2R5G	VM2P170X2S5G
				VM1P176X2GLG	VM1P176X2R1G	VM1P176X2R5G	VM2P176X2GLG	VM2P176X2R1G	VM2P176X2R5G	VM2P176X2S5G
				VM1P175X2GLG	VM1P175X2R1G	VM1P175X2R5G	VM2P175X2GLG	VM2P175X2R1G	VM2P175X2R5G	VM2P175X2S5G

VM 50 - 175 METAL HALIDE (PULSE **) - WALL										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	3/4"	Quad Tri	VM1H050B2GLG	VM1H050B2R1G	VM1H050B2R5G	VM2H050B2GLG	VM2H050B2R1G	VM2H050B2R5G	VM2H050B2S5G
				VM1H056B2GLG	VM1H056B2R1G	VM1H056B2R5G	VM2H056B2GLG	VM2H056B2R1G	VM2H056B2R5G	VM2H056B2S5G
70	M98	3/4"	Quad Tri 480	VM1H070B2GLG	VM1H070B2R1G	VM1H070B2R5G	VM2H070B2GLG	VM2H070B2R1G	VM2H070B2R5G	VM2H070B2S5G
				VM1H076B2GLG	VM1H076B2R1G	VM1H076B2R5G	VM2H076B2GLG	VM2H076B2R1G	VM2H076B2R5G	VM2H076B2S5G
				VM1H075B2GLG	VM1H075B2R1G	VM1H075B2R5G	VM2H075B2GLG	VM2H075B2R1G	VM2H075B2R5G	VM2H075B2S5G
100	M90	3/4"	Quad Tri 480	VM1H100B2GLG	VM1H100B2R1G	VM1H100B2R5G	VM2H100B2GLG	VM2H100B2R1G	VM2H100B2R5G	VM2H100B2S5G
				VM1H106B2GLG	VM1H106B2R1G	VM1H106B2R5G	VM2H106B2GLG	VM2H106B2R1G	VM2H106B2R5G	VM2H106B2S5G
				VM1H105B2GLG	VM1H105B2R1G	VM1H105B2R5G	VM2H105B2GLG	VM2H105B2R1G	VM2H105B2R5G	VM2H105B2S5G
150	M102 M142	3/4"	Quad Tri 480	VM1P150B2GLG	VM1P150B2R1G	VM1P150B2R5G	VM2P150B2GLG	VM2P150B2R1G	VM2P150B2R5G	VM2P150B2S5G
				VM1P156B2GLG	VM1P156B2R1G	VM1P156B2R5G	VM2P156B2GLG	VM2P156B2R1G	VM2P156B2R5G	VM2P156B2S5G
				VM1P155B2GLG	VM1P155B2R1G	VM1P155B2R5G	VM2P155B2GLG	VM2P155B2R1G	VM2P155B2R5G	VM2P155B2S5G
175	M137 M152	3/4"	Quad Tri 480	VM1P170B2GLG	VM1P170B2R1G	VM1P170B2R5G	VM2P170B2GLG	VM2P170B2R1G	VM2P170B2R5G	VM2P170B2S5G
				VM1P176B2GLG	VM1P176B2R1G	VM1P176B2R5G	VM2P176B2GLG	VM2P176B2R1G	VM2P176B2R5G	VM2P176B2S5G
				VM1P175B2GLG	VM1P175B2R1G	VM1P175B2R5G	VM2P175B2GLG	VM2P175B2R1G	VM2P175B2R5G	VM2P175B2S5G

① See hazardous location data pages L131 - L140 for application suitability.

② Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1H050X2GLN.

③ Catalog numbers shown are with 3/4" conduit openings; change "2" to "3" for 1" e.g. VM1H050X3GLG.

④ Consult catalog logic for other available voltage & lamp combinations.

⑤ Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (☞ only)

** 50, 70, & 100 Watt "Traditional Metal Halide" ballasts include a Pulse Ignitor, as do 150 & 175W Metal Halide Pulse models.



METAL HALIDE/METAL HALIDE PULSE, 50-175W MEDIUM BASE HID



VM1 Cone
w/5-1/2"
Globe & Guard



VM2 Cone
w/7-3/4"
Globe & Guard



VM1 EZ Adapter
w/5-1/2"
Refractor & Guard



VM2 EZ Adapter
w/7-3/4"
Refractor & Guard

VM 50 - 175 METAL HALIDE (PULSE**) - CONE

DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	3/4"	Quad Tri	VM1H050C2GLG	VM1H050C2R1G	VM1H050C2R5G	VM2H050C2GLG	VM2H050C2R1G	VM2H050C2R5G	VM2H050C2S5G
				VM1H056C2GLG	VM1H056C2R1G	VM1H056C2R5G	VM2H056C2GLG	VM2H056C2R1G	VM2H056C2R5G	VM2H056C2S5G
70	M98	3/4"	Quad Tri 480	VM1H070C2GLG	VM1H070C2R1G	VM1H070C2R5G	VM2H070C2GLG	VM2H070C2R1G	VM2H070C2R5G	VM2H070C2S5G
				VM1H076C2GLG	VM1H076C2R1G	VM1H076C2R5G	VM2H076C2GLG	VM2H076C2R1G	VM2H076C2R5G	VM2H076C2S5G
				VM1H075C2GLG	VM1H075C2R1G	VM1H075C2R5G	VM2H075C2GLG	VM2H075C2R1G	VM2H075C2R5G	VM2H075C2S5G
100	M90	3/4"	Quad Tri 480	VM1H100C2GLG	VM1H100C2R1G	VM1H100C2R5G	VM2H100C2GLG	VM2H100C2R1G	VM2H100C2R5G	VM2H100C2S5G
				VM1H106C2GLG	VM1H106C2R1G	VM1H106C2R5G	VM2H106C2GLG	VM2H106C2R1G	VM2H106C2R5G	VM2H106C2S5G
				VM1H105C2GLG	VM1H105C2R1G	VM1H105C2R5G	VM2H105C2GLG	VM2H105C2R1G	VM2H105C2R5G	VM2H105C2S5G
150	"M102 M142"	3/4"	Quad Tri 480	VM1P150C2GLG	VM1P150C2R1G	VM1P150C2R5G	VM2P150C2GLG	VM2P150C2R1G	VM2P150C2R5G	VM2P150C2S5G
				VM1P156C2GLG	VM1P156C2R1G	VM1P156C2R5G	VM2P156C2GLG	VM2P156C2R1G	VM2P156C2R5G	VM2P156C2S5G
				VM1P155C2GLG	VM1P155C2R1G	VM1P155C2R5G	VM2P155C2GLG	VM2P155C2R1G	VM2P155C2R5G	VM2P155C2S5G
175	"M137 M152"	3/4"	Quad Tri 480	VM1P170C2GLG	VM1P170C2R1G	VM1P170C2R5G	VM2P170C2GLG	VM2P170C2R1G	VM2P170C2R5G	VM2P170C2S5G
				VM1P176C2GLG	VM1P176C2R1G	VM1P176C2R5G	VM2P176C2GLG	VM2P176C2R1G	VM2P176C2R5G	VM2P176C2S5G
				VM1P175C2GLG	VM1P175C2R1G	VM1P175C2R5G	VM2P175C2GLG	VM2P175C2R1G	VM2P175C2R5G	VM2P175C2S5G

VM 50 - 175 METAL HALIDE (PULSE**) - EZ ADAPTER ⑥

DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	⑥	Quad Tri	VM1H050EZGLG	VM1H050EZR1G	VM1H050EZR5G	VM2H050EZGLG	VM2H050EZR1G	VM2H050EZR5G	VM2H050EZS5G
				VM1H056EZGLG	VM1H056EZR1G	VM1H056EZR5G	VM2H056EZGLG	VM2H056EZR1G	VM2H056EZR5G	VM2H056EZS5G
70	M98	⑥	Quad Tri 480	VM1H070EZGLG	VM1H070EZR1G	VM1H070EZR5G	VM2H070EZGLG	VM2H070EZR1G	VM2H070EZR5G	VM2H070EZS5G
				VM1H076EZGLG	VM1H076EZR1G	VM1H076EZR5G	VM2H076EZGLG	VM2H076EZR1G	VM2H076EZR5G	VM2H076EZS5G
				VM1H075EZGLG	VM1H075EZR1G	VM1H075EZR5G	VM2H075EZGLG	VM2H075EZR1G	VM2H075EZR5G	VM2H075EZS5G
100	M90	⑥	Quad Tri 480	VM1H100EZGLG	VM1H100EZR1G	VM1H100EZR5G	VM2H100EZGLG	VM2H100EZR1G	VM2H100EZR5G	VM2H100EZS5G
				VM1H106EZGLG	VM1H106EZR1G	VM1H106EZR5G	VM2H106EZGLG	VM2H106EZR1G	VM2H106EZR5G	VM2H106EZS5G
				VM1H105EZGLG	VM1H105EZR1G	VM1H105EZR5G	VM2H105EZGLG	VM2H105EZR1G	VM2H105EZR5G	VM2H105EZS5G
150	M102 M142	⑥	Quad Tri 480	VM1P150EZGLG	VM1P150EZR1G	VM1P150EZR5G	VM2P150EZGLG	VM2P150EZR1G	VM2P150EZR5G	VM2P150EZS5G
				VM1P156EZGLG	VM1P156EZR1G	VM1P156EZR5G	VM2P156EZGLG	VM2P156EZR1G	VM2P156EZR5G	VM2P156EZS5G
				VM1P155EZGLG	VM1P155EZR1G	VM1P155EZR5G	VM2P155EZGLG	VM2P155EZR1G	VM2P155EZR5G	VM2P155EZS5G
175	M137 M152	⑥	Quad Tri 480	VM1P170EZGLG	VM1P170EZR1G	VM1P170EZR5G	VM2P170EZGLG	VM2P170EZR1G	VM2P170EZR5G	VM2P170EZS5G
				VM1P176EZGLG	VM1P176EZR1G	VM1P176EZR5G	VM2P176EZGLG	VM2P176EZR1G	VM2P176EZR5G	VM2P176EZS5G
				VM1P175EZGLG	VM1P175EZR1G	VM1P175EZR5G	VM2P175EZGLG	VM2P175EZR1G	VM2P175EZR5G	VM2P175EZS5G

① See hazardous location data pages L131 - L140 for application suitability.

② Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1H050A2GLN.

③ Catalog numbers shown are with 3/4" conduit openings; change "2" to "3" for 1" e.g. VM1H050A3GLG.

④ Consult catalog logic for other available voltage & lamp combinations.

⑤ Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (☉ is only)

** 50, 70, & 100 Watt "Traditional Metal Halide" ballasts include a Pulse Ignitor, as do 150 & 175W Metal Halide Pulse models.



LIGHTING

METAL HALIDE/METAL HALIDE PULSE, 50-175W MEDIUM BASE HID



VM1 Stanchion 25°
w/5-1/2"
Globe & Guard



VM2 Stanchion 25°
w/7-3/4"
Globe & Guard



VM1 Stanchion Straight
w/5-1/2"
Refractor & Guard



VM2 Stanchion Straight
w/7-3/4"
Refractor & Guard

VM 50 - 175 METAL HALIDE (PULSE**) - STANCHION 25° ANGLE										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	1-1/2"	Quad Tri	VM1H050D5GLG	VM1H050D5R1G	VM1H050D5R5G	VM2H050D5GLG	VM2H050D5R1G	VM2H050D5R5G	VM2H050D5S5G
				VM1H056D5GLG	VM1H056D5R1G	VM1H056D5R5G	VM2H056D5GLG	VM2H056D5R1G	VM2H056D5R5G	VM2H056D5S5G
70	M98	1-1/2"	Quad Tri 480	VM1H070D5GLG	VM1H070D5R1G	VM1H070D5R5G	VM2H070D5GLG	VM2H070D5R1G	VM2H070D5R5G	VM2H070D5S5G
				VM1H076D5GLG	VM1H076D5R1G	VM1H076D5R5G	VM2H076D5GLG	VM2H076D5R1G	VM2H076D5R5G	VM2H076D5S5G
				VM1H075D5GLG	VM1H075D5R1G	VM1H075D5R5G	VM2H075D5GLG	VM2H075D5R1G	VM2H075D5R5G	VM2H075D5S5G
100	M90	1-1/2"	Quad Tri 480	VM1H100D5GLG	VM1H100D5R1G	VM1H100D5R5G	VM2H100D5GLG	VM2H100D5R1G	VM2H100D5R5G	VM2H100D5S5G
				VM1H106D5GLG	VM1H106D5R1G	VM1H106D5R5G	VM2H106D5GLG	VM2H106D5R1G	VM2H106D5R5G	VM2H106D5S5G
				VM1H105D5GLG	VM1H105D5R1G	VM1H105D5R5G	VM2H105D5GLG	VM2H105D5R1G	VM2H105D5R5G	VM2H105D5S5G
150	M102 M142	1-1/2"	Quad Tri 480	VM1P150D5GLG	VM1P150D5R1G	VM1P150D5R5G	VM2P150D5GLG	VM2P150D5R1G	VM2P150D5R5G	VM2P150D5S5G
				VM1P156D5GLG	VM1P156D5R1G	VM1P156D5R5G	VM2P156D5GLG	VM2P156D5R1G	VM2P156D5R5G	VM2P156D5S5G
				VM1P155D5GLG	VM1P155D5R1G	VM1P155D5R5G	VM2P155D5GLG	VM2P155D5R1G	VM2P155D5R5G	VM2P155D5S5G
175	M137 M152	1-1/2"	Quad Tri 480	VM1P170D5GLG	VM1P170D5R1G	VM1P170D5R5G	VM2P170D5GLG	VM2P170D5R1G	VM2P170D5R5G	VM2P170D5S5G
				VM1P176D5GLG	VM1P176D5R1G	VM1P176D5R5G	VM2P176D5GLG	VM2P176D5R1G	VM2P176D5R5G	VM2P176D5S5G
				VM1P175D5GLG	VM1P175D5R1G	VM1P175D5R5G	VM2P175D5GLG	VM2P175D5R1G	VM2P175D5R5G	VM2P175D5S5G

VM 50 - 175 METAL HALIDE (PULSE**) - STANCHION STRAIGHT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
50	M110	1-1/2"	Quad Tri	VM1H050S5GLG	VM1H050S5R1G	VM1H050S5R5G	VM2H050S5GLG	VM2H050S5R1G	VM2H050S5R5G	VM2H050S5S5G
				VM1H056S5GLG	VM1H056S5R1G	VM1H056S5R5G	VM2H056S5GLG	VM2H056S5R1G	VM2H056S5R5G	VM2H056S5S5G
70	M98	1-1/2"	Quad Tri 480	VM1H070S5GLG	VM1H070S5R1G	VM1H070S5R5G	VM2H070S5GLG	VM2H070S5R1G	VM2H070S5R5G	VM2H070S5S5G
				VM1H076S5GLG	VM1H076S5R1G	VM1H076S5R5G	VM2H076S5GLG	VM2H076S5R1G	VM2H076S5R5G	VM2H076S5S5G
				VM1H075S5GLG	VM1H075S5R1G	VM1H075S5R5G	VM2H075S5GLG	VM2H075S5R1G	VM2H075S5R5G	VM2H075S5S5G
100	M90	1-1/2"	Quad Tri 480	VM1H100S5GLG	VM1H100S5R1G	VM1H100S5R5G	VM2H100S5GLG	VM2H100S5R1G	VM2H100S5R5G	VM2H100S5S5G
				VM1H106S5GLG	VM1H106S5R1G	VM1H106S5R5G	VM2H106S5GLG	VM2H106S5R1G	VM2H106S5R5G	VM2H106S5S5G
				VM1H105S5GLG	VM1H105S5R1G	VM1H105S5R5G	VM2H105S5GLG	VM2H105S5R1G	VM2H105S5R5G	VM2H105S5S5G
150	"M102 M142"	1-1/2"	Quad Tri 480	VM1P150S5GLG	VM1P150S5R1G	VM1P150S5R5G	VM2P150S5GLG	VM2P150S5R1G	VM2P150S5R5G	VM2P150S5S5G
				VM1P156S5GLG	VM1P156S5R1G	VM1P156S5R5G	VM2P156S5GLG	VM2P156S5R1G	VM2P156S5R5G	VM2P156S5S5G
				VM1P155S5GLG	VM1P155S5R1G	VM1P155S5R5G	VM2P155S5GLG	VM2P155S5R1G	VM2P155S5R5G	VM2P155S5S5G
175	"M137 M152"	1-1/2"	Quad Tri 480	VM1P170S5GLG	VM1P170S5R1G	VM1P170S5R5G	VM2P170S5GLG	VM2P170S5R1G	VM2P170S5R5G	VM2P170S5S5G
				VM1P176S5GLG	VM1P176S5R1G	VM1P176S5R5G	VM2P176S5GLG	VM2P176S5R1G	VM2P176S5R5G	VM2P176S5S5G
				VM1P175S5GLG	VM1P175S5R1G	VM1P175S5R5G	VM2P175S5GLG	VM2P175S5R1G	VM2P175S5R5G	VM2P175S5S5G

① See hazardous location data pages L131 - L140 for application suitability.
 ② Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1H050D4GLN.
 ③ Catalog numbers shown are with 1-1/2" conduit openings; change "5" to "4" for 1-1/4" e.g. VM1H050D4GLG.
 ④ Consult catalog logic for other available voltage & lamp combinations.
 ⑤ Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (Ⓢ only)
 ** 50, 70, & 100 Watt "Traditional Metal Halide" ballasts include a Pulse Ignitor, as do 150 & 175W Metal Halide Pulse models.