



LIGHTING

CERTILITE® V SERIES

METAL HALIDE, 70-250W MOGUL BASE HID



Pendant
w/ 5-1/2"
Globe & Guard



Flexible Pendant
w/ 5-1/2"
Refractor & Guard



Pendant
w/ 7-3/4"
Globe & Guard



Flexible Pendant
w/ 7-3/4"
Refractor & Guard



Pendant
w/ Enclosed Reflector

Class I, Div. 2, Groups A,B,C,D①
Class I, Zone 2, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III

Suitable for wet locations
NEMA 3, 4, 4X

IP66

UL US LISTED - File E10514 (Hazardous & Marine)

CSB US Certified - File LR11713

NR Restricted Breathing Option®

Class I, Zone 2 AEx nAnR

Class I, Zone 2 Ex nR



VM 70 - 250 WATT METAL HALIDE PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98 M143	3/4"	Quad Tri 480	VM3H070A2GLG	VM3H070A2R1G	VM3H070A2R5G	VM4H070A2GLG	VM4H070A2R1G	VM4H070A2R5G	VM4H070A2ERN
				VM3H076A2GLG	VM3H076A2R1G	VM3H076A2R5G	VM4H076A2GLG	VM4H076A2R1G	VM4H076A2R5G	VM4H076A2ERN
				VM3H075A2GLG	VM3H075A2R1G	VM3H075A2R5G	VM4H075A2GLG	VM4H075A2R1G	VM4H075A2R5G	VM4H075A2ERN
100	M90 M140	3/4"	Quad Tri 480	VM3H100A2GLG	VM3H100A2R1G	VM3H100A2R5G	VM4H100A2GLG	VM4H100A2R1G	VM4H100A2R5G	VM4H100A2ERN
				VM3H106A2GLG	VM3H106A2R1G	VM3H106A2R5G	VM4H106A2GLG	VM4H106A2R1G	VM4H106A2R5G	VM4H106A2ERN
				VM3H105A2GLG	VM3H105A2R1G	VM3H105A2R5G	VM4H105A2GLG	VM4H105A2R1G	VM4H105A2R5G	VM4H105A2ERN
175 ⑤	M57	3/4"	Quad Tri 480	VM3H170A2GLG	VM3H170A2R1G	VM3H170A2R5G	VM4H170A2GLG	VM4H170A2R1G	VM4H170A2R5G	VM4H170A2ERN
				VM3H176A2GLG	VM3H176A2R1G	VM3H176A2R5G	VM4H176A2GLG	VM4H176A2R1G	VM4H176A2R5G	VM4H176A2ERN
				VM3H175A2GLG	VM3H175A2R1G	VM3H175A2R5G	VM4H175A2GLG	VM4H175A2R1G	VM4H175A2R5G	VM4H175A2ERN
250 ⑤	M58	3/4"	Quad Tri 480	VM3H250A2GLG	VM3H250A2R1G	VM3H250A2R5G	VM4H250A2GLG	VM4H250A2R1G	VM4H250A2R5G	VM4H250A2ERN
				VM3H256A2GLG	VM3H256A2R1G	VM3H256A2R5G	VM4H256A2GLG	VM4H256A2R1G	VM4H256A2R5G	VM4H256A2ERN
				VM3H255A2GLG	VM3H255A2R1G	VM3H255A2R5G	VM4H255A2GLG	VM4H255A2R1G	VM4H255A2R5G	VM4H255A2ERN

VM 70 - 250 WATT METAL HALIDE FLEXIBLE PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98 M143	3/4"	Quad Tri 480	VM3H070F2GLG	VM3H070F2R1G	VM3H070F2R5G	VM4H070F2GLG	VM4H070F2R1G	VM4H070F2R5G	VM4H070F2ERN
				VM3H076F2GLG	VM3H076F2R1G	VM3H076F2R5G	VM4H076F2GLG	VM4H076F2R1G	VM4H076F2R5G	VM4H076F2ERN
				VM3H075F2GLG	VM3H075F2R1G	VM3H075F2R5G	VM4H075F2GLG	VM4H075F2R1G	VM4H075F2R5G	VM4H075F2ERN
100	M90 M140	3/4"	Quad Tri 480	VM3H100F2GLG	VM3H100F2R1G	VM3H100F2R5G	VM4H100F2GLG	VM4H100F2R1G	VM4H100F2R5G	VM4H100F2ERN
				VM3H106F2GLG	VM3H106F2R1G	VM3H106F2R5G	VM4H106F2GLG	VM4H106F2R1G	VM4H106F2R5G	VM4H106F2ERN
				VM3H105F2GLG	VM3H105F2R1G	VM3H105F2R5G	VM4H105F2GLG	VM4H105F2R1G	VM4H105F2R5G	VM4H105F2ERN
175 ⑤	M57	3/4"	Quad Tri 480	VM3H170F2GLG	VM3H170F2R1G	VM3H170F2R5G	VM4H170F2GLG	VM4H170F2R1G	VM4H170F2R5G	VM4H170F2ERN
				VM3H176F2GLG	VM3H176F2R1G	VM3H176F2R5G	VM4H176F2GLG	VM4H176F2R1G	VM4H176F2R5G	VM4H176F2ERN
				VM3H175F2GLG	VM3H175F2R1G	VM3H175F2R5G	VM4H175F2GLG	VM4H175F2R1G	VM4H175F2R5G	VM4H175F2ERN
250 ⑤	M58	3/4"	Quad Tri 480	VM3H250F2GLG	VM3H250F2R1G	VM3H250F2R5G	VM4H250F2GLG	VM4H250F2R1G	VM4H250F2R5G	VM4H250F2ERN
				VM3H256F2GLG	VM3H256F2R1G	VM3H256F2R5G	VM4H256F2GLG	VM4H256F2R1G	VM4H256F2R5G	VM4H256F2ERN
				VM3H255F2GLG	VM3H255F2R1G	VM3H255F2R5G	VM4H255F2GLG	VM4H255F2R1G	VM4H255F2R5G	VM4H255F2ERN

① See hazardous application data on pages L131 - L140 for limitations.

② Catalog numbers shown are with guard (except enclosed reflector); to omit guard change ending G to N; e.g. VM3H070A2GLN

③ Catalog numbers shown are with 3/4" conduit openings, change 2 to 3 for 1"; e.g. VM3H070A3GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.

⑥ 175W M57 & 250W M58 Fixtures are EXPORT ONLY (EISA LAW).



METAL HALIDE, 70-250W MOGUL BASE HID



**Ceiling
w/ 5-1/2"
Globe & Guard**



**Wall
w/ 5-1/2"
Refractor & Guard**



**Ceiling
w/ 7-3/4"
Globe & Guard**



**Wall
w/ 7-3/4"
Refractor & Guard**



**Ceiling
w/ Enclosed Reflector**

VM 70 - 250 WATT METAL HALIDE CEILING										
DESCRIPTION				5-1/2 OPTIC THREAD SIZE ②			7-3/4 OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98 M143	3/4"	Quad Tri 480	VM3H070X2GLG	VM3H070X2R1G	VM3H070X2R5G	VM4H070X2GLG	VM4H070X2R1G	VM4H070X2R5G	VM4H070X2ERN
				VM3H076X2GLG	VM3H076X2R1G	VM3H076X2R5G	VM4H076X2GLG	VM4H076X2R1G	VM4H076X2R5G	VM4H076X2ERN
				VM3H075X2GLG	VM3H075X2R1G	VM3H075X2R5G	VM4H075X2GLG	VM4H075X2R1G	VM4H075X2R5G	VM4H075X2ERN
100	M90 M140	3/4"	Quad Tri 480	VM3H100X2GLG	VM3H100X2R1G	VM3H100X2R5G	VM4H100X2GLG	VM4H100X2R1G	VM4H100X2R5G	VM4H100X2ERN
				VM3H106X2GLG	VM3H106X2R1G	VM3H106X2R5G	VM4H106X2GLG	VM4H106X2R1G	VM4H106X2R5G	VM4H106X2ERN
				VM3H105X2GLG	VM3H105X2R1G	VM3H105X2R5G	VM4H105X2GLG	VM4H105X2R1G	VM4H105X2R5G	VM4H105X2ERN
175 ⑥	M57	3/4"	Quad Tri 480	VM3H170X2GLG	VM3H170X2R1G	VM3H170X2R5G	VM4H170X2GLG	VM4H170X2R1G	VM4H170X2R5G	VM4H170X2ERN
				VM3H176X2GLG	VM3H176X2R1G	VM3H176X2R5G	VM4H176X2GLG	VM4H176X2R1G	VM4H176X2R5G	VM4H176X2ERN
				VM3H175X2GLG	VM3H175X2R1G	VM3H175X2R5G	VM4H175X2GLG	VM4H175X2R1G	VM4H175X2R5G	VM4H175X2ERN
250 ⑥	M58	3/4"	Quad Tri 480	VM3H250X2GLG	VM3H250X2R1G	VM3H250X2R5G	VM4H250X2GLG	VM4H250X2R1G	VM4H250X2R5G	VM4H250X2ERN
				VM3H256X2GLG	VM3H256X2R1G	VM3H256X2R5G	VM4H256X2GLG	VM4H256X2R1G	VM4H256X2R5G	VM4H256X2ERN
				VM3H255X2GLG	VM3H255X2R1G	VM3H255X2R5G	VM4H255X2GLG	VM4H255X2R1G	VM4H255X2R5G	VM4H255X2ERN


VM 70 - 250 WATT METAL HALIDE WALL										
DESCRIPTION				5-1/2 OPTIC THREAD SIZE ②			7-3/4 OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98 M143	3/4"	Quad Tri 480	VM3H070B2GLG	VM3H070B2R1G	VM3H070B2R5G	VM4H070B2GLG	VM4H070B2R1G	VM4H070B2R5G	VM4H070B2ERN
				VM3H076B2GLG	VM3H076B2R1G	VM3H076B2R5G	VM4H076B2GLG	VM4H076B2R1G	VM4H076B2R5G	VM4H076B2ERN
				VM3H075B2GLG	VM3H075B2R1G	VM3H075B2R5G	VM4H075B2GLG	VM4H075B2R1G	VM4H075B2R5G	VM4H075B2ERN
100	M90 M140	3/4"	Quad Tri 480	VM3H100B2GLG	VM3H100B2R1G	VM3H100B2R5G	VM4H100B2GLG	VM4H100B2R1G	VM4H100B2R5G	VM4H100B2ERN
				VM3H106B2GLG	VM3H106B2R1G	VM3H106B2R5G	VM4H106B2GLG	VM4H106B2R1G	VM4H106B2R5G	VM4H106B2ERN
				VM3H105B2GLG	VM3H105B2R1G	VM3H105B2R5G	VM4H105B2GLG	VM4H105B2R1G	VM4H105B2R5G	VM4H105B2ERN
175 ⑥	M57	3/4"	Quad Tri 480	VM3H170B2GLG	VM3H170B2R1G	VM3H170B2R5G	VM4H170B2GLG	VM4H170B2R1G	VM4H170B2R5G	VM4H170B2ERN
				VM3H176B2GLG	VM3H176B2R1G	VM3H176B2R5G	VM4H176B2GLG	VM4H176B2R1G	VM4H176B2R5G	VM4H176B2ERN
				VM3H175B2GLG	VM3H175B2R1G	VM3H175B2R5G	VM4H175B2GLG	VM4H175B2R1G	VM4H175B2R5G	VM4H175B2ERN
250 ⑥	M58	3/4"	Quad Tri 480	VM3H250B2GLG	VM3H250B2R1G	VM3H250B2R5G	VM4H250B2GLG	VM4H250B2R1G	VM4H250B2R5G	VM4H250B2ERN
				VM3H256B2GLG	VM3H256B2R1G	VM3H256B2R5G	VM4H256B2GLG	VM4H256B2R1G	VM4H256B2R5G	VM4H256B2ERN
				VM3H255B2GLG	VM3H255B2R1G	VM3H255B2R5G	VM4H255B2GLG	VM4H255B2R1G	VM4H255B2R5G	VM4H255B2ERN

① See hazardous application data on pages L131 - L140 for limitations.
 ② Catalog numbers shown are with guard (except enclosed reflector); to omit guard change ending G to N; e.g. VM3H070X2GLN
 ③ Catalog numbers shown are with 3/4" conduit openings, change 2 to 3 for 1"; e.g. VM3H070X3GLG.
 ④ Consult catalog logic for other available voltages.
 ⑤ Add suffix NR for restricted breathing; see page L84 for more information.
 ⑥ 175W M57 & 250W M58 Fixtures are EXPORT ONLY (EISA LAW).



LIGHTING

METAL HALIDE, 70-250W MOGUL BASE HID



VM 70 - 250 WATT METAL HALIDE CONE										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98	3/4"	Quad Tri 480	VM3H070C2GLG	VM3H070C2R1G	VM3H070C2R5G	VM4H070C2GLG	VM4H070C2R1G	VM4H070C2R5G	VM4H070C2ERN
	M143			VM3H076C2GLG	VM3H076C2R1G	VM3H076C2R5G	VM4H076C2GLG	VM4H076C2R1G	VM4H076C2R5G	VM4H076C2ERN
				VM3H075C2GLG	VM3H075C2R1G	VM3H075C2R5G	VM4H075C2GLG	VM4H075C2R1G	VM4H075C2R5G	VM4H075C2ERN
100	M90	3/4"	Quad Tri 480	VM3H100C2GLG	VM3H100C2R1G	VM3H100C2R5G	VM4H100C2GLG	VM4H100C2R1G	VM4H100C2R5G	VM4H100C2ERN
	M140			VM3H106C2GLG	VM3H106C2R1G	VM3H106C2R5G	VM4H106C2GLG	VM4H106C2R1G	VM4H106C2R5G	VM4H106C2ERN
					VM3H105C2GLG	VM3H105C2R1G	VM3H105C2R5G	VM4H105C2GLG	VM4H105C2R1G	VM4H105C2R5G
175 ⑥	M57	3/4"	Quad Tri 480	VM3H170C2GLG	VM3H170C2R1G	VM3H170C2R5G	VM4H170C2GLG	VM4H170C2R1G	VM4H170C2R5G	VM4H170C2ERN
				VM3H176C2GLG	VM3H176C2R1G	VM3H176C2R5G	VM4H176C2GLG	VM4H176C2R1G	VM4H176C2R5G	VM4H176C2ERN
				VM3H175C2GLG	VM3H175C2R1G	VM3H175C2R5G	VM4H175C2GLG	VM4H175C2R1G	VM4H175C2R5G	VM4H175C2ERN
250 ⑥	M58	3/4"	Quad Tri 480	VM3H250C2GLG	VM3H250C2R1G	VM3H250C2R5G	VM4H250C2GLG	VM4H250C2R1G	VM4H250C2R5G	VM4H250C2ERN
				VM3H256C2GLG	VM3H256C2R1G	VM3H256C2R5G	VM4H256C2GLG	VM4H256C2R1G	VM4H256C2R5G	VM4H256C2ERN
				VM3H255C2GLG	VM3H255C2R1G	VM3H255C2R5G	VM4H255C2GLG	VM4H255C2R1G	VM4H255C2R5G	VM4H255C2ERN

VM 70 - 250 WATT METAL HALIDE EZ ADAPTER										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98	3/4"	Quad Tri 480	VM3H070EZGLG	VM3H070EZR1G	VM3H070EZR5G	VM4H070EZGLG	VM4H070EZR1G	VM4H070EZR5G	VM4H070EZERN
	M143			VM3H076EZGLG	VM3H076EZR1G	VM3H076EZR5G	VM4H076EZGLG	VM4H076EZR1G	VM4H076EZR5G	VM4H076EZERN
					VM3H075EZGLG	VM3H075EZR1G	VM3H075EZR5G	VM4H075EZGLG	VM4H075EZR1G	VM4H075EZR5G
100	M90	3/4"	Quad Tri 480	VM3H100EZGLG	VM3H100EZR1G	VM3H100EZR5G	VM4H100EZGLG	VM4H100EZR1G	VM4H100EZR5G	VM4H100EZERN
	M140			VM3H106EZGLG	VM3H106EZR1G	VM3H106EZR5G	VM4H106EZGLG	VM4H106EZR1G	VM4H106EZR5G	VM4H106EZERN
					VM3H105EZGLG	VM3H105EZR1G	VM3H105EZR5G	VM4H105EZGLG	VM4H105EZR1G	VM4H105EZR5G
175 ⑥	M57	3/4"	Quad Tri 480	VM3H170EZGLG	VM3H170EZR1G	VM3H170EZR5G	VM4H170EZGLG	VM4H170EZR1G	VM4H170EZR5G	VM4H170EZERN
				VM3H176EZGLG	VM3H176EZR1G	VM3H176EZR5G	VM4H176EZGLG	VM4H176EZR1G	VM4H176EZR5G	VM4H176EZERN
				VM3H175EZGLG	VM3H175EZR1G	VM3H175EZR5G	VM4H175EZGLG	VM4H175EZR1G	VM4H175EZR5G	VM4H175EZERN
250 ⑥	M58	3/4"	Quad Tri 480	VM3H250EZGLG	VM3H250EZR1G	VM3H250EZR5G	VM4H250EZGLG	VM4H250EZR1G	VM4H250EZR5G	VM4H250EZERN
				VM3H256EZGLG	VM3H256EZR1G	VM3H256EZR5G	VM4H256EZGLG	VM4H256EZR1G	VM4H256EZR5G	VM4H256EZERN
				VM3H255EZGLG	VM3H255EZR1G	VM3H255EZR5G	VM4H255EZGLG	VM4H255EZR1G	VM4H255EZR5G	VM4H255EZERN

① See hazardous application data on pages L131 - L140 for limitations.

② Catalog numbers shown are with guard (except enclosed reflector); to omit guard change ending G to N; e.g. VM3H070A2GLN

③ Catalog numbers shown are with 3/4" conduit openings, change 2 to 3 for 1"; e.g. VM3H070A3GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.

⑥ 175W M57 & 250W M58 Fixtures are EXPORT ONLY (EISA LAW).

⑦ VMEZA tank adapters UL "classified" as an assembly for use between VM tanks and EZ mounts. Order EZ mounts separately.



METAL HALIDE, 70-250W MOGUL BASE HID



Stanchion 25°
w/ 5-1/2"
Globe & Guard



Stanchion Straight
w/ 5-1/2"
Refractor & Guard



Stanchion 25°
w/ Enclosed Reflector



Stanchion 25°
w/ 7-3/4"
Globe & Guard



Stanchion Straight
w/ 7-3/4"
Refractor & Guard

VM 70 - 250 WATT METAL HALIDE STANCHION 25° ANGLE										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98 M143	1-1/2"	Quad Tri 480	VM3H070D5GLG	VM3H070D5R1G	VM3H070D5R5G	VM4H070D5GLG	VM4H070D5R1G	VM4H070D5R5G	VM4H070D5ERN
				VM3H076D5GLG	VM3H076D5R1G	VM3H076D5R5G	VM4H076D5GLG	VM4H076D5R1G	VM4H076D5R5G	VM4H076D5ERN
				VM3H075D5GLG	VM3H075D5R1G	VM3H075D5R5G	VM4H075D5GLG	VM4H075D5R1G	VM4H075D5R5G	VM4H075D5ERN
100	M90 M140	1-1/2"	Quad Tri 480	VM3H100D5GLG	VM3H100D5R1G	VM3H100D5R5G	VM4H100D5GLG	VM4H100D5R1G	VM4H100D5R5G	VM4H100D5ERN
				VM3H106D5GLG	VM3H106D5R1G	VM3H106D5R5G	VM4H106D5GLG	VM4H106D5R1G	VM4H106D5R5G	VM4H106D5ERN
				VM3H105D5GLG	VM3H105D5R1G	VM3H105D5R5G	VM4H105D5GLG	VM4H105D5R1G	VM4H105D5R5G	VM4H105D5ERN
175 ⑥	M57	1-1/2"	Quad Tri 480	VM3H170D5GLG	VM3H170D5R1G	VM3H170D5R5G	VM4H170D5GLG	VM4H170D5R1G	VM4H170D5R5G	VM4H170D5ERN
				VM3H176D5GLG	VM3H176D5R1G	VM3H176D5R5G	VM4H176D5GLG	VM4H176D5R1G	VM4H176D5R5G	VM4H176D5ERN
				VM3H175D5GLG	VM3H175D5R1G	VM3H175D5R5G	VM4H175D5GLG	VM4H175D5R1G	VM4H175D5R5G	VM4H175D5ERN
250 ⑥	M58	1-1/2"	Quad Tri 480	VM3H250D5GLG	VM3H250D5R1G	VM3H250D5R5G	VM4H250D5GLG	VM4H250D5R1G	VM4H250D5R5G	VM4H250D5ERN
				VM3H256D5GLG	VM3H256D5R1G	VM3H256D5R5G	VM4H256D5GLG	VM4H256D5R1G	VM4H256D5R5G	VM4H256D5ERN
				VM3H255D5GLG	VM3H255D5R1G	VM3H255D5R5G	VM4H255D5GLG	VM4H255D5R1G	VM4H255D5R5G	VM4H255D5ERN

VM 70 - 250 WATT METAL HALIDE STANCHION STRAIGHT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
70	M98 M143	1-1/2"	Quad Tri 480	VM3H070S5GLG	VM3H070S5R1G	VM3H070S5R5G	VM4H070S5GLG	VM4H070S5R1G	VM4H070S5R5G	VM4H070S5ERN
				VM3H076S5GLG	VM3H076S5R1G	VM3H076S5R5G	VM4H076S5GLG	VM4H076S5R1G	VM4H076S5R5G	VM4H076S5ERN
				VM3H075S5GLG	VM3H075S5R1G	VM3H075S5R5G	VM4H075S5GLG	VM4H075S5R1G	VM4H075S5R5G	VM4H075S5ERN
100	M90 M140	1-1/2"	Quad Tri 480	VM3H100S5GLG	VM3H100S5R1G	VM3H100S5R5G	VM4H100S5GLG	VM4H100S5R1G	VM4H100S5R5G	VM4H100S5ERN
				VM3H106S5GLG	VM3H106S5R1G	VM3H106S5R5G	VM4H106S5GLG	VM4H106S5R1G	VM4H106S5R5G	VM4H106S5ERN
				VM3H105S5GLG	VM3H105S5R1G	VM3H105S5R5G	VM4H105S5GLG	VM4H105S5R1G	VM4H105S5R5G	VM4H105S5ERN
175 ⑥	M57	1-1/2"	Quad Tri 480	VM3H170S5GLG	VM3H170S5R1G	VM3H170S5R5G	VM4H170S5GLG	VM4H170S5R1G	VM4H170S5R5G	VM4H170S5ERN
				VM3H176S5GLG	VM3H176S5R1G	VM3H176S5R5G	VM4H176S5GLG	VM4H176S5R1G	VM4H176S5R5G	VM4H176S5ERN
				VM3H175S5GLG	VM3H175S5R1G	VM3H175S5R5G	VM4H175S5GLG	VM4H175S5R1G	VM4H175S5R5G	VM4H175S5ERN
250 ⑥	M58	1-1/2"	Quad Tri 480	VM3H250S5GLG	VM3H250S5R1G	VM3H250S5R5G	VM4H250S5GLG	VM4H250S5R1G	VM4H250S5R5G	VM4H250S5ERN
				VM3H256S5GLG	VM3H256S5R1G	VM3H256S5R5G	VM4H256S5GLG	VM4H256S5R1G	VM4H256S5R5G	VM4H256S5ERN
				VM3H255S5GLG	VM3H255S5R1G	VM3H255S5R5G	VM4H255S5GLG	VM4H255S5R1G	VM4H255S5R5G	VM4H255S5ERN

① See hazardous application data on pages L131 - L140 for limitations.

② Catalog numbers shown are with guard (except enclosed reflector); to omit guard change ending G to N; e.g. VM3P150A2GLN

③ Catalog numbers shown are with 3/4" conduit openings; change 5 to 4 for 1-1/4"; e.g. VM3H070D4GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.

⑥ 175W M57 & 250W M58 Fixtures are EXPORT ONLY (EISA LAW).