


Special Application Commercial Pump Three Phase Totally Enclosed Fan Cooled (TEFC) C-Face



APPLICATIONS:

For use on chiller, condensate, and other HVAC duty pumps, booster and irrigation pumps, dishwasher and part washer pumps, watering and de-watering pumps, and other commercial duty pumping applications.


FEATURES:

- Totally Enclosed, 50 Hertz Motors supplied with CE Markings
- Double Sealed Ball Bearings On All 56 Frame Commercial Duty Pump Motors
- Double Shielded Ball Bearings On All Other Motors
- Continuous Duty
- 60 Hertz & 60/50 Hertz
- 50/60 Hertz Motors have 1.0 Service Factor on 50 Hertz
- 40°C Ambient
- Shaft Slinger On Pulley End
- NEMA® "C" Flange Mounting
- Premium 303 S.S. on 56J Mount: 7/16-20 UNC-2A
- Shaft Threads for 56J Mount: 7/16-20 UNC-2A

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	Base (Feet)	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Max Amps	Notes
1/4	1800	208-230/460	56C	U14S2DCR	DS-3RST	No	1.25	10.8	23	70.0	0-1.1/0.5	16
	1800	575	56C	U14P2GC	DS-3RST	Rigid	1.25	10.8	30	74.0	0.4	
	1200	208-230/460	56C	T14S3DCR	DS-3RST	No	1.15	11.3	27	75.5	1.6-1.6/0.8	
	1200	575	56C	U14P3GC	DS-3RST	Rigid	1.25	10.8	30	72.0	0.6	
1/3	3600	208-230/460	56C	T13S1ACR	DS-3RST	No	1.15	10.8	32	-	1.8-1.9/1.0	
	1800	208-230/460	42CZ	T13S2D4ZCR	DS-3RST	No	1.00	10.4	9	65.0	1.5-1.5/0.75	
	1800	208-230/460	56C	U13S2ACR	DS-3RST	No	1.25	10.8	25	75.5	1.4-1.3/0.7	16
	1800	575	56C	U13P2GC	DS-3RST	Rigid	1.25	10.8	30	74.0	0.5	
	1800	575	56C	T13S2GCR	DS-3RST	No	1.15	11.4	26	75.3	0.62	
	1200	208-230/460	56C	T13S3DCR	DS-3RST	No	1.15	11.3	32	77.0	1.7-1.7/0.9	
	1200	575	56C	U13P3GC	DS-3RST	Rigid	1.25	10.8	30	72.0	0.8	
	1200	575	56C	U13P3GC	DS-3RST	Rigid	1.25	10.8	30	72.0	0.8	
1/2	3600	208-230/460	56J	EE283B	DS-3RST	Rigid	1.60	11.2	26	-	2.8-2.7/1.35	98
	3600	208-230/460	56C	T12S1ACR	DS-3RST	No	1.15	10.9	32	64.0	2.34-2.34/1.17	
	3600	208-230/460	56J	EE283	DS-3RST	No	1.60	11.2	17	-	2.8-2.7/1.35	98
	3600	575	56C	U12P1GC	DS-3RST	Rigid	1.25	12.1	30	74.0	0.6	
	1800	208-230/460	56C	U12P2DCR	DS-3RST	No	1.25	12.1	30	82.5	1.8/0.9	03
	1800	208-230/460	56C	U12S2ACR	DS-3RST	No	1.25	10.8	25	75.5	2.1-2/1	16
	1800	208-230/460	56C	EE256	DS-CPMP	No	1.15	11.1	22	-	2.2-2.0/1.0	98
	1800	575	56C	U12P2GC	DS-3RST	Rigid	1.25	10.8	30	78.5	0.9	
	1800	575	56C	U12P2GCR	DS-3RST	No	1.25	10.8	30	78.5	0.9	
	1200	208-230/460	56C	U12S3ACR	DS-3RST	No	1.25	10.8	25	72.0	2.5-2.3/1.2	16
	1200	575	56C	U12P3GC	DS-3RST	Rigid	1.25	12.1	30	75.5	0.9	
	3600	208-230/460	56J	EE515B	DS-3RST	Rigid	1.50	11.9	22	-	3.7-3.6/1.8	98
	3600	208-230/460	56C	U34S1ACR	DS-3RST	No	1.25	10.8	27	75.5	0-2.6/1.3	16
	3600	208-230/460	56J	EE515	DS-3RST	No	1.50	11.9	17	-	3.7-3.6/1.8	98
	3600	575	56C	U34P1GC	DS-3RST	Rigid	1.25	12.1	30	77.0	0.8	
	3600	575	56C	U34P1GCR	DS-3RST	No	1.25	12.1	30	77.0	0.8	
3600	575	56J	EE515-5PE	DS-3RST	No	1.25	12.6	30	77.0	1		
1800	208-230/460	56J	EE586	DS-3RST	Rigid	1.25	12.4	27	81.7	3.0-2.9/1.5	03,98	
1800	208-230/460	56C	U34P2DCR	DS-3RST	No	1.25	12.1	30	84.0	2.3/1.1	03	
1800	208-230/460	56C	U34S2ACR	DS-3RST	No	1.25	10.8	28	78.5	3.1-3/1.5	16	
1800	575	56C	U34P2GC	DS-3RST	Rigid	1.25	10.8	30	81.5	1.1		
1800	575	56C	U34P2GCR	DS-3RST	No	1.25	10.8	30	81.5	1.1		
1200	575	143TC	U34P3G14C	DS-3RST	Rigid	1.25	12.1	30	82.5	1.3		
1200	208-230/460	56C	U34S3ACR	DS-3RST	No	1.15	12.8	32	-	3.4-3.4/1.7		
1200	575	56C	U34P3GC	DS-3RST	Rigid	1.25	12.1	30	82.5	1.3		
1200	575	56C	U34P3GCR	DS-3RST	No	1.25	12.1	30	82.5	1.3		
1	3600	208-230/460	56C	U1P1DC	DS-3RST	Rigid	1.25	13.1	30	81.5	3.6-3.2/1.6	03
	3600	208-230/460	56C	U1P1DCR	DS-3RST	No	1.25	13.1	30	81.5	3.6-3.2/1.6	03
	3600	208-230/460	56J	EE516B	DS-3RST	No	1.40	11.2	17	77.0	4.4-4.2/2.1	98
	3600	208-230/460	56J	EE516	DS-3RST	No	1.40	11.2	28	77.0	4.4-4.2/2.1	98
	3600	575	56C	U1P1GCR	DS-3RST	No	1.25	10.8	30	80.0	1.3	
	3600	575	56C	U1P1GC	DS-3RST	No	1.25	13.1	50	81.5	1.3	
	1800	208-230/460	143TC	U1P2DC	DS-3RST	Rigid	1.25	13.1	30	85.5	0-3.4/1.7	03
	1800	208-230/460	143TC	U1P2DCR	DS-3RST	No	1.25	12.1	30	85.5	0-3.4/1.7	03
	1800	575	143TC	U1P2GC	DS-3RST	Rigid	1.25	13.1	30	85.5	1.3	
	1800	575	143TC	U1P2GCR	DS-3RST	No	1.25	13.1	30	85.5	1.3	
	1800	208-230/460	56J	EE684	DS-3RST	Removeable	1.15	13.4	27	85.5	3.6-3.7/1.8	03,98
	1800	208-230/460	56C	U1P2DFC	DS-3RST	Rigid	1.25	13.1	30	85.5	3.7-3.4/1.7	03
	1800	208-230/460	56C	U1P2DFCR	DS-3RST	No	1.25	13.1	30	85.5	3.7-3.4/1.7	03
	1800	575	56C	U1P2GFC	DS-3RST	Rigid	1.25	13.1	30	85.5	1.3	03
	1800	575	56C	U1P2GFCR	DS-3RST	No	1.25	13.1	30	85.5	1.3	03

Note 03 60/50 Hz rated with no derate on HP; 230/460 volt 60 Hz ratings operate on 190/380 volt 50 Hz, 460V 60 Hz ratings operate on 380V 50 Hz; Full 60 & 50 Hz data on Nameplate
 Note 16 Motors marked 208-230/460 volts may not meet all NEMA (MG-1) performance standards when operated at 208 volts
 Note 98 50/60 Hz Motor

Special Application Commercial Pump Three Phase Totally Enclosed Fan Cooled (TEFC) C-Face



(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	Base (Feet)	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Max Amps	Notes	
1	1200	208-230/460	145TC	U1P3DC	DS-3RST	Rigid	1.25	13.1	35	82.5	4.3-4/2	03	
	1200	575	145TC	U1P3GC	DS-3RST	Rigid	1.25	13.1	35	82.5	1.6		
	1200	208-230/460	56C	U1P3DFC	DS-3RST	Rigid	1.25	13.1	30	82.5	4.3-4/2	03	
	1200	575	56C	U1P3GFC	DS-3RST	Rigid	1.25	13.1	30	82.5	1.6		
	1200	575	56C	U1P3GFCR	DS-3RST	No	1.25	13.4	35	82.5	1.6		
1 1/2	3600	200	143TC	U32P1HC	DS-3RST	Rigid	1.25	13.1	30	84.0	5.4		
	3600	208-230/460	143TC	U32P1DC	DS-3RST	Rigid	1.25	13.1	30	84.0	5.3-4.7/2.4	03	
	3600	208-230/460	143TC	U32P1A14CR	DS-3RST	No	1.15	11.9	32	84.0	4.9-5.2/2.6		
	3600	575	143TC	U32P1GC	DS-3RST	Rigid	1.25	13.1	30	84.0	1.9		
	3600	575	143TC	U32P1GCR	DS-3RST	No	1.25	13.1	30	84.0	1.9		
	3600	208-230/460	56C	U32P1DFC	DS-3RST	Rigid	1.25	13.1	30	84.0	5.3-4.7/2.4	03	
	3600	208-230/460	56J	EE661B	DS-3RST	Rigid	1.30	12.9	37	84.0	4.9-4.6/2.4	98	
	3600	208-230/460	56C	T32P1ACR	DS-3RST	No	1.15	12.3	32	84.0	4.9-5.2/2.6		
	3600	208-230/460	56J	EE661	DS-3RST	No	1.30	12.9	34	84.0	4.9-4.6/2.4	98	
	3600	208-230/460	56C	T32S1ACR	DS-3RST	No	1.15	11.9	27	80.0	4.8/2.4	LA	
	3600	575	56C	U32P1GFC	DS-3RST	Rigid	1.25	13.1	30	84.0	1.9		
	3600	575	56C	U32P1GFRCR	DS-3RST	No	1.25	13.1	30	84.0	1.9		
	1800	200	145TC	U32P2HC	DS-3RST	Rigid	1.25	13.1	35	86.5	5.7		
	1800	208-230/460	145TC	U32P2DC	DS-3RST	Rigid	1.15	13.1	35	86.5	5.4-5/2.4	03	
	1800	208-230/460	145TC	U32P2DCR	DS-3RST	No	1.15	13.1	35	86.5	5.4-5/2.4	03	
	1800	575	145TC	U32P2GC	DS-3RST	Rigid	1.25	13.1	35	86.5	2		
	1800	575	145TC	U32P2GCR	DS-3RST	No	1.25	13.1	35	86.5	2		
	1800	208-230/460	56C	U32P2DFC	DS-3RST	Rigid	1.25	13.1	30	86.5	5.4-5/2.5	03	
	1800	208-230/460	56J	EE694	DS-3RST	Rigid	1.15	13.9	32	86.5	4.9-4.9/2.5	03,98	
	1800	208-230/460	56C	U32P2DFCR	DS-3RST	No	1.25	13.1	30	86.5	5.4-5/2.5	03	
	1800	575	56C	U32P2GFC	DS-3RST	Rigid	1.25	13.1	30	86.5	2	03	
	1800	575	56C	U32P2GFRCR	DS-3RST	No	1.25	13.1	30	86.5	2		
	1200	208-230/460	182TC	U32P3DC	DS-3AL	Rigid	1.25	16.2	60	87.5	0.5-5/2.7	03	
	1200	575	182TC	U32P3GC	DS-3AL	Rigid	1.25	16.2	60	87.5	2.2		
2	3600	208-230/460	145TC	U2P1DC	DS-3RST	Rigid	1.25	13.1	35	86.5	6.8-6/3	03	
	3600	575	145TC	U2P1GC	DS-3RST	Rigid	1.25	13.1	35	86.5	2.4		
	3600	208-230/460	56C	U2P1DFC	DS-3RST	Rigid	1.25	13.1	30	86.5	6.8-6/3	03	
	3600	208-230/460	56J	EE706B	DS-3RST	Rigid	1.25	13.4	39	85.5	5.4-5.1/2.6	98	
	3600	208-230/460	56J	EE706	DS-3RST	No	1.25	13.4	36	85.5	6.6-6.1/3.1	98	
	3600	208-230/460	56C	T2P1ACR	DS-3RST	No	1.15	13.6	35	85.5	7.1-6.0/3.0	04,16	
	3600	575	56C	U2P1GFC	DS-3RST	Rigid	1.25	13.1	30	86.5	2.4		
	3600	575	56C	U2P1GFRCR	DS-3RST	No	1.25	13.1	30	86.5	2.4		
	1800	208-230/460	145TC	U2P2DC	DS-3RST	Rigid	1.15	13.1	35	86.5	0.6-3/3.1	03	
	1800	208-230/460	145TC	U2P2DCR	DS-3RST	No	1.25	13.1	35	86.5	7.2-6.7/3.3	03	
	1800	575	145TC	U2P2GC	DS-3RST	Rigid	1.25	13.1	35	86.5	2.7		
	1800	575	145TC	U2P2GCR	DS-3RST	No	1.25	13.1	35	86.5	2.7		
	1800	208-230/460	56C	U2P2DFC	DS-3RST	Rigid	1.25	13.1	30	86.5	7.2-6.7/3.3	03	
	1800	208-230/460	56J	EE2156	DS-3RST	Rigid	1.15	14.4	37	86.5	6.5-6.6/3.3	03,98	
	1800	208-230/460	56C	U2P2DFCR	DS-3RST	No	1.25	13.1	30	86.5	7.2-6.7/3.3	03	
	1800	575	56C	U2P2GFC	DS-3RST	Rigid	1.25	13.9	50	85.5	3	04,16	
	1200	208-230/460	184TC	U2P3DC	DS-3AL	Rigid	1.25	16.9	70	88.5	0.7-2/3.6	03	
	1200	575	184TC	U2P3GC	DS-3AL	Rigid	1.25	16.2	70	88.5	2.9		
	3	3600	208-230/460	145TC	U3P1AFC	DS-3RST	Rigid	1.25	13.1	35	86.5	9.4-9.1/4.5	03,14
		3600	208-230/460	145TC	U3P1A14CR	DS-3RST	No	1.25	13.9	34	86.5	8.7/4.3	04,16
3600		575	145TC	U3P1G14C	DS-3RST	Rigid	1.25	13.1	35	86.5	3.6		
3600		575	145TC	U3P1GCR	DS-3RST	No	1.25	13.1	35	86.5	3.6		
3600		208-230/460	182TC	U3P1DC	DS-3AL	Rigid	1.25	16.2	50	87.5	0.9-4/4.7	03	
3600		208-230/460	182TCH	U3P1DK	DS-3AL	Rigid	1.25	16.2	50	87.5	0.9-4/4.7	03	
3600		575	182TC	U3P1GC	DS-3AL	Rigid	1.25	16.2	60	87.5	3.8		
3600		208-230/460	56C	U3P1DFC	DS-3RST	Rigid	1.25	13.1	30	86.5	9.4-9.1/4.5	03	
3600		208-230/460	56J	EE707B	DS-3RST	Rigid	1.15	13.9	42	86.5	9.1-8.2/4.2		
3600		208-230/460	56C	T3P1ACR	DS-3RST	No	1.15	14.1	40	86.5	7.7/3.9		
3600		208-230/460	56J	EE707	DS-3RST	No	1.15	14.4	42	86.5	9.1-8.2/4.2		
3600		575	56C	U3P1GFC	DS-3RST	Rigid	1.25	13.1	30	86.5	3.6		
3600		575	56C	U3P1GFRCR	DS-3RST	No	1.25	13.1	30	86.5	3.6		
1800		208-230/460	182TC	U3P2DC	DS-3AL	Rigid	1.25	16.2	70	89.5	0.9-5/4.7	03	
1800		208-230/460	182TCH	U3P2DK	DS-3AL	Rigid	1.25	16.2	60	89.5	0.9-5/4.7	03	
1800		208-230/460	182TC	S3P2AC	DS-3RST	Rigid	1.15	15.9	85	89.5	9.6-8.8/4.4	04,16	
1800		208-230/460	182TC	S3P2ACR	DS-3RST	No	1.15	15.9	60	89.5	9.6-8.8/4.4	04,16	
1800		575	182TC	U3P2GC	DS-3AL	Rigid	1.25	16.2	60	89.5	3.8		
1800		575	182TC	S3P2GCR	DS-3RST	Rigid	1.15	15.9	60	89.5	3.5	04	
1800		575	182TC	S3P2GCR	DS-3RST	No	1.15	15.9	60	89.5	3.5	04	
1200		208-230/460	213TC	U3P3DC	DS-3AL	Rigid	1.15	18.8	110	89.5	0-10.5/4.9	03	


Note 03 60/50 Hz rated with no derate on HP; 230/460 volt 60 Hz ratings operate on 190/380 volt 50 Hz, 460V 60 Hz ratings operate on 380V 50 Hz; Full 60 & 50 Hz data on Nameplate

Note 04 On 60 Hertz Sine Wave power
Note 14 NEMA[®] Design A

Note 16 Motors marked 208-230/460 volts may not meet all NEMA (MG-1) performance standards when operated at 208 volts

Note 98 50/60 Hz Motor
Note LA Limited Availability

Special Application Commercial Pump Three Phase Totally Enclosed Fan Cooled (TEFC) C-Face



(continued)

HP	RPM	Voltage	Frame	Catalog Number	Discount Symbol	Base (Feet)	SF	"C" Dim. (inches)	Ship Wt. (lbs)	Full Load Eff.	Max Amps	Notes	
5	3600	208-230/460	184TC	U5P1DC	DS-3AL	Rigid	1.15	16.2	75	88.5	0-13.8/6.9	03	
	3600	208-230/460	184TCH	U5P1DK	DS-3AL	Rigid	1.15	16.2	75	88.5	0-13.8/6.9	03	
	3600	208-230/460	184TC	S5P1AC	DS-3RST	Rigid	1.15	15.9	65	88.5	16-14/7	04,16	
	3600	208-230/460	184TC	S5P1ACR	DS-3RST	No	1.15	15.9	70	88.5	16-14/7	04,16	
	3600	575	184TC	S5P1GC	DS-3RST	Rigid	1.15	15.9	70	88.5	5.6	04	
	3600	575	184TC	U5P1GC	DS-3AL	Rigid	1.25	16.2	70	88.5	6.1		
	3600	575	184TC	S5P1GCR	DS-3RST	No	1.15	15.9	70	88.5	5.6	04	
	1800	200	184TCH	U5P2HK	DS-3AL	Rigid	1.25	16.9	80	89.5	17.6	03	
	1800	208-230/460	184TC	U5P2DC	DS-3AL	Rigid	1.25	16.9	80	90.2	17.4-15.3/7.7	03	
	1800	208-230/460	184TCH	U5P2DK	DS-3AL	Rigid	1.25	16.9	80	90.2	17.4-15.3/7.7	03	
	1800	208-230/460	184TC	S5P2AC	DS-3RST	Rigid	1.15	15.9	110	89.5	0-14.1/7	04,16	
	1800	208-230/460	184TC	S5P2ACR	DS-3RST	No	1.15	15.9	70	89.5	15.7-14.1/7	04,16	
	1800	575	184TC	U5P2GC	DS-3AL	Rigid	1.25	16.9	70	89.5	6.2		
	1800	575	184TC	S5P2GC	DS-3RST	Rigid	1.15	15.9	70	89.5	5.6	04	
	1800	575	184TC	S5P2GCR	DS-3RST	No	1.15	15.9	70	89.5	5.6	04	
	1200	208-230/460	215TC	U5P3DC	DS-3AL	Rigid	1.25	20.3	135	90.2	0-16.8/8.4	03	
1200	575	215TC	U5P3GC	DS-3AL	Rigid	1.25	20.3	135	89.5	6.7			
7 1/2	3600	208-230/460	213TC	S7P1AC	DS-3RST	Rigid	1.15	19.4	116	89.5	23.4-20.5/10.3	04,16	
	3600	208-230/460	213TC	U7P1DC	DS-3AL	Rigid	1.25	18.8	105	91.0	0-22.3/11.2	03	
	3600	208-230/460	213TC	S7P1ACR	DS-3RST	No	1.15	19.4	105	89.5	23.4-20.5/10.3	04,16	
	3600	575	213TC	U7P1GC	DS-3AL	Rigid	1.25	18.8	105	89.5	9.3		
	3600	575	213TC	S7P1GC	DS-3RST	Rigid	1.15	19.4	105	89.5	8.3	04,16	
	3600	575	213TC	S7P1GCR	DS-3RST	No	1.15	19.4	105	89.5	8.3	04	
	1800	208-230/460	213TC	U7P2DC	DS-3AL	Rigid	1.25	19.1	105	91.7	0-22.5/11.3	03	
	1800	208-230/460	213TC	S7P2AC	DS-3RST	Rigid	1.15	19.4	90	91.7	23.1-20.7/10.4	04,16	
	1800	208-230/460	213TC	S7P2ACR	DS-3RST	No	1.15	19.4	105	91.7	23.1-20.7/10.4	04,16	
	1800	575	213TC	S7P2GC	DS-3RST	Rigid	1.15	19.4	105	91.7	8.3	04,16	
	1800	575	213TC	U7P2GC	DS-3AL	Rigid	1.25	18.8	105	91.7	9		
	1800	575	213TC	S7P2GCR	DS-3RST	No	1.15	19.4	105	91.7	8.3	04	
	1200	208-230/460	254TC	U7P3DC	DS-3AL	Rigid	1.25	23.9	180	91.0	0-23.1/11.6	03	
	1200	575	254TC	U7P3GC	DS-3AL	Rigid	1.25	24.0	180	91.0	9.3		
	10	3600	208-230/460	215TC	U10P1DC	DS-3AL	Rigid	1.25	20.3	125	91.0	35-29.8/14.9	03
		3600	208-230/460	215TC	S10P1AC	DS-3RST	Rigid	1.15	19.4	131	90.2	0-27.2/13.6	04,16
3600		208-230/460	215TC	S10P1ACR	DS-3RST	No	1.15	19.4	120	90.2	31-27.2/13.6	04,16	
3600		575	215TC	U10P1GC	DS-3AL	Rigid	1.25	20.1	125	91.7	11.9		
3600		575	215TC	S10P1GC	DS-3RST	Rigid	1.15	19.4	120	90.2	10.9	04,16	
3600		575	215TC	S10P1GCR	DS-3RST	No	1.15	19.4	120	90.2	10.9	04	
1800		208-230/460	215TC	U10P2DC	DS-3AL	Rigid	1.25	20.3	133	91.7	0-30/15	03	
1800		208-230/460	215TC	S10P2AC	DS-3RST	Rigid	1.15	19.4	120	91.7	31-27.5/13.8	04,16	
1800		208-230/460	215TC	S10P2ACR	DS-3RST	No	1.15	19.4	120	91.7	31-27.5/13.8	04,16	
1800		575	215TC	U10P2GC	DS-3AL	Rigid	1.25	20.3	133	91.7	12		
1800		575	215TC	S10P2GC	DS-3RST	Rigid	1.15	19.4	120	91.7	11	04,16	
1800		575	215TC	S10P2GCR	DS-3RST	No	1.15	19.4	120	91.7	11	04	
1200		208-230/460	256TC	U10P3DC	DS-3AL	Rigid	1.25	25.8	230	91.7	0-31/15.3	03	
15		3600	208-230/460	215TC	U15P1DFC	DS-3AL	Rigid	1.25	20.3	120	91.0	0-45/22.5	03
		3600	208-230/460	254TC	U15P1DC	DS-3AL	Rigid	1.25	24.0	180	91.0	0-44/22.2	02,03
		3600	575	254TC	U15P1GC	DS-3AL	Rigid	1.25	24.0	185	91.0	17.9	
	1800	208-230/460	254TC	U15P2DC	DS-3AL	Rigid	1.15	23.9	180	92.4	0-42/21	03	
20	3600	208-230/460	256TC	U20P1DC	DS-3AL	Rigid	1.25	25.6	230	91.0	0-59/29.7	02,03	
	3600	575	256TC	U20P1GC	DS-3AL	Rigid	1.25	25.8	230	91.0	23.9	02	
	1800	208-230/460	256TC	U20P2DC	DS-3AL	Rigid	1.25	25.8	230	93.0	0-60/29.8	03	
25	3600	208-230/460	284TC	U25P1DC	DS-3AL	Rigid	1.25	28.3	250	91.7	0-74/37	03	
	1800	208-230/460	284TC	U25P2DC	DS-3AL	Rigid	1.25	28.3	280	93.6	0-74/37	03	
30	1800	208-230/460	286TC	U30P2DC	DS-3AL	Rigid	1.25	28.4	325	93.6	92-91/45	03	

Note 02 Suitable for Wye-Delta start on voltages shown
 Note 03 60/50 Hz rated with no derate on HP; 230/460 volt 60 Hz ratings operate on 190/380 volt 50 Hz, 460V 60 Hz ratings operate on 380V 50 Hz; Full 60 & 50 Hz data on Nameplate

Note 04 On 60 Hertz Sine Wave power
 Note 16 Motors marked 208-230/460 volts may not meet all NEMA (MG-1) performance standards when operated at 208 volts