



Data sheet | Item number: 2022-1207

1-conductor/1-pin ground carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>; Push-in CAGE CLAMP®



2022-1207





## Data

### Connection data

Connection technology	Push-in CAGE CLAMP®
Actuation type	Open Tool Slot Push-in
Connectable conductor materials	Copper
Nominal cross section	2.5 mm <sup>2</sup>
Solid conductor	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
Solid conductor, push-in termination	0.75 ... 4 mm <sup>2</sup> / 18 ... 12 AWG
Fine-stranded conductor	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
Strip length	10 ... 12 mm / 0.39 ... 0.47 inch
Note (conductor cross-section)	Depending on the conductor characteristic, a conductor with a smaller cross section can also be inserted via push-in termination.
Total number of connection points	1
Total number of potentials	1
Number of levels	1
Type of wiring	Front-entry wiring

### Geometrical Data

Width	5.2 mm / 0.205 inch
Height from upper-edge of DIN-35 rail	32.5 mm / 1.28 inch
Depth	50.8 mm / 0.2 inch

## Mechanical data

Design	horizontal
Type of mounting	DIN-35 rail
Marking level	Center/side marking

## Material Data




Color	green-yellow
Insulating material	Polyamide 66 (PA 66)
Fire load	0.108 MJ
Weight	7.837 g

## Commercial data


Product Group	18 (X-COM-System)
Country of origin	CN
GTIN	4050821145097
Customs Tariff No.	85366990990

## Approvals / Certificates

### Country specific Approvals

Logo	Approval	Additional Approval Text	Certificate name
	CCA DEKRA Certification B.V.	EN 60947	NTR NL 7628
	CSA DEKRA Certification B.V.	C22.2 No. 158	70107915
	KEMA/KEUR DEKRA Certification B.V.	EN 61984	71- 101201

### UL-Approvals

Logo	Approval	Additional Approval Text	Certificate name
	UR Underwriters Laboratories Inc.	UL 1059	E45172

















## Compatible products
















## End plate
















	<b>Item no.: 2022-1291</b> End and intermediate plate; 1 mm thick	2022-1291
	<b>Item no.: 2022-1292</b> End and intermediate plate; 1 mm thick	2022-1292



















## Marking accessories



















	<b>Item no.: 2002-161</b> Adaptor	2002-161
	<b>Item no.: 2009-110</b> Marking strips; on reel; not stretchable; plain; snap-on type	2009-110
	<b>Item no.: 2009-115</b> WMB-Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115
	<b>Item no.: 2009-115/000-002</b> WMB-Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115 /000-002
	<b>Item no.: 2009-115/000-005</b> WMB-Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115 /000-005
	<b>Item no.: 2009-115/000-006</b> WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115 /000-006
	<b>Item no.: 2009-115/000-007</b> WMB-Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115 /000-007
	<b>Item no.: 2009-115/000-012</b> WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115 /000-012
	<b>Item no.: 2009-115/000-017</b> WMB-Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115 /000-017

















	<b>Item no.: 2009-115/000-023</b> WMB-Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115
		/000-023
	<b>Item no.: 2009-115/000-024</b> WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-115
		/000-024
	<b>Item no.: 2009-145</b> Mini-WSB Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
	<b>Item no.: 2009-145/000-002</b> Mini-WSB Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
		/000-002
	<b>Item no.: 2009-145/000-005</b> Mini-WSB Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
		/000-005
	<b>Item no.: 2009-145/000-006</b> Mini-WSB Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
		/000-006
	<b>Item no.: 2009-145/000-007</b> Mini-WSB Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
		/000-007
	<b>Item no.: 2009-145/000-012</b> Mini-WSB Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
		/000-012
	<b>Item no.: 2009-145/000-023</b> Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
		/000-023
	<b>Item no.: 2009-145/000-024</b> Mini-WSB Inline; for Smart Printer; on reel; stretchable 5 - 5.2 mm; plain; snap-on type	2009-145
		/000-024
	<b>Item no.: 2009-191</b> Group marker carrier	2009-191
	<b>Item no.: 2009-192</b> Group marker carrier	2009-192
	<b>Item no.: 2009-193</b> Group marker carrier	2009-193
	<b>Item no.: 2009-198</b> Adaptor	2009-198
	<b>Item no.: 248-501</b> Miniature WSB Quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	248-501
	<b>Item no.: 248-501/000-002</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	248-501
		/000-002


















	<b>Item no.: 248-501/000-005</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	/000-005	248-501
	<b>Item no.: 248-501/000-006</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	/000-006	248-501
	<b>Item no.: 248-501/000-007</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	/000-007	248-501
	<b>Item no.: 248-501/000-012</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	/000-012	248-501
	<b>Item no.: 248-501/000-017</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	/000-017	248-501
	<b>Item no.: 248-501/000-023</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	/000-023	248-501
	<b>Item no.: 248-501/000-024</b> Mini-WSB marking card; as card; not stretchable; plain; snap-on type	/000-024	248-501
	<b>Item no.: 793-501</b> WMB marking card; as card; not stretchable; plain; snap-on type		793-501
	<b>Item no.: 793-501/000-002</b> WMB marking card; as card; not stretchable; plain; snap-on type	/000-002	793-501
	<b>Item no.: 793-501/000-005</b> WMB marking card; as card; not stretchable; plain; snap-on type	/000-005	793-501
	<b>Item no.: 793-501/000-006</b> WMB marking card; as card; not stretchable; plain; snap-on type	/000-006	793-501
	<b>Item no.: 793-501/000-007</b> WMB marking card; as card; not stretchable; plain; snap-on type	/000-007	793-501
	<b>Item no.: 793-501/000-012</b> WMB marking card; as card; not stretchable; plain; snap-on type	/000-012	793-501
	<b>Item no.: 793-501/000-017</b> WMB marking card; as card; not stretchable; plain; snap-on type	/000-017	793-501
	<b>Item no.: 793-501/000-023</b> WMB marking card; as card; not stretchable; plain; snap-on type	/000-023	793-501















	<b>Item no.: 793-501/000-024</b> WMB marking card; as card; not stretchable; plain; snap-on type	793-501 /000-024
	<b>Item no.: 793-5501</b> WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501
	<b>Item no.: 793-5501/000-002</b> WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-002
	<b>Item no.: 793-5501/000-005</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-005
	<b>Item no.: 793-5501/000-006</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-006
	<b>Item no.: 793-5501/000-007</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-007
	<b>Item no.: 793-5501/000-012</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-012
	<b>Item no.: 793-5501/000-014</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-014
	<b>Item no.: 793-5501/000-017</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-017
	<b>Item no.: 793-5501/000-023</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-023
	<b>Item no.: 793-5501/000-024</b> WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type	793-5501 /000-024
<b>ferrule</b>		
	<b>Item no.: 216-241</b> Ferrule; Sleeve for 0.5 mm <sup>2</sup> / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-241
	<b>Item no.: 216-242</b> Ferrule; Sleeve for 0.75 mm <sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-242
	<b>Item no.: 216-243</b> Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-243
	<b>Item no.: 216-244</b> Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-244
	<b>Item no.: 216-246</b>	















	Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-246
	<b>Item no.: 216-262</b>	
	Ferrule; Sleeve for 0.75 mm <sup>2</sup> / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-262
	<b>Item no.: 216-263</b>	
	Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-263
	<b>Item no.: 216-264</b>	
	Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-264
	<b>Item no.: 216-266</b>	
	Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-266
	<b>Item no.: 216-284</b>	
	Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-284
	<b>Item no.: 216-286</b>	
	Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	216-286
<b>Carrier rail</b>		
	<b>Item no.: 210-112</b>	
	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm	210-112
	<b>Item no.: 210-113</b>	
	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715	210-113
	<b>Item no.: 210-114</b>	
	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715	210-114
	<b>Item no.: 210-115</b>	
	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm	210-115
	<b>Item no.: 210-118</b>	
	Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715	210-118
	<b>Item no.: 210-196</b>	
	Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715	210-196
	<b>Item no.: 210-197</b>	
	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715	210-197
	<b>Item no.: 210-198</b>	
	Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715	210-198
<b>check</b>		
	<b>Item no.: 2002-511</b>	
	Modular TOPJOB®S connector; modular; for jumper contact slot; 1-pole	2002-511
	<b>Item no.: 2002-549</b>	
	Spacer module; modular; e.g., for bridging commoned terminal blocks	2002-549
	<b>Item no.: 2002-552</b>	
	Modular TOPJOB®S connector; modular; for jumper contact slot; 2-pole	2002-552





	<b>Item no.: 2002-553</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 3-pole	2002-553
	<b>Item no.: 2002-554</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 4-pole	2002-554
	<b>Item no.: 2002-555</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 5-pole	2002-555
	<b>Item no.: 2002-556</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 6-pole	2002-556
	<b>Item no.: 2002-557</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 7-pole	2002-557
	<b>Item no.: 2002-558</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 8-pole	2002-558
	<b>Item no.: 2002-559</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 9-pole	2002-559
	<b>Item no.: 2002-560</b> Modular TOPJOB®S connector; modular; for jumper contact slot; 10-pole	2002-560
	<b>Item no.: 2009-174</b> Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks	2009-174
	<b>Item no.: 2009-182</b> Testing tap; for max. 2.5 mm <sup>2</sup> ; tool-free connection for individual test wires 0.08 - 2.5 mm	2009-182
	<b>Item no.: 859-500</b> Test pin; 1 mm Ø; with solder connection for test wire	859-500
<b>Insulation stop</b>		
	<b>Item no.: 2002-171</b> Insulation stop; 0.25 - 0.5 mm <sup>2</sup> ; 5 pieces/strip	2002-171
	<b>Item no.: 2002-172</b> Insulation stop; 0.75 - 1 mm <sup>2</sup> ; 5 pieces/strip	2002-172
<b>Jumper</b>		
	<b>Item no.: 2002-400</b> Adjacent jumper for continuous commoning; insulated; 2-way; Nominal current 25 A	2002-400
	<b>Item no.: 2002-402</b> Push-in type jumper bar; insulated; 2-way; Nominal current 25 A	2002-402
	<b>Item no.: 2002-402/000-005</b> Push-in type jumper bar; insulated; 2-way; Nominal current 25 A	2002-402 /000-005
	<b>Item no.: 2002-402/000-006</b> Push-in type jumper bar; insulated; 2-way; Nominal current 25 A	2002-402 /000-006
	<b>Item no.: 2002-403</b> Push-in type jumper bar; insulated; 3-way; Nominal current 25 A	2002-403













	<b>Item no.: 2002-403/000-005</b> Push-in type jumper bar; insulated; 3-way; Nominal current 25 A	2002-403 /000-005
	<b>Item no.: 2002-403/000-006</b> Push-in type jumper bar; insulated; 3-way; Nominal current 25 A	2002-403 /000-006
	<b>Item no.: 2002-404</b> Push-in type jumper bar; insulated; 4-way; Nominal current 25 A	2002-404
	<b>Item no.: 2002-404/000-005</b> Push-in type jumper bar; insulated; 4-way; Nominal current 25 A	2002-404 /000-005
	<b>Item no.: 2002-404/000-006</b> Push-in type jumper bar; insulated; 4-way; Nominal current 25 A	2002-404 /000-006
	<b>Item no.: 2002-405</b> Push-in type jumper bar; insulated; 5-way; Nominal current 25 A	2002-405
	<b>Item no.: 2002-405/000-005</b> Push-in type jumper bar; insulated; 5-way; Nominal current 25 A	2002-405 /000-005
	<b>Item no.: 2002-405/000-006</b> Push-in type jumper bar; insulated; 5-way; Nominal current 25 A	2002-405 /000-006
	<b>Item no.: 2002-405/011-000</b> Star point jumper; insulated; 3-way (1-3-5); IN = IN terminal block	2002-405 /011-000
	<b>Item no.: 2002-406</b> Push-in type jumper bar; insulated; 6-way; Nominal current 25 A	2002-406
	<b>Item no.: 2002-406/000-005</b> Push-in type jumper bar; insulated; 6-way; Nominal current 25 A	2002-406 /000-005
	<b>Item no.: 2002-406/000-006</b> Push-in type jumper bar; insulated; 6-way; Nominal current 25 A	2002-406 /000-006
	<b>Item no.: 2002-406/020-000</b> Delta jumper; insulated; 1-2 3-4 5-6; IN = IN terminal block	2002-406 /020-000
	<b>Item no.: 2002-407</b> Push-in type jumper bar; insulated; 7-way; Nominal current 25 A	2002-407
	<b>Item no.: 2002-407/000-005</b> Push-in type jumper bar; insulated; 7-way; Nominal current 25 A	2002-407 /000-005
	<b>Item no.: 2002-407/000-006</b> Push-in type jumper bar; insulated; 7-way; Nominal current 25 A	2002-407 /000-006













	<b>Item no.: 2022-408</b> Push-in type jumper bar; insulated; 8-way; Nominal current 25 A	2022-408
	<b>Item no.: 2022-408/000-005</b> Push-in type jumper bar; insulated; 8-way; Nominal current 25 A	2022-408 /000-005
	<b>Item no.: 2022-408/000-006</b> Push-in type jumper bar; insulated; 8-way; Nominal current 25 A	2022-408 /000-006
	<b>Item no.: 2022-409</b> Push-in type jumper bar; insulated; 9-way; Nominal current 25 A	2022-409
	<b>Item no.: 2022-409/000-005</b> Push-in type jumper bar; insulated; 9-way; Nominal current 25 A	2022-409 /000-005
	<b>Item no.: 2022-409/000-006</b> Push-in type jumper bar; insulated; 9-way; Nominal current 25 A	2022-409 /000-006
	<b>Item no.: 2022-410</b> Push-in type jumper bar; insulated; 10-way; Nominal current 25 A	2022-410
	<b>Item no.: 2022-410/000-005</b> Push-in type jumper bar; insulated; 10-way; Nominal current 25 A	2022-410 /000-005
	<b>Item no.: 2022-410/000-006</b> Push-in type jumper bar; insulated; 10-way; Nominal current 25 A	2022-410 /000-006
	<b>Item no.: 2022-423</b> Adjacent jumper for continuous commoning; insulated; from 1 to 3; Nominal current 25 A	2022-423
	<b>Item no.: 2022-423/000-005</b> Adjacent jumper for continuous commoning; insulated; from 1 to 3; Nominal current 25 A	2022-423 /000-005
	<b>Item no.: 2022-423/000-006</b> Adjacent jumper for continuous commoning; insulated; from 1 to 3; Nominal current 25 A	2022-423 /000-006
	<b>Item no.: 2022-433</b> Push-in type jumper bar; insulated; from 1 to 3; Nominal current 25 A	2022-433
	<b>Item no.: 2022-434</b> Push-in type jumper bar; insulated; from 1 to 4; Nominal current 25 A	2022-434
	<b>Item no.: 2022-435</b> Push-in type jumper bar; insulated; from 1 to 5; Nominal current 25 A	2022-435
	<b>Item no.: 2022-436</b> Push-in type jumper bar; insulated; from 1 to 6; Nominal current 25 A	2022-436
	<b>Item no.: 2022-437</b> Push-in type jumper bar; insulated; from 1 to 7; Nominal current 25 A	2022-437













	<b>Item no.: 2002-438</b> Push-in type jumper bar; insulated; from 1 to 8; Nominal current 25 A	2002-438
	<b>Item no.: 2002-439</b> Push-in type jumper bar; insulated; from 1 to 9; Nominal current 25 A	2002-439
	<b>Item no.: 2002-440</b> Push-in type jumper bar; insulated; from 1 to 10; Nominal current 25 A	2002-440
	<b>Item no.: 2002-472</b> Staggered jumper; insulated; 2-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-472
	<b>Item no.: 2002-473</b> Staggered jumper; insulated; 3-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-473
	<b>Item no.: 2002-473/011-000</b> Ready-made staggered jumper; insulated; 2-way (1-3); Nominal current 25 A; with contact lugs broken off at the factory and circuit marking	2002-473 /011-000
	<b>Item no.: 2002-474</b> Staggered jumper; insulated; 4-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-474
	<b>Item no.: 2002-475</b> Staggered jumper; insulated; 5-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-475
	<b>Item no.: 2002-475/011-000</b> Ready-made staggered jumper; insulated; 3-way (1-3-5); Nominal current 25 A; with contact lugs broken off at the factory and circuit marking	2002-475 /011-000
	<b>Item no.: 2002-476</b> Staggered jumper; insulated; 6-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-476
	<b>Item no.: 2002-477</b> Staggered jumper; insulated; 7-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-477
	<b>Item no.: 2002-477/011-000</b> Ready-made staggered jumper; insulated; 1-3-5-7; Nominal current 25 A; with contact lugs broken off at the factory and circuit marking	2002-477 /011-000
	<b>Item no.: 2002-478</b> Staggered jumper; insulated; 8-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-478
	<b>Item no.: 2002-479</b> Staggered jumper; insulated; 9-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-479
	<b>Item no.: 2002-479/011-000</b> Ready-made staggered jumper; insulated; 1-3-5-7-9; Nominal current 25 A; with contact lugs broken off at the factory and circuit marking	2002-479 /011-000
	<b>Item no.: 2002-480</b> Staggered jumper; insulated; 10-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-480
	<b>Item no.: 2002-481</b> Staggered jumper; insulated; 11-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks	2002-481













	<p><b>Item no.: 2002-481/011-000</b>                  Ready-made staggered jumper; insulated; 1-3-5-7-9-11; Nominal current 25 A; with contact lugs broken off at the factory and circuit marking</p>	2002-481	/011-000
	<p><b>Item no.: 2002-482</b>                  Staggered jumper; insulated; 12-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks</p>	2002-482	
	<p><b>Item no.: 2009-412</b>                  Push-in type wire jumper; insulated; wire length 60 mm; Conductor cross section 1.5 mm<sup>2</sup>; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks</p>	2009-412	
	<p><b>Item no.: 2009-414</b>                  Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm<sup>2</sup>; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks</p>	2009-414	
	<p><b>Item no.: 2009-414/000-005</b>                  Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm<sup>2</sup>; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks</p>	2009-414	/000-005
	<p><b>Item no.: 2009-414/000-006</b>                  Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm<sup>2</sup>; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks</p>	2009-414	/000-006
	<p><b>Item no.: 2009-416</b>                  Push-in type wire jumper; insulated; wire length 250 mm; Conductor cross section 1.5 mm<sup>2</sup>; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks</p>	2009-416	
	<p><b>Item no.: 210-103</b>                  Wire commoning chain; insulated; 50 connections</p>	210-103	
	<p><b>Item no.: 210-123</b>                  Wire commoning chain; insulated; 50 connections</p>	210-123	
<b>tools</b>			
	<p><b>Item no.: 210-720</b>                  Operating tool with partially insulated shaft; Type 2, blade (3.5 x 0.5) mm</p>	210-720	
<b>Coding</b>			
	<p><b>Item no.: 2022-100</b>                  Carrier with 6 coding pins; for coding of female plugs</p>	2022-100	
<b>Female plug</b>			
	<p><b>Item no.: 2022-101</b>                  1-conductor female plug; 2.5 mm<sup>2</sup>; 1-pole</p>	2022-101	
	<p><b>Item no.: 2022-101/000-006</b>                  1-conductor female plug; 1-pole</p>	2022-101	/000-006
	<p><b>Item no.: 2022-101/000-012</b>                  1-conductor female plug; 1-pole</p>	2022-101	/000-012
	<p><b>Item no.: 2022-101/000-016</b>                  1-conductor female plug; 1-pole</p>	2022-101	/000-016
	<p><b>Item no.: 2022-101/122-000</b>                  1-conductor female plug; 1-pole</p>	2022-101	/122-000












	<b>Item no.: 2022-101/122-006</b> 1-conductor female plug; 1-pole	/ 122-006	2022-101
	<b>Item no.: 2022-101/122-016</b> 1-conductor female plug; 1-pole	/ 122-016	2022-101
	<b>Item no.: 2022-101/132-000</b> 1-conductor female plug; Strain relief plate; 1-pole	/ 132-000	2022-101
	<b>Item no.: 2022-101/132-006</b> 1-conductor female plug; Strain relief plate; 1-pole	/ 132-006	2022-101
	<b>Item no.: 2022-101/132-016</b> 1-conductor female plug; Strain relief plate; 1-pole	/ 132-016	2022-101
	<b>Item no.: 2022-101/142-000</b> 1-conductor female plug; Strain relief plate; 1-pole	/ 142-000	2022-101
	<b>Item no.: 2022-101/142-006</b> 1-conductor female plug; Strain relief plate; 1-pole	/ 142-006	2022-101
	<b>Item no.: 2022-101/142-016</b> 1-conductor female plug; Strain relief plate; 1-pole	/ 142-016	2022-101
	<b>Item no.: 2022-102</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 2-pole		2022-102
	<b>Item no.: 2022-102/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 2-pole	/ 000-006	2022-102
	<b>Item no.: 2022-102/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 2-pole	/ 000-012	2022-102
	<b>Item no.: 2022-102/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 2-pole	/ 000-016	2022-102
	<b>Item no.: 2022-102/122-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 2-pole	/ 122-000	2022-102
	<b>Item no.: 2022-102/132-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 2-pole	/ 132-000	2022-102
	<b>Item no.: 2022-102/142-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 2-pole	/ 142-000	2022-102











	<b>Item no.: 2022-103</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole		2022-103
	<b>Item no.: 2022-103/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole	/000-006	2022-103
	<b>Item no.: 2022-103/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole	/000-012	2022-103
	<b>Item no.: 2022-103/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole	/000-016	2022-103
	<b>Item no.: 2022-103/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole	/000-036	2022-103
	<b>Item no.: 2022-103/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole	/000-037	2022-103
	<b>Item no.: 2022-103/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole	/000-038	2022-103
	<b>Item no.: 2022-103/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 3-pole	/000-039	2022-103
	<b>Item no.: 2022-103/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 3-pole	/123-000	2022-103
	<b>Item no.: 2022-103/133-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 3-pole	/133-000	2022-103
	<b>Item no.: 2022-103/143-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 3-pole	/143-000	2022-103
	<b>Item no.: 2022-104</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole		2022-104
	<b>Item no.: 2022-104/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole	/000-006	2022-104
	<b>Item no.: 2022-104/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole	/000-012	2022-104
	<b>Item no.: 2022-104/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole	/000-016	2022-104













	<b>Item no.: 2022-104/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole	/000-036	2022-104
	<b>Item no.: 2022-104/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole	/000-037	2022-104
	<b>Item no.: 2022-104/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole	/000-038	2022-104
	<b>Item no.: 2022-104/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 4-pole	/000-039	2022-104
	<b>Item no.: 2022-104/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 4-pole	/123-000	2022-104
	<b>Item no.: 2022-104/133-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 4-pole	/133-000	2022-104
	<b>Item no.: 2022-104/143-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 4-pole	/143-000	2022-104
	<b>Item no.: 2022-105</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole		2022-105
	<b>Item no.: 2022-105/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole	/000-006	2022-105
	<b>Item no.: 2022-105/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole	/000-012	2022-105
	<b>Item no.: 2022-105/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole	/000-016	2022-105
	<b>Item no.: 2022-105/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole	/000-036	2022-105
	<b>Item no.: 2022-105/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole	/000-037	2022-105
	<b>Item no.: 2022-105/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole	/000-038	2022-105
	<b>Item no.: 2022-105/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 5-pole	/000-039	2022-105











	<b>Item no.: 2022-105/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 5-pole	/ 123-000	2022-105
	<b>Item no.: 2022-105/134-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 5-pole	/ 134-000	2022-105
	<b>Item no.: 2022-105/144-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 5-pole	/ 144-000	2022-105
	<b>Item no.: 2022-106</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole		2022-106
	<b>Item no.: 2022-106/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole	/000-006	2022-106
	<b>Item no.: 2022-106/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole	/000-012	2022-106
	<b>Item no.: 2022-106/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole	/000-016	2022-106
	<b>Item no.: 2022-106/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole	/000-036	2022-106
	<b>Item no.: 2022-106/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole	/000-037	2022-106
	<b>Item no.: 2022-106/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole	/000-038	2022-106
	<b>Item no.: 2022-106/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 6-pole	/000-039	2022-106
	<b>Item no.: 2022-106/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 6-pole	/ 123-000	2022-106
	<b>Item no.: 2022-106/134-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 6-pole	/ 134-000	2022-106
	<b>Item no.: 2022-106/144-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 6-pole	/ 144-000	2022-106
	<b>Item no.: 2022-107</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole		2022-107












	<b>Item no.: 2022-107/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole	/000-006	2022-107
	<b>Item no.: 2022-107/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole	/000-012	2022-107
	<b>Item no.: 2022-107/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole	/000-016	2022-107
	<b>Item no.: 2022-107/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole	/000-036	2022-107
	<b>Item no.: 2022-107/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole	/000-037	2022-107
	<b>Item no.: 2022-107/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole	/000-038	2022-107
	<b>Item no.: 2022-107/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 7-pole	/000-039	2022-107
	<b>Item no.: 2022-107/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 7-pole	/123-000	2022-107
	<b>Item no.: 2022-107/135-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 7-pole	/135-000	2022-107
	<b>Item no.: 2022-107/145-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 7-pole	/145-000	2022-107
	<b>Item no.: 2022-108</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole		2022-108
	<b>Item no.: 2022-108/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole	/000-006	2022-108
	<b>Item no.: 2022-108/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole	/000-012	2022-108
	<b>Item no.: 2022-108/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole	/000-016	2022-108
	<b>Item no.: 2022-108/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole	/000-036	2022-108














	<b>Item no.: 2022-108/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole	/000-037	2022-108
	<b>Item no.: 2022-108/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole	/000-038	2022-108
	<b>Item no.: 2022-108/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 8-pole	/000-039	2022-108
	<b>Item no.: 2022-108/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 8-pole	/123-000	2022-108
	<b>Item no.: 2022-108/135-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 8-pole	/135-000	2022-108
	<b>Item no.: 2022-108/145-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 8-pole	/145-000	2022-108
	<b>Item no.: 2022-109</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole		2022-109
	<b>Item no.: 2022-109/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole	/000-006	2022-109
	<b>Item no.: 2022-109/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole	/000-012	2022-109
	<b>Item no.: 2022-109/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole	/000-016	2022-109
	<b>Item no.: 2022-109/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole	/000-036	2022-109
	<b>Item no.: 2022-109/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole	/000-037	2022-109
	<b>Item no.: 2022-109/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole	/000-038	2022-109
	<b>Item no.: 2022-109/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 9-pole	/000-039	2022-109
	<b>Item no.: 2022-109/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 9-pole	/123-000	2022-109






	<b>Item no.: 2022-109/135-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 9-pole	/ 135-000	2022-109
	<b>Item no.: 2022-109/145-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 9-pole	/ 145-000	2022-109
	<b>Item no.: 2022-110</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole		2022-110
	<b>Item no.: 2022-110/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole	/000-006	2022-110
	<b>Item no.: 2022-110/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole	/000-012	2022-110
	<b>Item no.: 2022-110/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole	/000-016	2022-110
	<b>Item no.: 2022-110/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole	/000-036	2022-110
	<b>Item no.: 2022-110/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole	/000-037	2022-110
	<b>Item no.: 2022-110/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole	/000-038	2022-110
	<b>Item no.: 2022-110/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 10-pole	/000-039	2022-110
	<b>Item no.: 2022-110/123-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 10-pole	/ 123-000	2022-110
	<b>Item no.: 2022-110/135-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 10-pole	/ 135-000	2022-110
	<b>Item no.: 2022-110/145-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 10-pole	/ 145-000	2022-110
	<b>Item no.: 2022-111</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole		2022-111
	<b>Item no.: 2022-111/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole	/000-006	2022-111

	<b>Item no.: 2022-111/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole	/000-012	2022-111
	<b>Item no.: 2022-111/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole	/000-016	2022-111
	<b>Item no.: 2022-111/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole	/000-036	2022-111
	<b>Item no.: 2022-111/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole	/000-037	2022-111
	<b>Item no.: 2022-111/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole	/000-038	2022-111
	<b>Item no.: 2022-111/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 11-pole	/000-039	2022-111
	<b>Item no.: 2022-111/126-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 11-pole	/126-000	2022-111
	<b>Item no.: 2022-111/136-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 11-pole	/136-000	2022-111
	<b>Item no.: 2022-111/146-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 11-pole	/146-000	2022-111
	<b>Item no.: 2022-112</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole		2022-112
	<b>Item no.: 2022-112/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole	/000-006	2022-112
	<b>Item no.: 2022-112/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole	/000-012	2022-112
	<b>Item no.: 2022-112/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole	/000-016	2022-112
	<b>Item no.: 2022-112/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole	/000-036	2022-112
	<b>Item no.: 2022-112/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole	/000-037	2022-112

	<b>Item no.: 2022-112/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole	/000-038	2022-112
	<b>Item no.: 2022-112/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 12-pole	/000-039	2022-112
	<b>Item no.: 2022-112/126-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 12-pole	/126-000	2022-112
	<b>Item no.: 2022-112/136-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 12-pole	/136-000	2022-112
	<b>Item no.: 2022-112/146-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 12-pole	/146-000	2022-112
	<b>Item no.: 2022-113</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole		2022-113
	<b>Item no.: 2022-113/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole	/000-006	2022-113
	<b>Item no.: 2022-113/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole	/000-012	2022-113
	<b>Item no.: 2022-113/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole	/000-016	2022-113
	<b>Item no.: 2022-113/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole	/000-036	2022-113
	<b>Item no.: 2022-113/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole	/000-037	2022-113
	<b>Item no.: 2022-113/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole	/000-038	2022-113
	<b>Item no.: 2022-113/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 13-pole	/000-039	2022-113
	<b>Item no.: 2022-113/126-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 13-pole	/126-000	2022-113
	<b>Item no.: 2022-113/136-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 13-pole	/136-000	2022-113

	<b>Item no.: 2022-113/146-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 13-pole	/ 146-000	2022-113
	<b>Item no.: 2022-114</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole		2022-114
	<b>Item no.: 2022-114/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole	/ 000-006	2022-114
	<b>Item no.: 2022-114/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole	/ 000-012	2022-114
	<b>Item no.: 2022-114/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole	/ 000-016	2022-114
	<b>Item no.: 2022-114/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole	/ 000-036	2022-114
	<b>Item no.: 2022-114/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole	/ 000-037	2022-114
	<b>Item no.: 2022-114/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole	/ 000-038	2022-114
	<b>Item no.: 2022-114/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 14-pole	/ 000-039	2022-114
	<b>Item no.: 2022-114/126-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 14-pole	/ 126-000	2022-114
	<b>Item no.: 2022-114/136-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 14-pole	/ 136-000	2022-114
	<b>Item no.: 2022-114/146-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 14-pole	/ 146-000	2022-114
	<b>Item no.: 2022-115</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole		2022-115
	<b>Item no.: 2022-115/000-006</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole	/ 000-006	2022-115
	<b>Item no.: 2022-115/000-012</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole	/ 000-012	2022-115

	<b>Item no.: 2022-115/000-016</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /000-016
	<b>Item no.: 2022-115/000-036</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /000-036
	<b>Item no.: 2022-115/000-037</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /000-037
	<b>Item no.: 2022-115/000-038</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /000-038
	<b>Item no.: 2022-115/000-039</b> 1-conductor female plug; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /000-039
	<b>Item no.: 2022-115/127-000</b> 1-conductor female plug; Locking lever; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /127-000
	<b>Item no.: 2022-115/137-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /137-000
	<b>Item no.: 2022-115/147-000</b> 1-conductor female plug; Strain relief plate; 2.5 mm <sup>2</sup> ; 15-pole	2022-115 /147-000
<b>Protective Warning Marker</b>		
	<b>Item no.: 2002-115</b> Protective warning marker; with high-voltage symbol, black; for 5 terminal blocks	2002-115
<b>General accessories</b>		
	<b>Item no.: 2022-161</b> Start module for 1-conductor female connector; with integrated end plate; 2.5 mm <sup>2</sup> ; 1-pole	2022-161
	<b>Item no.: 2022-162</b> Start module for 1-conductor female connector; with integrated end plate; 2.5 mm <sup>2</sup> ; 1-pole	2022-162
	<b>Item no.: 2022-164</b> Start module for 1-conductor female connector; with integrated end plate; 2.5 mm <sup>2</sup> ; 1-pole	2022-164
	<b>Item no.: 2022-167</b> Start module for 1-conductor female connector; with integrated end plate; 2.5 mm <sup>2</sup> ; 1-pole	2022-167
	<b>Item no.: 2022-171</b> Center module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-171
	<b>Item no.: 2022-172</b> Center module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-172
	<b>Item no.: 2022-174</b> Center module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-174
	<b>Item no.: 2022-177</b>	

	Center module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-177
	<b>Item no.: 2022-181</b> End module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-181
	<b>Item no.: 2022-182</b> End module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-182
	<b>Item no.: 2022-184</b> End module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-184
	<b>Item no.: 2022-187</b> End module for 1-conductor female connector; 2.5 mm <sup>2</sup> ; 1-pole	2022-187

Downloads

Documentation

Bid Text

2022-1207	docx 15.5 kB	Download
-----------	-----------------	----------

Additional Information

	pdf 2.1 MB	Download
--	---------------	----------

CAD/CAE - Smart Data

CAD data

3D Download 2022-1207	URL	Download
-----------------------	-----	----------

Product family

**X-COM S**  
[Show all products from the family](#)

Subject to changes.