Hart lock industrial grade 20A locking devices



Receptacle **Plug**

Product description

4-pole, 4-wire non-grounding
20A, 3ØY 120/208V/AC
Non-NEMA

7411C



7413C



7410B



7400N

Industrial grade plugs & connectors

Rating A	Rating V/AC	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
20	120/208	3ØY safety grip straight body	0.63-1.16" (15.9-29.4mm)	GY	☐ 7411C	☐ 7413C*	•	•

*Not NOM cert

Industrial grade receptacles

Rating A	Rating V/AC	Description	Color	Single receptacle	
20	120/208	3ØY standard industrial	BK	☐ 7410B	•

Industrial grade flanged inlets & outlets

Rating A	Rating V/AC	Description	Color	Flanged inlet	Flanged outlet	
20	120/208	3ØY standard industrial	GY	☐ 7408N	☐ 7409N	•

Accessories for non-NEMA 20A locking devices

Description	Catalog no.		
Neoprene weather protective boot for 4-W & 5-W plugs	☐ BL1		•
Neoprene weather protective boot for 4-W & 5-W connectors	☐ BL2		•
Diecast aluminum single receptacle cover, vertical mount, for FS/FD boxes	☐ 7420	•	•
Glass-filled nylon flanged inlet/outlet cover, vertical mount, for 20A devices	☐ WP2	•	•

BL1

BL2

7420

WP2

Dimensional information:
C-76-C-78

Plug & connector specification information:
Safety grip non-NEMA 20A: C-84
Receptacle specification information:
Non-NEMA 20A: C-87
Flanged inlet & flanged outlet specification information:
Non-NEMA 20A: C-89

Color information:

BK (Black), GY (Gray)

BK	GY
(Black)	(Gray)

Compliances, specifications and availability are subject to change without notice.