Straight Blade Devices

Industrial Grade Extra Heavy Duty, Specification Grade Duplex Receptacles

- Nylon construction with Circuit ID marking area
- Heavy duty nickel and brass plated steel wrap-around yoke
- Heavy duty, copper-alloy self-grounding system
- UL Listed, CSA Certified, Complies with NEMA® Standards WD-1 and WD-6, Listed to UL 498, Verified under Federal Specification WC596

The BRY5362 Design

The one-piece ground system provides a more reliable continuity to ground than riveted designs. Triple-wipe brass line contacts deliver excellent conductivity for low resistance, low heat rise. Superior spring properties provide reliable, long-life blade retention. All nylon, wrap-around, full-face design provides secure assembly, even under stress.

15A and 20A 125V and 250V Receptacles, Back and Side Wired

BRY5262

BRY5362IWR

BRY5262IG

BRY5362IGWWR

BRY5262CR

		Duplex			Isolated Ground			Corrosion Resistant
Rating	Color	Standard	Weather Resistant WR	Color	Standard	Weather Resistant WR	Color	Standard
NEMA 5-15, 15A 125V	Black	**BRY5262BLK**	**BRY5262BLKWR**	Brown	**BRY5262IGB**	—	Brown	**BRY5262BCR**
	Blue	**BRY5262BU**	**BRY5262BUWR**	Gray	**BRY5262IGGRY**	**BRY5262IGGRYWR**	Yellow	**BRY5262CR**
	Brown	**BRY5262**	**BRY5262WR**	Ivory	**BRY5262IGI**	**BRY5262IGIWR**		
	Gray	**BRY5262GRY**	**BRY5262GRYWR**	Orange	**BRY5262IG**	**BRY5262IGWR**		
	Ivory	**BRY5262I**	**BRY5262IWR**	White	**BRY5262IGW**	**BRY5262IGWWR**		
	Red	**BRY5262RED**	**BRY5262REDWR**					
	White	**BRY5262W**	**BRY5262WWR**					
NEMA 5-20, 20A 125V	Black	**BRY5362BLK**	**BRY5362BLKWR**	Brown	**BRY5362IGB**	—	Yellow	**BRY5362CR**
	Blue	**BRY5362BU**	**BRY5362BUWR**	Gray	**BRY5362IGGRY**	**BRY5362IGGRYWR**		
	Brown	**BRY5362**	**BRY5362WR**	Ivory	**BRY5362IGI**	**BRY5362IGIWR**		
	Gray	**BRY5362GRY**	**BRY5362GRYWR**	Orange	**BRY5362IG**	**BRY5362IGWR**		
	Ivory	**BRY5362I**	**BRY5362IWR**	White	**BRY5362IGW**	**BRY5362IGWWR**		
	Red	**BRY5362RED**	**BRY5362REDWR**					
	White	**BRY5362W**	**BRY5362WWR**					
NEMA 6-15, 15A 250V	Black	**BRY5662BLK**	—	Orange	**BRY5662IG**	—	Yellow	**BRY5662CR**
	Brown	**BRY5662**	—					
	Gray	**BRY5662GRY**	—					
	Ivory	**BRY5662I**	—					
	Red	**BRY5662RED**	—					
	White	**BRY5662W**	—					
NEMA 6-20, 20A 250V	Black	**BRY5462BLK**	—	Orange	**BRY5462IG**	—	Yellow	**BRY5462CR**
	Brown	**BRY5462**	—					
	Gray	**BRY5462GRY**	—					
	Ivory	**BRY5462I**	—					
	Red	**BRY5462RED**	—					
	White	**BRY5462W**	—					

Note: See page R-6 for weather resistant description. See page A-28 for technical specifications.

See Section C for isolated ground products. See page R-6 for weather resistant description.

See Section I for corrosion-resistant products.

15A and 20A 125V Specialty Receptacles

Inches (mm)

BRY5282

Rating	Description	Color	Catalog Number
NEMA 5-15, 15A 125V	BRY5262 on 4.0" (101.6) round metal box cover	Brown	**BRY5282**
NEMA 5-20, 20A 125V	BRY5362 on 4.0" (101.6) round metal box cover	Brown	**BRY5382**

NEMA® is a registered trademark of the National Electrical Manufacturers Association.

Product Dimensions

Inches (mm)

A	4.06" (103.1)
B	3.28" (83.3)
C	1.54" (39.1)
D	1.16" (29.5)