Straight Blade Devices

Hospital Grade ● QUADPLEX® Receptacles

- Accepts up to four straight or angle plugs
- Heavy duty, triple-wipe, high performance brass line contacts for excellent retention and conductivity
- Break-off tab for two-circuit wiring (except surge)
- Saves wiring and installation time
- "A" and "B" circuits molded into face for easy identification
- Easily removable knockouts for mounting to octagon concrete ring or box

QUADPLEX®

Mounts directly to 4" square or octagon boxes. No cover plate required. Can be retrofitted to 1 and 2-gang device boxes, mud rings on 4" boxes or 4 11/16" boxes using adapter plate. Rugged impact resistant construction. Break-off tabs for split circuit wiring (except surge units).

15A and 20A 125V Receptacles

QUADPLEX®

21254HR

21254HIGO

21254HSA

21254HIL

Wiring		Terminal Screws					Wire leads	
Rating	Color	Standard	Color	Isolated Ground	Color	Surge Suppression Isolated Ground	Color	Standard
NEMA 5-15, 15A 125V	Brown Gray Ivory Red White	**1254HB** **1254HGY** **1254HI** **1254HR** **1254HW**	Orange	—	Blue Ivory	**1254HSA** **1254HSIA**	Brown Ivory	— —
NEMA 5-20, 20A 125V	Brown Gray Ivory Red White	**21254HB** **21254HGY** **21254HI** **21254HR** **21254HW**	Orange	**21254HIGO**	Blue Ivory	**21254HSA** **21254HSIA**	Brown Ivory	**21254HBL** **21254HIL**

Note: See Section C for isolated ground products. See page A-15 for additional information on QUADPLEX® surge receptacles.

Adapter Plates and Portable Boxes

	Adapter Plates		Portable Boxes	
Color	For 1- and 2-Gang Device Boxes	For 4 11/16" Boxes	with Cord Grip	Feed-thru with Two Cord Grips
Black	**ADAPBLK**	—	**4SQBXBLK**	**4SQBXFBLK**
Blue	**ADAPBLU**	—	**4SQBXBLU**	—
Brown	**ADAPB**	—	**4SQBXB**	—
Gray	**ADAPGRY**	—	**4SQBXGRY**	—
Ivory	**ADAPI**	**ADAPIS**	**4SQBXI**	**4SQBXFI**
Orange	**ADAPO**	—	**4SQBXO**	—
Red	**ADAPR**	—	**4SQBXR**	**4SQBXFR**
White	**ADAPW**	—	**4SQBXW**	—

ADAPI

4SQBXI

Product Dimensions Inches (mm)

	Receptacle	Adapter Plate	Portable Box
A	4.30" (109.2)	4.78" (121.4)	4.30" (109.2)
B	3.38" (85.9)	4.25" (108.0)	4.05" (102.9)
C	3.02" (76.7)	3.38" (85.9)	3.28" (85.9)
D	0.92" (23.4)	2.75" (69.9)*	0.84" (21.3)
E	0.10" (2.6)	0.38" (9.5)	0.75" (19.1)
F	–	2.75" (6.9)	–

*Note: *Mounting dimensions for 4 11/16" adapter plate.*



Receptacle



Adapter Plate



Portable Box