Power Rated Raceway Channels

TSRP - Power Rated Surface Raceway

HellermannTyton's TSRP power surface raceway is a one piece, non-metallic, adhesive backed latching raceway designed to aesthetically organize and route either power or communications cables. Completely tamper resistant, the cover's self-locking, hidden positive latch permits quick reentry as well as providing a secure installation of power cables.

Features and Benefits

- Completely tamper resistant, the cover's self-locking, hidden positive latch permits quick re-entry as well as providing a secure installation of power cables.
- U.L. Listed for power up to 600 Volts, meeting UL5A and CSA 22.2 Number 62-93 Standards.
- Manufactured from UL 94V-0 rated PVC material.
- Fittings incorporate a minimum 1" bend radius per TIA/EIA 568-B and 569-A standards.
- Large base for greater adhesive surface.
- Rubber-based foam tape adhesive with high ultimate bond strength, which conforms to any surface.
- Flexible hinge allows the raceway to endure numerous openings without creating discoloration or stress cracking.
- Junction boxes can be used for electrical or data outlets.
- Designed to complement HellermannTyton's industry standard TSR low voltage raceway system.

MATERIAL	Polyvinylchloride (PVC)
Flammability	UL 94 V0
Operating Temperature	+122°F (+50°C)



RoHS

PART NO.	TYPE	Description	Width (W) in. (mm)	Height (H) in. (mm)	Length (L) in. (mm)	Color	Pkg. Qty.
TSRP1I-6A*	**TSRP1-6A**	3/4" One Piece Surface Raceway	0.75 (19.1)	0.5 (12.7)	6.0 ft (1.8)	Ivory	120 ft
TSRP1FW-6A*		3/4" One Piece Surface Raceway	0.75 (19.1)	0.5 (12.7)	6.0 ft (1.8)	Office White	120 ft
TSRP1W-6A*		3/4" One Piece Surface Raceway	0.75 (19.1)	0.5 (12.7)	6.0 ft (1.8)	White	120 ft
TSRP1I-8A*	**TSRP1-8A**	3/4" One Piece Surface Raceway	0.75 (19.1)	0.5 (12.7)	8.0 ft (2.4)	Ivory	160 ft
TSRP1FW-8A*		3/4" One Piece Surface Raceway	0.75 (19.1)	0.5 (12.7)	8.0 ft (2.4)	Office White	160 ft
TSRP1W-8A*		3/4" One Piece Surface Raceway	0.75 (19.1)	0.5 (12.7)	8.0 ft (2.4)	White	160 ft
TSRP2I-6A*	**TSRP2-6A**	1-1/4" One Piece Surface Raceway	1.25 (31.8)	0.8 (19.1)	6.0 ft (1.8)	Ivory	120 ft
TSRP2FW-6A*		1-1/4" One Piece Surface Raceway	1.25 (31.8)	0.8 (19.1)	6.0 ft (1.8)	Office White	120 ft
TSRP2W-6A*		1-1/4" One Piece Surface Raceway	1.25 (31.8)	0.8 (19.1)	6.0 ft (1.8)	White	120 ft
TSRP2I-8A*	**TSRP2-8A**	1-1/4" One Piece Surface Raceway	1.25 (31.8)	0.8 (19.1)	8.0 ft (2.4)	Ivory	160 ft
TSRP2FW-8A*		1-1/4" One Piece Surface Raceway	1.25 (31.8)	0.8 (19.1)	8.0 ft (2.4)	Office White	160 ft
TSRP2W-8A*		1-1/4" One Piece Surface Raceway	1.25 (31.8)	0.8 (19.1)	8.0 ft (2.4)	White	160 ft
TSRP3I-6A*	**TSRP3-6A**	1-3/4" One Piece Surface Raceway	1.75 (44.5)	1.0 (25.4)	6.0 ft (1.8)	Ivory	120 ft
TSRP3FW-6A*		1-3/4" One Piece Surface Raceway	1.75 (44.5)	1.0 (25.4)	6.0 ft (1.8)	Office White	120 ft
TSRP3W-6A*		1-3/4" One Piece Surface Raceway	1.75 (44.5)	1.0 (25.4)	6.0 ft (1.8)	White	120 ft
TSRP3I-8A*	**TSRP3-8A**	1-3/4" One Piece Surface Raceway	1.75 (44.5)	1.0 (25.4)	8.0 ft (2.4)	Ivory	160 ft
TSRP3FW-8A*		1-3/4" One Piece Surface Raceway	1.75 (44.5)	1.0 (25.4)	8.0 ft (2.4)	Office White	160 ft
TSRP3W-8A*		1-3/4" One Piece Surface Raceway	1.75 (44.5)	1.0 (25.4)	8.0 ft (2.4)	White	160 ft

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
*This product meets UL standards. Please see appendix for specific file numbers. For wire fill capacities, see appendix.

Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.