Specification Sheet

Part Number: MCRFW-BS8

InfoStream Multi-Channel Raceway Base With Side Divider, 8 ft Long, PVC, Office White, 48 ft/pkg

Article Number	250-00006
Type	MCR-BS8
Color	Office White (OEWH)
Features & Benefits	• Raceway and fittings are manufactured from a UL94 V0 rated material to insure compliance with codes • All fittings have been designed to maintain the required 1" minimum bend radius to meet TIA/EIA-568-B and 569-A standard • Raceway and fittings are UL Listed to 600 Volts to meet new UL5A and CSA 22.2 No. 62-93 standards • Patented hinged cover speeds installation time by allowing installer to partially mount cover prior to laying cables
Quantity Per	box
Product Description	HellermannTyton's InfoStream non-metallic raceway system can accommodate up to four separate channels of electrical, voice, data, video or fiber optic cabling. The elliptical shape is aesthetically pleasing when compared to other designs. The raceway's unique and patented design make installations quicker and easier.

Short Description	InfoStream Multi-Channel Raceway Base With Side Divider, 8 ft Long, PVC, Office White, 48 ft/pkg
Global Part Name	MCR-BS8-PVC-WH

Length L (Imperial)	8.0
Length L (Metric)	2.44
Width W (Imperial)	4.5
Width W (Metric)	114.3
Height H (Imperial)	2.05
Height H (Metric)	52.07

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V0
Halogen free	No
Operating Temperature (Metric)	+122°F (+50°C)
Reach Complaint(Article 33)	No
ROHS Complaint	Yes

UL Listed (US and Canada)	Yes
UL Listed (US	Yes
Package Quantity(Imperial)	48
Package Quantity (Metric)	14.63
Customs Number	3925900000

© 2019 HellermannTyton. All Rights Reserved.