Part number

# CDMD 1.5



## Brief description:

10A CD contacts, gold plated, 1,50mmq, AWG 16

| Product description | |
|---|---|
| **Model** | male contacts |
| **Version** | Crimp contacts CLASS series |
| **Series** | 10A CD contacts |
| **Family** | crimp contacts |
| **N. of poles** | 1 pole |
| **Technical data** | |
| **Current** | 10 A |
| **Wire cross-section** | 1,50 mm² |
| **AWG size** | 16 |
| **Operating temperature range (min, max)** | -40°C … +125°C |
| **Contact type** | gold plated |
| **Further technical details** | |
| **Weight** | 0,80 g |

| Approvals / Standards | |
|---|---|
| **Quality mark** | , EAC |
| **Conformity** | CQC, CE |
| **General ordering information** | |
| **EAN13 code** | 8015747015646 |
| **Tariff number** | 85369095 |
| **Packaging Information** | |
| **Packaging length** | 112,00 mm |
| **Packaging height** | 95,00 mm |
| **Packaging width** | 117,00 mm |
| **Packaging weight** | 1,28 kg |
| **Packaging volume** | 1,24 dm³ |
| **Packaging description** | Carton box |
| **Packaging quantity** | 1600 Pcs |
| **Packaging EAN code** | 8015747207010 |
| **Sub-packaging length** | 50,00 mm |
| **Sub-packaging height** | 44,00 mm |
| **Sub-packaging width** | 50,00 mm |
| **Sub-packaging weight** | 0,16 kg |
| **Sub-packaging volume** | 0,11 dm³ |
| **Sub-packaging description** | Plastic box |
| **Sub-packaging quantity** | 200 Pcs |
| **Sub-packaging EAN barcode** | 8015747015653 |

Part number

# CDMD 1.5

Catalogue drawings

**CDM**







**CDF**