Part number

MHV 24 L40

Brief description:

hoods for single lever, size "104.27", top entry, M40, metal version, IP66

Product description	
Version	metal version
Series	hoods for single lever
Product type	with 2 pegs
Variant	top entry
Family	CLASS enclosures
Size	size "104.27"
Technical data	
Material	metal
IP degree of protection	IP66 (and IP69K DIN 40050 - 9)
Cable entry	M40
Further technical details	
Weight	180,00 g

Approvals / Standards	
Quality mark	(type:4/4X/12), , EAC
Conformity	CQC, CE
General ordering information	
EAN13 code	8015747056052
Tariff number	85369095
Packaging Information	
Sub-packaging weight	0,90 kg
Sub-packaging description	Plastic pakaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747106016