# CONDUIT BODIES • COVERS • GASKETS

**Form 7 Steel & Gray Iron Conduit Body Covers & Neoprene Gaskets** **COMING SEPTEMBER 2016**

E208392

## Applications

To cover conduit body opening

## Features

- Raised dome affords additional wiring room
- Captive steel screws

## Standard Materials

Steel cover & clips
Stainless Steel screws
Gray iron
Neoprene rubber

## Applicable Third Party Standards

- UL Standard: 514A
- Fed. Spec. W-C-586D
- NEMA: FB-1
- UL Listed File # E208392




**Cover and Gasket**




**Gray Iron Cast Cover**

Cover and Gasket

| CATALOG NUMBER | TRADE SIZE | DIM A | DIM B | DIM C | MASTER PACK | WEIGHT PER C |
|---|---|---|---|---|---|---|
| 170-CGKON | 1/2" | 3.688 | 1.375 | 0.250 | 25 | 14.7 |
| 270-CGKON | 3/4" | 4.313 | 1.563 | 0.250 | 25 | 18.4 |
| 370-CGKON | 1" | 5.063 | 1.938 | 0.250 | 20 | 25.7 |
| 470-CGKON | 1-1/4" | 5.563 | 2.250 | 0.250 | 10 | 32.8 |
| 570-CGKON | 1-1/2" | 6.063 | 2.500 | 0.250 | 10 | 38.6 |
| 670-CGKON | 2" | 7.063 | 3.063 | 0.250 | 10 | 53.0 |
| 870-CGKON | 2-1/2" – 3" | 9.063 | 4.250 | 0.500 | 5 | 107.0 |
| 970-CGKON | 3-1/2" – 4" | 11.063 | 5.313 | 0.500 | 5 | 170.2 |

Gray Iron Cast Cover

| CATALOG NUMBER | TRADE SIZE | DIM A | DIM B | DIM C | MASTER PACK | WEIGHT PER C |
|---|---|---|---|---|---|---|
| 170F-CGKON | 1/2" | 3.688 | 1.313 | 0.375 | 20 | 29.9 |
| 270F-CGKON | 3/4" | 4.313 | 1.500 | 0.375 | 20 | 34.7 |
| 370F-CGKON | 1" | 5.063 | 1.750 | 0.500 | 10 | 57.6 |
| 470F-CGKON | 1-1/4" | 5.500 | 2.188 | 0.500 | 5 | 71.7 |
| 570F-CGKON | 1-1/2" | 6.063 | 2.438 | 0.563 | 5 | 96.4 |
| 670F-CGKON | 2" | 7.063 | 3.000 | 0.563 | 5 | 126.9 |
| 870F-CGKON | 2-1/2" – 3" | 8.750 | 4.250 | 0.563 | 5 | 213.0 |
| 970F-CGKON | 3-1/2" – 4" | 11.000 | 5.063 | 0.563 | 5 | 323.4 |