7/8” MIN Series Size I Cordsets

5 & 6 Conductor MIN Series Size I Cordsets, 18AWG

Right Angle Male Cordsets | 300 Volt, 5.5 amps | IP67 Rating

c UL us LISTED

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MIN-5MPX-*-R (YELLOW) MIN-5MPX-*-R-B (BLACK)	PVC AWM **5 X 18 AWG** 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	**North American** 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black	 7/8”-16UN2
	MINP-5MPX-*-R	Yellow PUR AWM **5 X 18 AWG** 300V, 5.5A -40°C to +80°C 7.4mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MIN-5MPX-*A-R (YELLOW) MIN-5MPX-*A-R-B (BLACK)	Yellow PVC AWM **5 X 18 AWG** 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC	**North American** **Auto Color Code** 1. Red/White 2. Red 3. Green/Yellow 4. Red/Yellow 5. Red/Black	
	MINE-5MPX-**-R	Yellow PVC AWM **5 X 18 AWG** 300V, 5.5A -40°C to +105°C 7.4mm OD	Industry Standard PVC Male Threaded Coupling Nut	**European** 1. Black 2. Blue 3. Green/Yellow 4. Brown 5. White	 7/8”-16UN2
	MIN-6MPX-*-R	Yellow PVC SJTOOW **6 X 18 AWG** 300V, 5.5A -40°C to +105°C 10.1mm OD	Industry Standard PVC	**North American** 1. White 2. Red 3. Green/Yellow 4. Orange 5. Black 6. Blue	 7/8”-16UN2
	MINP-6MPX-*-R	Yellow PUR AWM **6 X 18 AWG** 300V, 5.5A -40°C to +80°C 8.5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MINE-6MPX-**-R	Yellow PVC SJTOOW **6 X 18 AWG** 300V, 5.5A -40°C to +105°C 10.1mm OD	Industry Standard PVC Male Threaded Coupling Nut	**European** 1. Green 2. White 3. Blue 4. Gray 5. Yellow 6. Brown	 7/8”-16UN2

* Lengths in feet. Standard cable lengths are 3, 6, 12, 20, 30 & 50 feet. Consult factory for other lengths.
** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.
Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a “-SS” suffix. (e.g. MIN-5MPX-3-R becomes MIN-5MPX-3-R-SS)
For male threaded coupling replace “MPX” with “MPMX”. (e.g. MIN-5MPX-3-R becomes MIN-5MPMX-3-R)
See Page A-33 for Armored Cordset options.