MURR ELEKTRONIK
stay connected

MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 230/400+/-15VAC OUT: :24V/1ADC

Current: 1 A
Output rating: 24 W
with MES DIN-rail adapter
This power supply units meet the (EN 61000-3-2) standard for harmonic current.

Link to Product

Illustration

Product may differ from Image

Approvals

Input

Input voltage	230/400 ±15 V AC
Input current	0.25 A (230 V AC); 145 A (400 V AC)
Input fuse (external)	0.4 A (T) (230 V AC); 0.25 A (T) (400 V AC)
Frequency	50...60 Hz

Output

Output voltage	24 V DC (SELV)
Output current (Ta 60/40 °C)	max. 1 A (230 V AC); 1.5 A (400 V AC)
Ripple	max. 5% eff/rms
Output fuse	3 A (automotive fuse FKS)
Output suppression	LED, VDR and smoothing capacitor

General data

Standards	EN 61558-2-6, EN 62041 category I, EN 55011 B, EN 61000-3-2
Mounting method	DIN-rail mountable TH35-15 (EN 60715) or for key-hole mounting
Dimensions H×W×D	64×78×120 mm
Fixing centers a×b×c	47.5×56×4.8 mm
Temperature range	-20...+60 °C, no condensation

The information in this brochure has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 11/20

MURR ELEKTRONIK
stay connected

Commercial data	
country of origin	CZ
customs tariff number	85044090
EAN	4048879065757
eClass	27049002
Packaging unit	1

Sketch





Product may differ from Image

The information in this brochure has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 11/20