Catalog Number:	**LTZUS08B-A**
Product ID:	7TAA012LT0R0007
UPC Number:	78621011620
EAN Number:	05415022394580
Status:	A

Representative

Liquid Tight Flexible Metallic Conduit, Galvanised Steel Core with PVC Jacket, Conduit Size 2-1/2 Inch, Length 8 Meters/25 Feet, Halogen Free, UL 360, CSA, Compliant to RoHS, Working Temperature -40 to 80 Degrees C, Black

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Type	Liquid Tight Flexible Metallic Conduit
Standard	UL 360, CSA, RoHS
Trade Size	2-1/2 in ; 70 mm
Outside Diameter	2.875 in
Inside Diameter	2.480 in
Length	25 ft ; 8 m
Material	Galvanized Steel Core
Finish	PVC Jacket
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	70mm
Nominal size in inch	2 1/2 inch
Outer diameter	73.03mm
Inner diameter	62.99mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-40-+80°C
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	25
Outer Dimensions (inches)	33.62x37x10.38
Weight Uom	1.92 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000010
Technical Drawing / Data Sheet	TDS000117
Catalog US	Available on Website