Catalog Number:	**MLP750-6-A**
Product ID:	7TCA017310R0319
UPC Number:	78621081702
EAN Number:	05414363105619
Status:	A

Actual

Heat Shrink Tubing, Flexible for High Specifications, UL/CSA Listed, Thin Wall, Shrink Ratio 2:1, 3/4 Inch/19.1mm Expanded Diameter, Blue, 10 X 1.22M Lengths

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Shrink Ratio	2:1
Thickness	Thin
Length	4 ft ; 1.22 m
Continuous Operating Temperature	-67 to +212 F ; -55 to +100 C
Minimum Shrink Temperature	194 F ; 90 C
Flammability	Flame Retardant
Color	Blue

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	19.1mm
Inner diameter after heat-shrink	9.5mm
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	0.8mm
Length	1.22m
Operation temperature	-55-+135°C
Colour	Blue
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	10
Outer Dimensions (inches)	49.3x1.9x1.8
Weight Uom	9.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001470
Safety Data Sheet (SDS) Global	SDS-00046-TB2