Not for usage in European Market

Power Extension Cord, Locking C19 to C20 - Heavy Duty, 20A, 100-250V, 12 AWG, 6 ft., Black

MODEL NUMBER: **P036-L06**

C20 to C19 cord powers a server, router, switch, blade server enclosure or other network device that requires a heavy-gauge cable.

Features

C20 to C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection This rugged cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a server, router, switch, blade server enclosure or other network device to a UPS system or PDU. It is also an ideal replacement or upgrade from the standard power cord provided by the device's manufacturer. The six-foot length allows you flexibility in placing equipment with respect to the power outlet.
Locking C19 Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C19 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.
Lifetime Warranty The P036-L06 is backed by a lifetime warranty, ensuring reliability and performance.

Highlights

- Recommended for powering network devices that require heavy-gauge cabling
- 6 ft. length allows flexibility in placing devices in relationship to AC outlet
- Reliable replacement or upgrade from standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking C19 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like servers, routers and network switches to a UPS system up to 6 ft. away in your data center
- Extend an existing power connection up to 6 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P036-L06 C20 to C19 Power Cable, Locking C19 Connector, 6 ft., Black

Specifications

OVERVIEW	
UPC Code	037332218315
Country/Region	North America
INPUT	
Maximum Input Amps	20
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	32.51 x 21.82 x 1.27
Shipping Dimensions (hwd / in.)	12.80 x 8.59 x 0.50
Shipping Weight (kg)	0.44
Shipping Weight (lbs.)	0.98
Wire Gauge (AWG)	12
Wire Gauge (OD - mm^2)	3.31
ENVIRONMENTAL	
Operating Temperature Range	-4 to 221 F (-20 to 105 C)
Storage Temperature Range	-4 to 221 F (-20 to 105 C)
Relative Humidity	0-65% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19 - LOCKING
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	Yes
STANDARDS & COMPLIANCE	
Certifications	UL Listed

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.
Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
https:/ products/product-certification-agencies