



Representative

**Catalog Number:** AL13/U075/A/000620  
**Product ID:** 7TCA296000R0278  
**EAN Number:** 05020963008665  
**Status:** Active

Connector Conduit Fitting, Straight, Conduit Size 13, 3/4 Inch Connector UNEF Thread, Swivel Internal Thread, Black

## North American Specifications (UNSPSC)

|             |                                                                    |
|-------------|--------------------------------------------------------------------|
| UNSPSC      | 39121311 Electrical fittings                                       |
| IGCC        | 4441 Electrical fittings                                           |
| Brand Name  | Adaptaflex                                                         |
| Type        | Conduit Fitting with UNEF Threads                                  |
| Application | For Insertion into Threaded Entries or Knockout to Connect Conduit |
| Size        | NC 13mm                                                            |
| Material    | Polyamide/Nylon 6.6                                                |
| Color       | Black                                                              |
| Connection  | Straight                                                           |
| Cable Entry | 3/4 Inch UNEF Thread                                               |

## European Specifications (ETIM)

|                                                                 |                                                       |
|-----------------------------------------------------------------|-------------------------------------------------------|
| ETIM                                                            | EC001176 Screw connection for corrugated plastic hose |
| Nominal diameter                                                | 13mm                                                  |
| Degree of protection (IP)                                       | IP68                                                  |
| Model                                                           | Straight                                              |
| Revolving thread                                                | Y                                                     |
| Construction type                                               | Internal thread                                       |
| Type of connection                                              | Snap connection                                       |
| Thread type                                                     | UNEF                                                  |
| Thread connection size                                          | Other                                                 |
| Thread length                                                   | 9.5mm                                                 |
| Total length                                                    | 23.6mm                                                |
| Total height                                                    | 50.2mm                                                |
| Material                                                        | Polyamide                                             |
| Colour                                                          | Black                                                 |
| Approved in combination with protective conduit UR              | N                                                     |
| Approved in combination with protective conduit DIN EN 61386-23 | Y                                                     |

## Packaging

|                           |                |
|---------------------------|----------------|
| Outer Quantity            | 10             |
| Outer Dimensions (inches) | 1x1x1          |
| Weight Uom                | 0.03 lbs. Each |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)