

Complex environment straight blade devices

Product description

2-pole, 3-wire grounding
15A, 125V/AC
NEMA 5-15



5-15P



5-15R

Plugs & connectors



Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
15	125	5-15	Watertight	0.30-0.65" (7.6-16.5mm)	Y	□ 14W47*	□ 15W47*	•	•
			Watertight	0.30-0.65" (7.6-16.5mm)	BK	□ 14W47BK*	□ 15W47BK*	•	•
			Severe duty	0.38-1.00" (19.1-25.4mm)	Y & BK	□ 1447*	□ 1547*	•	•
			Quick grip corrosion resistant	0.22-0.66" (5.6-16.8mm)	Y	□ AH5965CR	□ AH5969CR	•	•
			Auto grip corrosion resistant	0.33-0.66" (6.4-16.7mm)	Y	□ 5266NCR	□ 5269NCR	•	•

* Not Fed Spec


Receptacles, back & side wire



Rating A	V/AC	NEMA	Description	Color	Single receptacle catalog no.	Duplex receptacle catalog no.		
15	125	5-15	Watertight	Y	□ 60W47	□ 60W47DPLX	•	•
			Watertight	BK	□ 60W47BK	□ 60W47DPLXBK	•	•
			Corrosion resistant	Y	--	□ AH5262CRY	•	•
			Corrosion resistant	GY	--	□ AH5262CRGY	•	•
		5-15/ L5-15	Corrosion resistant combination locking & straight blade	Y	--	□ CR5792	•	•

Accessories for watertight 15/20A plugs & connectors


Description	Cord diameter	Catalog no.		
Watertight plug closure cap for 15A plug, yellow		□ 14W	•	•
Watertight plug closure cap for 15A plug, black		□ 14WBK	•	•
Replacement watertight connector closure cap for 15A connector, yellow		□ 15W	•	•
Replacement watertight connector closure cap for 15A connector, black		□ 15WBK	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.31-0.37" (7.9-9.5mm)	□ WTM131	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.38-0.44" (9.5-11.1mm)	□ WTM138	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.43-0.50" (10.9-12.7mm)	□ WTM143	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.50-0.56" (12.7-14.3mm)	□ WTM150	•	•
Wire mesh grip for 15/20A watertight plugs & connectors	0.56-0.63" (14.3-15.9mm)	□ WTM156	•	•




14W47



1547



60W47



60W47DPLX



14W



15W



WTM143

Dimensional information: D-9

Specification information:

Watertight industrial plugs & connectors: D-36
Watertight industrial receptacles: D-36
Severe duty industrial plugs & connectors: D-37
Corrosion resistant auto grip industrial plugs & connectors: D-37

Color information:

BK (Black), Y (Yellow)



Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

RoHS compliant - Page Q-30