

**Paint-Free,
Three Phase,
Totally Enclosed,
C-Face**

1/2 thru 10 Hp

NEMA 56C thru 215TC

Applications: Food processing, packaging and outdoor applications.

Features: Sealed ball bearings with moisture-resistant grease. Rotating non-contact labyrinth seal on output shaft extension and contact lip seals on fan shaft extension. Moisture resistant insulation system. Neoprene gaskets. Special processed cast endplates. 300 series stainless steel motor frame, base, shaft and hardware. No exterior paint. Super-E® motors have NEMA Premium® efficiency and 3 year warranty.



Hp	RPM	NEMA Frame	Catalog Number	List Price	Mult. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	EISA Status ^(a)	Notes ^(a)
Foot Mounted												
1	1800	56C	CESWDM3546	1,014	WD	12.06	40	85.5	208-230/460	1.4	C	1, 60
1 1/2	1800	145TC	CESWDM3554T	1,062	WD	13.00	47	86.5	230/460	2	C	1, 30, 60
2	3600	145TC	CESWDM3555T	1,258	WD	13.28	49	85.5	208-230/460	2.5	A	
	1800	145TC	CESWDM3558T	1,304	WD	14.18	55	86.5	230/460	2.7	A	1
3	3600	145TC	CESWDM3559T	1,548	WD	15.54	57	86.5	208-230/460	3.6	A	
	1800	182TC	CESWDM3611T	1,595	WD	16.56	80	89.5	208-230/460	4	A	1
5	3600	184TC	CESWDM3613T	1,963	WD	18.06	83	88.5	208-230/460	5.7	A	
	1800	184TC	CESWDM3615T	1,856	WD	18.06	100	89.5	208-230/460	6.4	A	1
7 1/2	3600	213TC	CESWDM3709T	2,478	WD	18.68	129	89.5	208-230/460	8.3	A	
	1800	213TC	CESWDM3710T	2,283	WD	19.81	146	91.7	230/460	9.5	A	1
10	3600	215TC	CESWDM3711T	2,747	WD	19.81	154	90.2	208-230/460	10.6	A	
	1800	215TC	CESWDM3714T	2,598	WD	21.31	168	91.7	230/460	12	A	1
Footless												
1	1800	56C	VESWDM3546	965	WD	12.06	39	85.5	208-230/460	1.4	C	1, 60
1 1/2	1800	56C	VESWDM3554	1,051	WD	12.95	47	86.5	230/460	2	C	1, 30, 60
		145TC	VESWDM3554T	1,051	WD	13.00	47	86.5	230/460	2	C	1, 30, 60
2	1800	145TC	VESWDM3558T	1,200	WD	14.19	50	86.5	208-230/460	2.7	B	1

^(a) See notes on inside back flap.

General Information

Premium Efficient Super-E® Motors

Single Phase Motors

General Purpose Industrial Motors

Severe Duty Motors

Washdown Duty Motors

Explosion Proof Motors

Pump Motors

Light Industrial/Commercial Motors

HVAC Motors