



Steel Group Lockout Hasps

- Constructed of vinyl-coated high tensile steel w/ rust resistant plating
- Lock holes: 3/8" diameter

Catalog #	Description	Qty.
133161	1" Diameter Jaws	1
65375	1" Diameter Jaws	12
133162	1-1/2" Diameter Jaws	1
65376	1-1/2" Diameter Jaws	12



Steel Group Lockout Hasps with Tabs

- Tamperproof interlocking tabs prevent unauthorized opening
- Case-hardened steel with rust proof plating and bright red vinyl insulation
- Lock holes: 3/8" diameter

Catalog #	Description	Qty.
105718	1" Diameter Jaws	1
105719	1-1/2" Diameter Jaws	1



Corrosion-Resistant Group Lockout Hasps

- 12 gauge epoxy coated steel provides superior rust resistance and added dielectric strength
- Lock holes: 5/16" diameter

Catalog #	Description	Qty.
T218	1" diameter jaws	1
T220	1-1/2" diameter	1



Aluminum Economy Group Lockout Hasps

- Non-sparking, aluminum small hasps are a great addition to your tool box
- Lightweight at only 1-1/2 ounces
- Lock holes: 3/8" diameter

Catalog #	Description	Qty.
105720	1" Diameter Jaws	1
105721	1-1/2" Diameter Jaws	1



Non-Conductive Group Lockout Hasps

- Strong, rigid plastic resin
- Excellent electrical insulating
- Performs at low temps, excellent heat resistance
- Patent #7,124,606

Catalog #	Description	Qty.
LH220A	Red Lockout Hasp	1



Heavy Duty Lockout Hasp

- Hasp allows multiple workers to lockout at each isolation point
- Stainless steel construction
- Accommodates up to 1/3" dia. padlock shackles

Catalog #	Description	Qty.
871239	Heavy Duty Hasp	24



Dual Jaw Hasp

- Dual construction allows for increased versatility in a single product
- Larger jaw measures 1.25" x 1.75"
- Smaller jaw measures 0.75" dia.

Catalog #	Description	Qty.
236919	Dual Jaw Hasp	1



Non-Conductive Nylon Group Lockout Hasp

- Accommodate up to 6 locks
- Withstands up to 1,000 lbs despite weighing only 1 oz.
- Dimensions: 7"H x 1-3/4"W
- Lock holes: 3/8" diameter

Catalog #	Description	Qty.
99668	Nylon Lockout Hasp	1



Labeled Group Lockout Hasps

- Tough 5052 anodized aluminum alloy hasps include tamperproof locking tabs
- Write-on label accepts pencil, pen or marker. Pen and pencil markings are easily erased for repeated use
- Dimensions: 7-1/4"H x 3"W x 3/16"D
- Lock holes: 5/16" dia.



Legend Option 1

Catalog #	Color	Qty.
65960	Red	5
65961	Silver	5
65962	Blue	5
65963	Green	5
65964	Gold	5
65967	Combo*	5



Legend Option 2

Catalog #	Color	Qty.
65970	Red	5
65971	Silver	5
65972	Blue	5
65973	Green	5
65974	Gold	5
65975	Combo*	5



Legend Option 3

Catalog #	Color	Qty.
39480	Red	5

*Combo includes 1 each of the five colors listed above.