



- Provide economical alternative to wall phone outlet placement
- High impact-resistant thermoplastic plate
- Convenient screw down terminals
- Meets FCC part 68
- UL Listed 1863 – Communication Circuit Accessory and CSA Certified

Molded-In Plates for Voice, 1-Gang



One RJ11 Jack,
6-Position, 4-Conductor,
Screw Terminations



One RJ11 Jack,
6-Position, 6-Conductor,
Screw Terminations



Duplex RJ11 Jacks,
6-Position, 4-Conductor,
Screw Terminations



Duplex RJ11 Jacks,
6-Position, 6-Conductor,
Screw Terminations

Description	One RJ11 Jack, 6-Position, 4-Conductor, Screw Terminations		One RJ11 Jack, 6-Position, 6-Conductor, Screw Terminations		Duplex RJ11 Jacks, 6-Position, 4-Conductor, Screw Terminations		Duplex RJ11 Jacks, 6-Position, 6-Conductor, Screw Terminations
Color	Standard	Mid-Size	Standard		Standard	Mid-Size	Standard
Brown	NS730	NS735	NS732		—	—	—
Ivory	NS730I	NS735I	NS732I		NS742I	NS745I	NS744I
Light Almond	NS730LA	NS735LA	NS732LA		NS742LA	—	—
White	NS730W	NS735W	NS732W		NS742W	NS745W	NS744W

Molded-In Plates for Voice and CATV/Satellite, 1-Gang



One RJ11 Jack,
6-Position, 6-Conductor,
One F-Type Coupler Bulkhead,
Female to Female



One RJ11 Jack,
6-Position, 4-Conductor,
One F-Type Coupler Bulkhead,
Female to Female



One F-Type
Coupler Bulkhead,
Female to Female



Duplex F-Type
Coupler Bulkhead,
Female to Female

Description	One RJ11 Jack, 6-Position, 6-Conductor, One F-Type Coupler Bulkhead, Female to Female		One RJ11 Jack, 6-Position, 4-Conductor, One F-Type Coupler Bulkhead, Female to Female		One F-Type Coupler Bulkhead, Female to Female		Duplex F-Type Coupler Bulkhead, Female to Female
Color	Standard	Mid-Size	Standard		Standard	Mid-Size	Standard
Ivory	NS748I	NS755I	NS747I		NS750I	NS751I	NS752I
Light Almond	NS748LA	NS755LA	NS747LA		NS750LA	NS751LA	NS752LA
White	NS748W	NS755W	NS747W		NS750W	NS751W	NS752W



One Category 5e 110 Punch-Down,
One RJ11 Jack, 6-Position, 4-Conductor,
One F-Type Coupler Bulkhead,
Female to Female

Description	One Category 5e 110 Punch-Down, One RJ11 Jack, 6-Position, 4-Conductor, One F-Type Coupler Bulkhead, Female to Female	
Color	Standard	
Black	NS790BK	
Brown	NS790	
Gray	NS790GY	
Ivory	NS790I	
Light Almond	NS790LA	
White	NS790W	