


ARMTI-2

Solution Water Applications (*cont'd.*)

- 2" NPT Stainless Steel Screw Plug
- INCOLOY® Sheath Elements
- High Watt Density (46 - 51 W/in²)
- 2 - 15 kW
- Integral Thermostat (DPST)
- 240 and 480 Volt, Single Phase
- Moisture Resistant/Explosion Resistant Terminal Enclosure



E2 — Dimensions (Inches)



SCREW PLUG

Specifications and Ordering Information

							T2 — Temperature (60 - 250°F)			T1 — Temperature (0 - 100°F)		
kW	Volts	Phase	W/in ²	No. Elem.	DIM B (In.)	Wt. (Lbs.)	Model	Stock	PCN	Model	Stock	PCN
E2 Moisture Resistant /Explosion Resistant												
2	240	1	51	2	8	12	ARMTI-2205-3E2T2	NS	188007	ARMTI-2205-3E2T1	NS	188015
2	480	1	51	2	8	12	ARMTI-2205-3E2T2	NS	188040	ARMTI-2205-3E2T1	NS	188058
2.5	240	1	51	2	9	13	ARMTI-2255E2T2	NS	188082	ARMTI-2255E2T1	NS	188090
2.5	480	1	51	2	9	13	ARMTI-2255E2T2	NS	188120	ARMTI-2255E2T1	NS	188138
3	240	1	48	2	12	13	ARMTI-2305E2T2	NS	188162	ARMTI-2305E2T1	NS	188170
3	480	1	48	2	12	13	ARMTI-2305E2T2	NS	188200	ARMTI-2305E2T1	NS	188218
4	240	1	47	2	17-1/2	13	ARMTI-2405E2T2	NS	188242	ARMTI-2405E2T1	NS	188250
4	480	1	47	2	17-1/2	13	ARMTI-2405E2T2	NS	188285	ARMTI-2405E2T1	NS	188293
5	240	1	46	2	19-5/8	14	ARMTI-2505E2T2	NS	188322	ARMTI-2505E2T1	NS	188330
5	480	1	46	2	19-5/8	14	ARMTI-2505E2T2	NS	188365	ARMTI-2505E2T1	NS	188373
6	240	1	46	2	25-1/16	14	ARMTI-2605E2T2	NS	188402	ARMTI-2605E2T1	NS	188410
6	480	1	46	2	25-1/16	14	ARMTI-2605E2T2	NS	188445	ARMTI-2605E2T1	NS	188453
7	240	1	49	2	28-1/8	15	ARMTI-2705E2T2	NS	188488	ARMTI-2705E2T1	NS	188496
7	480	1	49	2	28-1/8	15	ARMTI-2705E2T2	NS	188525	ARMTI-2705E2T1	NS	188533
10	240	1	46	2	40-5/8	16	ARMTI-21005E2T2	NS	188568	ARMTI-21005E2T1	NS	188576
10	480	1	46	2	40-5/8	16	ARMTI-21005E2T2	NS	188605	ARMTI-21005E2T1	NS	188613
12	240	1	46	2	47-5/8	17	ARMTI-21205E2T2 ¹	NS	188648	ARMTI-21205E2T1 ¹	NS	188656
12	480	1	46	2	47-5/8	17	ARMTI-21205E2T2	NS	188680	ARMTI-21205E2T1	NS	188699
15	240	1	50	2	54	18	ARMTI-21505E2T2 ¹	NS	188728	ARMTI-21505E2T1 ¹	NS	188736
15	480	1	50	2	54	18	ARMTI-21505E2T2	NS	188760	ARMTI-21505E2T1	NS	188779

Stock Status: S = stock NS = non-stock
To Order—Specify model, volts, phase, kW, PCN and quantity.

1. Not cCSA_{US}® Certified (Exceeds 48 Amps).

FASTShip

Same-day shipping on stock item
orders received before 4 pm CST.
3-day shipping on assembly-stock items.