


ARMTI-2

Solution Water Applications



- 2" NPT Stainless Steel Screw Plug
- INCOLOY® Sheath Elements
- High Watt Density (46 - 51 W/in²)
- 2 - 15 kW
- Integral Thermostat (DPST)
- 240 and 480 Volt, Single Phase
- General Purpose Terminal Enclosure

E1 — Dimensions (Inches)



Specifications and Ordering Information

							T2 — Temperature (60 - 250°F)			T1 — Temperature (0 - 100°F)		
kW	Volts	Phase	W/in ²	No. Elem.	DIM B (In.)	Wt. (Lbs.)	Model	Stock	PCN	Model	Stock	PCN
E1 General Purpose												
2	240	1	51	2	8	6	ARMTI-2205-3T2	NS	187987	ARMTI-2205-3T1	NS	187995
2	480	1	51	2	8	6	ARMTI-2205-3T2	NS	188023	ARMTI-2205-3T1	NS	188031
2.5	240	1	51	2	9	7	ARMTI-2255T2	NS	188066	ARMTI-2255T1	NS	188074
2.5	480	1	51	2	9	7	ARMTI-2255T2	NS	188103	ARMTI-2255T1	NS	188111
3	240	1	48	2	12	7	ARMTI-2305T2	NS	188146	ARMTI-2305T1	NS	188154
3	480	1	48	2	12	7	ARMTI-2305T2	NS	188189	ARMTI-2305T1	NS	188197
4	240	1	47	2	17-1/2	7	ARMTI-2405T2	NS	188226	ARMTI-2405T1	NS	188234
4	480	1	47	2	17-1/2	7	ARMTI-2405T2	NS	188269	ARMTI-2405T1	NS	188277
5	240	1	46	2	19-5/8	8	ARMTI-2505T2	NS	188306	ARMTI-2505T1	NS	188314
5	480	1	46	2	19-5/8	8	ARMTI-2505T2	NS	188349	ARMTI-2505T1	NS	188347
6	240	1	46	2	25-1/16	8	ARMTI-2605T2	NS	188381	ARMTI-2605T1	NS	188390
6	480	1	46	2	25-1/16	8	ARMTI-2605T2	NS	188429	ARMTI-2605T1	NS	188437
7	240	1	49	2	28-1/8	9	ARMTI-2705T2	NS	188461	ARMTI-2705T1	NS	188470
7	480	1	49	2	28-1/8	9	ARMTI-2705T2	NS	188509	ARMTI-2705T1	NS	188517
10	240	1	46	2	40-5/8	10	ARMTI-21005T2	NS	188541	ARMTI-21005T1	NS	188550
10	480	1	46	2	40-5/8	10	ARMTI-21005T2	NS	188584	ARMTI-21005T1	NS	188592
12	240	1	46	2	47-5/8	11	ARMTI-21205T2 ¹	NS	188621	ARMTI-21205T1 ¹	NS	188630
12	480	1	46	2	47-5/8	11	ARMTI-21205T2	NS	188664	ARMTI-21205T1	NS	188672
15	240	1	50	2	54	12	ARMTI-21505T2 ¹	NS	188701	ARMTI-21505T1 ¹	NS	188710
15	480	1	50	2	54	12	ARMTI-21505T2	NS	188744	ARMTI-21505T1	NS	188752

Stock Status: S = stock NS = non-stock
To Order—Specify model, volts, phase, kW, PCN and quantity.

1. Not UL Listed or CSA Certified (Exceeds 48 Amps).

FASTShip™

Same-day shipping on stock item
orders received before 4 pm CST.
3-day shipping on assembly-stock items.