


Specification Sheet

Part Number: 596-97003

- Leaves no exposed adhesive, so it won't adhere to adjacent labels.
- Notched score line for error-free, single-finger folding.
- After installation, information can be read from both sides of the marker, making it easy to identify specific cables.
- Self-locking tail permanently bonds the label to the cable.
- Available in thermal transfer or laser printable formats for expanded printing options.



1" x 4" FlagTag Label, Thermal Transfer, 2400 Labels/Roll

Article Number	596-97003
Type	FTTT
Color	White gloss (GSWH)
Quantity Per	pack

Product Description	The HellermannTyton FlagTag is an innovative flag-style solution for labeling various conductor sizes. Print from any compatible HellermannTyton thermal transfer printer. Applications include high-density cable groups, where it's not possible to move the wires to view critical identifiers. FlagTags also allow for the printing of barcodes, graphics and multiple lines of text without losing direct visibility of the printed data. Whether the application is in data centers, wire harness assemblies or in hard-to-reach areas, FlagTags are an ideal option for organizing and marking wire and cable or even bundles of cables when required.
Short Description	1" x 4" FlagTag Label, Thermal Transfer, 2400 Labels/Roll
Global Part Name	FTTT-PET-WH
Width W (Imperial)	1.0
Width W (Metric)	25.4
Thickness T (Imperial)	.007
Thickness T (Metric)	64.0
Height H (Imperial)	1.75
Height H (Metric)	44.5
Width of Liner (Metric)	101.6
Width of Liner (Imperial)	4.0
Material	Polyester (PET)

Material Shortcut	PET
Adhesive	Acrylic
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	2400
Package Quantity (Metric)	2400
Customs Number	3919905060
Labels per Column	1
Labels per Row	1

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)