

20 Amp, 125, 250 Volts and 277 Volts AC 2 Pole, 3 Wire, Grounding



20A 125V NEMA L5-20R 1 HP	20A 250V NEMA L6-20R 2 HP	20A 277V AC NEMA L7-20R 2 HP
---------------------------------	---------------------------------	------------------------------------

Connector Bodies

Watertight Safety-Shroud®

IP66 SUITABILITY

UL Type 4x, 12

Description	Cord Dia.	Catalog Number
Black Valox® housing, white Valox® clamps.	.360"-.930" (9-24)	HBL2313SW HBL2323SW HBL2333SW

Insulgrip®

IP20 SUITABILITY

Description	Cord Dia.	Catalog Number
Black and white nylon.	.360"-.930" (9-24)	HBL2313 HBL2323 HBL2333
Corrosion resistant, yellow nylon.	.360"-.930" (9-24)	HBL23CM13 HBL23CM23 -
All black nylon.	.360"-.930" (9-24)	HBL2313BK HBL2323BK -
Cord clamps with removable inserts. All black nylon.	.360"-.930" (9-24)	HBL2313EBK HBL2323EBK -

Note: See page B-54 for accessories.

Valise®

IP20 SUITABILITY



Description	Cord Dia.	Catalog Number
Yellow nylon.	.325"-.720" (8.26-18.3)	HBL2313VY HBL2323VY -
Black nylon.	.325"-.720" (8.26-18.3)	HBL2313VBK HBL2323VBK HBL2333VBK

Note: See page B-55 for accessories.

Receptacles

Watertight Safety-Shroud®

IP66 SUITABILITY

UL Type 4x, 12

Description	Catalog Number
Gray Valox® housing and flange, back wired.	HBL2310SW HBL2320SW HBL2330SW

Note: See page B-56 for accessories.

Safety-Shroud® Twist-Lock®

IP20 SUITABILITY

Description	Catalog Number
Gray Valox® angle housing, one gang, back wired.	HBL2310AR HBL2320AR HBL2330AR
Gray Valox® surface mounting, one gang, back wired.	HBL2310SR HBL2320SR HBL2330SR
Gray Valox® semi-flush, two gang, back wired.	HBL2310SR2 HBL2320SR2 HBL2330SR2

Single Flush Receptacles

IP20 SUITABILITY

Description	Catalog Number
Black nylon face, back and side wired.	HBL2310 HBL2320 HBL2330
Black nylon face, spring terminals.	HBL2310ST HBL2320ST -
Blue nylon face, back and side wired.	HBL2310M7 HBL2320M4 -
Isolated ground, orange nylon face, back and side wired.	IG2310 IG2320 -
Corrosion resistant, yellow nylon face, back and side wired.	HBL23CM10 - -
Ring terminal connection.	HBL2310RT HBL2320RT -

Note: See page B-54 for accessories.

Insulgrip® Flanged Receptacles

Description	Catalog Number
Nylon casing, back wired.	HBL2316 HBL2326 HBL2336

Note: See page B-54 for accessories.


Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.



HBL2323SW




HBL2313



HBL2313VY



HBL2320SW



HBL2310ST



HBL2320SR

Dimensions in Inches (mm)