






MATERIALS:

CASE-----NYLON ZYTEL ST-801
SHROUD-----NYLON ZYTEL ST-801
CORD CLAMP-----NYLON ZYTEL ST-801
PIN HOLDER-----NYLON ZYTEL 101-L
PINS-----BRASS CDA #360
ASSEMBLY SCREWS (5)-----300 SERIES SST.
TERMINAL SCREWS (4)-----300 SERIES SST.

PRODUCT INFORMATION:


1. THIS PRODUCT IS NOT WATERTIGHT.
2. SHIPPED WITH CASE, CORD CLAMP AND SHROUD ASSEMBLY UNASSEMBLED.
3. SHROUD ASSEMBLY IS PRE-ASSEMBLED CONSISTING OF SHROUD, PIN HOLDER, PINS AND (2) ASSEMBLY SCREWS (300 SERIES SST.)
4. CORD GRIP RANGE: 14/4 SJ THRU 10/4 S (.390 DIA. - .775 DIA.)
5. COLOR, RATING AND CONTACT CONFIGURATION IS COMPATIBLE WITH IEC 309-2.
6. APPROVALS: UL LISTED, CSA CERTIFIED.

RATING CONFIGURATION



CAT. No. L430P9

RATING- 30A 3Ø 250VAC
(BLUE SHROUD)



CAT. No. L430P12

RATING- 30A 125/250VAC
(ORANGE SHROUD)

REVISIONS
4-27-89 X-REMOVED:
LAST "X" WAS X-O
JL SANDOR
SUB 1

"IN ACCEPTING OUR DRAWINGS OR BLUEPRINTS FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION OR DESIGNS THEREIN SHOWN, AND THAT YOU WILL MAKE NO USE OF OUR DRAWINGS OR BLUEPRINTS OR OF THE IDEAS, INFORMATION OR DESIGNS THEREIN SHOWN WITHOUT OUR PERMISSION."



**DO NOT SCALE
DRAWING
USE DIMENSIONS ONLY**

TITLE 30A LOW PROFILE P&S RIGHT ANGLE PLUG	
WIRING DEVICE DIVISION HUBBELL INCORPORATED BRIDGEPORT, CT.	
DR. BY JLS	APP. BY
PROJECT NO. 1045	SCALE 1:1
CHK. BY	DATE 4-27-89
DR. NO. M-6788	
SHEET 1 OF 1	