

### TYPE TIES

#### Features

- Quick & Easy
- Strong & Flexible
- Nylon 6/6

#### Benefits

- Can accommodate .75" to 15" bundle diameter
- Tensile strengths from 18 lbs to 250 lbs
- Resists weather & chemicals

K



Mounting Head Cable Ties

| Catalog Number | Length | Width | Bolt Size | Color    | Tensile Strength | Bundle Diameter | Bag Qty |
|----------------|--------|-------|-----------|----------|------------------|-----------------|---------|
| 93310          | 4.5    | .10   | #4        | NATURAL  | 18 LBS.          | .62             | 100     |
| 93410          | 4.5    | .10   | #4        | UV BLACK | 18 LBS.          | .62             | 100     |
| 93320          | 5.9    | .14   | #8        | NATURAL  | 40 LBS.          | 1.25            | 100     |
| 93420          | 5.9    | .14   | #10       | UV BLACK | 40 LBS.          | 1.25            | 100     |
| 93340          | 8      | .19   | #10       | NATURAL  | 50 LBS.          | 2               | 100     |
| 93440          | 8      | .19   | #10       | UV BLACK | 50 LBS.          | 2               | 100     |
| 93350          | 12.6   | .19   | #10       | NATURAL  | 50 LBS.          | 3               | 100     |
| 93450          | 12.6   | .19   | #10       | UV BLACK | 50 LBS.          | 3               | 100     |
| 93380          | 15     | .19   | #10       | NATURAL  | 50 LBS.          | 4               | 100     |
| 93480          | 15     | .19   | #10       | UV BLACK | 50 LBS.          | 4               | 100     |
| 93390          | 15     | .30   | #10       | NATURAL  | 120 LBS.         | 4               | 100     |
| 93490          | 15     | .30   | #10       | UV BLACK | 120 LBS.         | 4               | 100     |

Push Mount Cable Ties

| Catalog Number | Length | Width | Color    | Tensile Strength | Bundle Diameter | Bag Qty |
|----------------|--------|-------|----------|------------------|-----------------|---------|
| 93345          | 7.9    | .19   | NATURAL  | 50 LBS.          | 2               | 100     |
| 93445          | 7.9    | .19   | UV BLACK | 50 LBS.          | 2               | 100     |

Releasable Cable Ties

| Catalog Number | Length | Width | Color    | Tensile Strength | Bundle Diameter | Bag Qty |
|----------------|--------|-------|----------|------------------|-----------------|---------|
| 93620          | 5.9    | .30   | NATURAL  | 50 LBS.          | 1.2             | 100     |
| 93720          | 5.9    | .30   | UV BLACK | 50 LBS.          | 1.2             | 100     |
| 93640          | 7.8    | .30   | NATURAL  | 50 LBS.          | 2               | 100     |
| 93740          | 7.8    | .30   | UV BLACK | 50 LBS.          | 2               | 100     |
| 93650          | 10.5   | .30   | NATURAL  | 50 LBS.          | 3               | 100     |
| 93750          | 10.5   | .30   | UV BLACK | 50 LBS.          | 3               | 100     |