



Specialty Fuses

MARS SERIES **820**

Specialty Fuses (Cont.)

MARS NO.	DESCRIPTION	MARS PACK	CASE QTY.
----------	-------------	-----------	-----------

Low Voltage Supplementary Fast Acting Fuses

82608	BLS/BBS 1a, 250V fuse	10	100
82609	BLS/BBS 2a, 250V fuse	10	100
82610	BLS/BBS 3a, 250V fuse	10	100
82611	BLS/BBS 4a, 600V fuse	10	100
82612	BLS/BBS 5a, 600V fuse	10	100

Medium Voltage Fuses Class J Fast Acting

82158	A4J -6a, 600V fuse	10	100
82160	A4J -15a, 600V fuse	10	100
82161	A4J -20a, 600V fuse	10	100
82163	A4J -30a, 600V fuse	10	100
82169	A3T -40a, 600V fuse	10	100
82170	A6T -25a, 600V fuse	10	100
82179	A6T -30a, 600V fuse	10	100
82181	A6T -35a, 600V fuse	10	100
82182	A6T -60a, 600V fuse	10	100
82964	RFS -40a, 600V fuse	10	100

Fuse Reducer

82975	263M/H632 fuse reducer(1 pair)	1	10
-------	--------------------------------	---	----

Automotive Blade Type Fuse Acting 32V DC

82230	ATC-3a, auto blade fuse(5 pk)	1	5
82232	ATC -4a, auto blade fuse	5	5
82231	ATC -5a, auto blade fuse (5 pk)	1	5
82233	ATC -7.5a, auto blade fuse	1	5
82234	ATC -10a, auto blade fuse	5	5
82235	ATC -15a, auto blade fuse	5	5
82236	ATC -20a, auto blade fuse	5	5
82237	ATC -25a, auto blade fuse	5	5
82238	ATC -30a, auto blade fuse	5	5

ATDR Time Delay Class CC

(Small motors, Contactors, Branch Circuit Protection)

82226	ATDR -6.25a, 600V fuse, class CC	10	10
82228	ATDR-10a, 600V fuse	10	10

ATQR Time Delay Class CC

(Control Transformers, Solenoids, Inductive Loads)

82227	ATQR -15a, 600V fuse	10	10
-------	----------------------	----	----

Class G Fuses 480 Volt, 600 Volt Type AG = Type SC

Time delay (above 5A) current limiting

MARS NO.	DESCRIPTION	MARS PACK	CASE QTY.
82271	1a -600V, AG fuse	4	100
82290	2a -600V, AG fuse	4	100
82272	3a -600V, AG fuse	4	100
82291	4a -600V, AG fuse	4	100
82273	5a -600V, AG fuse	4	100
82274	6a -600V, AG fuse	4	100
82275	8a -600V, AG fuse	4	100
82276	10a -600V, AG fuse	4	100
82278	15a -600V, AG fuse	4	100
82279	20a -600V, AG fuse	4	100
82280	25a -480V, AG fuse	4	100
82281	30a -480V, AG fuse	4	100
82282	35a -480V, AG fuse	2	100
82283	40a -480V, AG fuse	2	100
82285	50a -480V, AG fuse	2	100
82286	60a -480V, AG fuse	2	100



Glass Body Time Delay Fuses, Type GDL

Time delay 1/4" x 1 1/4"

MARS NO.	DESCRIPTION	MARS PACK	CASE QTY.
82502	1a -250V, GDL glass fuse	5	100
82505	1.5a -250V, GDL glass fuse	5	100
82507	2a -250V, GDL glass fuse	5	100
82508	2.5a -250V, GDL glass fuse	5	100
82510	3a -250V, GDL glass fuse	5	100
82512	4a -250V, GDL glass fuse	5	100
82513	5a -250V, GDL glass fuse	5	100
82514	7a -250V, GDL glass fuse	5	100
82517	8a -250V, GDL glass fuse	5	100
82518	10a -125V, GDL glass fuse	5	100
82519	15a -125V, GDL glass fuse	5	100



The largest selection of motors, components and accessories for the HVAC/R Industry