

# Glass & Plug Fuses

MARS SERIES **820**



## Dual Element, Time Delay (Type S) UL 125V

Plug fuses all UL listed; CSA models also listed

Rejection Time delay, tamper resistant

| MARS NO. | DESCRIPTION          | MARS PACK | CASE QTY. |
|----------|----------------------|-----------|-----------|
| 82307    | 1 1/4a, S plug fuse  | 4         | 100       |
| 82308    | 1 6/10a, S plug fuse | 4         | 100       |
| 82311    | 2a, S plug fuse      | 4         | 100       |
| 82313    | 2 1/2a, S plug fuse  | 4         | 100       |
| 82315    | 3a, S plug fuse      | 4         | 100       |
| 82316    | 3 2/10a, S plug fuse | 4         | 100       |
| 82318    | 4a, S plug fuse      | 4         | 100       |
| 82320    | 5a, S plug fuse      | 4         | 100       |
| 82323    | 6 1/4a, S plug fuse  | 4         | 100       |
| 82325    | 8a, S plug fuse      | 4         | 100       |
| 82326    | 9a, S plug fuse      | 4         | 100       |
| 82327    | 10a, S plug fuse     | 4         | 100       |
| 82328    | 12a, S plug fuse     | 4         | 100       |
| 82330    | 15a, S plug fuse     | 4         | 100       |
| 82331    | 20a, S plug fuse     | 4         | 100       |
| 82332    | 25a, S plug fuse     | 4         | 100       |
| 82333    | 30a, S plug fuse     | 4         | 100       |

## Dual Element Time Delay Fuse-Type S Clamshell Packaging For Merchandisers

Rejection Time delay, tamper resistant

| MARS NO. | DESCRIPTION                    | MARS PACK |
|----------|--------------------------------|-----------|
| 82745    | 15 a, S plug fuse 125V, (6 pk) | 1         |
| 82746    | 20 a, S plug fuse 125V, (6 pk) | 1         |
| 82747    | 25 a, S plug fuse 125V, (6 pk) | 1         |
| 82748    | 30 a, S plug fuse 125V, (6 pk) | 1         |

## Dual Element, Time Delay (Type T) UL 125V

| MARS NO. | DESCRIPTION           | MARS PACK | CASE QTY. |
|----------|-----------------------|-----------|-----------|
| 82334    | 1 1/4a, T plug fuse   | 4         | 100       |
| 82337    | 2a, T plug fuse       | 4         | 100       |
| 82344    | 2.5a, T plug fuse     | 4         | 100       |
| 82338    | 3.2a, T plug fuse     | 4         | 100       |
| 82339    | 4a, T plug fuse       | 4         | 100       |
| 82340    | 5a, T plug fuse       | 4         | 100       |
| 82341    | 6 1/4a, T plug fuse   | 4         | 100       |
| 82342    | 8a, T plug fuse       | 4         | 100       |
| 82343    | 10a, T plug fuse      | 4         | 100       |
| 82660    | 15a, T plug fuse GT15 | 4         | 100       |
| 82661    | 20a, T plug fuse GT20 | 4         | 100       |
| 82662    | 30a, T plug fuse GT30 | 4         | 100       |
| 82663    | 25a, T plug fuse GT25 | 4         | 100       |

## Dual Element, Time Delay (Type TL) UL 125V

| MARS NO. | DESCRIPTION       | MARS PACK | CASE QTY. |
|----------|-------------------|-----------|-----------|
| 82346    | 15a, TL plug fuse | 4         | 100       |
| 82347    | 20a, TL plug fuse | 4         | 100       |
| 82348    | 25a, TL plug fuse | 4         | 100       |
| 82349    | 30a, TL plug fuse | 4         | 100       |

FERRAZ SHAWMUT IS NOW MERSEN

**merSEN**

82308



82337



82350



82735



## Dual Element, Time Delay (Type TD) UL 125V

| MARS NO. | DESCRIPTION           | MARS PACK | CASE QTY. |
|----------|-----------------------|-----------|-----------|
| 82350    | 15a, TD plug fuse-CSA | 4         | 100       |
| 82351    | 20a, TD plug fuse-CSA | 4         | 100       |
| 82352    | 25a, TD plug fuse-CSA | 4         | 100       |
| 82353    | 30a, TD plug fuse-CSA | 4         | 100       |

## Dual Element Time Delay Fuse-Type TL Clamshell Packaging For Merchandisers

| MARS NO. | DESCRIPTION                     | MARS PACK |
|----------|---------------------------------|-----------|
| 82735    | 15 a, 125V, TL plug fuse (6 pk) | 1         |
| 82736    | 20 a, 125V, TL plug fuse (6 pk) | 1         |
| 82737    | 25 a, 125V, TL plug fuse (6 pk) | 1         |
| 82738    | 30 a, 125V, TL plug fuse (6 pk) | 1         |