



Plug Fuses

MARS SERIES **820**

S Plug Fuse Adapters, UL 125

MARS NO.	DESCRIPTION	MARS PACK	CASE QTY.
82375	2 1/2a, S plug fuse	4	100
82376	3 2/10a, S plug fuse	4	100
82379	6 1/4a, S plug fuse	4	100
82382	15a, S plug fuse	4	100
82383	20a, S plug fuse	4	100
82384	30a, S plug fuse	4	100

Fast Acting, (Type W) UL 125V

MARS NO.	DESCRIPTION	MARS PACK	CASE QTY.
82360	10a, W plug fuse	4	100
82363	15a, W plug fuse	4	100
82364	20a, W plug fuse	4	100
82365	25a, W plug fuse	4	100
82366	30a, W plug fuse	4	100


Dual Element, Time Delay Fuse - Type W Clamshell Packaging For Merchandisers

MARS NO.	DESCRIPTION	MARS PACK
82755	15a, 125V, W plug fuse (6 pk)	1
82756	20a, 125V, W plug fuse (6 pk)	1
82757	25a, 125V, W plug fuse (6 pk)	1
82758	30a, 125V, W plug fuse (6 pk)	1

"W" Fuse

FERRAZ SHAWMUT IS NOW MERSEN

MERSEN



Fuse Adapters



SERVICE & INSTALLATION



Fuse Blocks

MARS SERIES **820**

Fuse Blocks - Class H & K 250 Volts

Mersen manufactures the highest quality 250 to 600 volt fuse blocks handling current capacities of 30 to 600 amperes. These durable fuse blocks are designed for class H, J, K, R, CC and Midget fuses. All blocks are UL listed and CSA certified.


Mersen fuse blocks feature a unique adder block which can be snapped on to form multi-pole segmented blocks of as many poles as desired. Multiple pole blocks thus formed save valuable space, are permanent, and can be added to in the future.

Fuse block insulators are constructed of either phenolic or molded polycarbonate. Three types of wire connectors are used. Screw type is for copper wire with terminals. Pressure plate type is for bare copper wire where vibration may be a factor. Box type connectors are the most durable and versatile for stranded or solid wire. All fuse clips are one piece high-conductivity tin-plated copper for low resistance connections and cool operation.

MARS NO.	DESCRIPTION	MARS PACK	CASE QTY.
83010	Adder 30 amp - AI box	1	50
83011	1 pole 30 amp - AI box	1	50
83012	1 pole 30 amp - screw	1	50
83013	2 pole 30 amp - screw	1	50
83015	Adder 60 amp - AI box	1	50
83017	2 pole 60 amp - AI box	1	25
83018	3 pole 60 amp - AI box	1	25

FERRAZ SHAWMUT IS NOW MERSEN

MERSEN



The largest selection of motors, components and accessories for the HVAC/R Industry

SI-21