



Panel Interface Connectors

Other Popular Models



Single Outlet Versions | Standard Metal Housing | NEMA/UL 4, 4X, 12 | IP66 Rating

Part Number	Description
DP1-16LS	Single Outlet, Size 16 Housing
DP1-2DB9-16LS	Single Outlet, 2 x 9 Pin D-Sub, Size 16 Housing
DP1-2DB9-DB15-32	Single Outlet, 2 x 9 Pin D-Sub, 15 Pin D-Sub, Size 16 Housing
DP1-2DB9F-RJ45-R-32	Single Outlet, 2 x 9 Pin D-Sub Female Ext/Female Interior, RJ45, 3 AMP Reset, Size 16 Housing
DP1-2DB9-RJ45-32	Single Outlet, 2 x 9 Pin D-Sub, RJ45, Size 16 Housing
DP1-2RJ45-PL16	Single Outlet, 2 x RJ45, Size 16 Plate
DP1-3USB-*R-32	Single Outlet, 3 x USB Form A Cables, 3 AMP Reset, Size 32 Housing
DP1-8M-16LS	Single Outlet, 8 Pin Mini-DIN, Size 16 Housing
DP1-8M-R-24LS	Single Outlet, 8 Pin Mini-DIN, 3 AMP Reset, Size 16 Housing
DP1-DB25-24LS	Single Outlet, 25 Pin D-Sub, Size 24 Housing
DP1-DB9-2RJ45-24LS	Single Outlet, 9 Pin D-Sub, 2 x RJ45, Size 24 Housing
DP1-DB9-DDB15-RJ45-R-32	Single Outlet, 9 Pin D-Sub, Hi-Density 15 Pin D-Sub, RJ45, 3 AMP Reset, Size 24 Housing
DP1-DB9F-16LS	Single Outlet, 9 Pin D-Sub Female Ext/Female Interior, Size 16 Housing
DP1-DB9-R-16LS	Single Outlet, 9 Pin D-Sub, 3 AMP Reset, Size 16 Housing
DP1-DB9-RJ45-5R-32	Single Outlet, 9 Pin D-Sub, RJ45, 5 AMP Reset, Size 32 Housing
DP1-DB9-RJ45-R-32	Single Outlet, 9 Pin D-Sub, RJ45, 5 AMP Reset, Size 32 Housing
DP1-DB9-RJ45-USB-*R-32	Single Outlet, 9 Pin D-Sub, RJ45, USB Form A Cable, 3 AMP Reset, Size 32 Housing
DP1-DB9-TS	Single Outlet, 9 Pin D-Sub, DIN Rail Mounting
DP1-DDB15F-2RJ45-2USB-AFAF-32	Single Outlet, Hi-Density 15 Pin D-Sub Female Ext./Int., 2xRJ45, 2xUSB Form A Female to Female, Size 32 Housing
DP1-DDB15F-RJ45-USB-32	Single Outlet, Hi-Density 15 Pin D-Sub Female Ext./Int., RJ45, 2xUSB Form A, Size 32 Housing
DP1-DDB15F-USB-R-32	Single Outlet, Hi-Density 15 Pin D-Sub Female Ext./Int., 2xUSB Form A, 3 AMP Reset, Size 32 Housing
DP1-DDB15-RJ45-6M2-R-32	Single Outlet, Hi-Density 15 Pin D-Sub, RJ45, 2x6 Pin Mini-DIN, 3 AMP Reset, Size 32 Housing
DP1-DDB15-USB-R-32	Single Outlet, Hi-Density 15 Pin D-Sub, RJ45, 2xUSB Form A, 3 AMP Reset, Size 32 Housing
DP1-EV-48LS	Single Outlet, 9 pin D-Sub, Hi-Density 15 Pin D-Sub, 2x6 Pin Mini-DIN, 25 pin D-Sub, RJ45, Size 48 Housing
DP1-MDB9-16LS	Single Outlet, 15 Pin D-Sub Male Exterior/Female Interior, Size 16 Housing
DP1-MDB9-RJ45-16LS	Single Outlet, 15 Pin D-Sub Male Exterior/Female Interior, RJ45, Size 16 Housing
DP1-R-16LS	Single Outlet, 3 AMP Reset, Size 16 Housing
DP1-RJ11-15R-16	Single Outlet, RJ11, 15 AMP Reset, Size 16 Housing
DP1-RJ45-2USB-*R-32	Single Outlet, RJ45, 2 x USB Form A cables, 3 AMP Reset, Size 16 Housing
DP1-RJ45-PL16	Single Outlet, RJ45, Size 16 Plate
DP1-RJ45S-R-16	Single Outlet, Shielded RJ45, 3 AMP Reset, Size 16 Housing
DP1-RJ45-USB-R-32	Single Outlet, RJ45, 2 x USB Form A, 3 AMP Reset, Size 32 Housing
DP1-USB-*16LS	Single Outlet, USB Form A cable, Size 16 Housing
DP1-USB-AFAF-16LS	Single Outlet, USB Form A Female to Female, Size 16 Housing

* Length in feet. Standard cable lengths are 3,6 & 10 feet. Consult factory for other lengths.