



6 TO 8 POLE PVC MINI-LINK™ PLUG ASSEMBLIES

SPECIFICATIONS

MATERIALS

Body	PVC
Contact Sleeve	Stainless Steel
Contact	Brass, Gold Plated over Nickel
Coupling Nut	Machined Aluminum, Black Anodized
Cable	#16 AWG Type STOW, 65 x #34 stranding 105° C
Cable Diameters	6/C-.53", 7/C-.54", 8/C-.58"

ELECTRICAL

Voltage Rating	600 V
Contact Resistance	≤5mΩ

ENVIRONMENTAL

Protection	IP 67
Operating Temp	-20°C to 105°C

CERTIFICATIONS




Recognized,
File No. E165657




Certified,
File No. E165657

OPTIONS

#16 AWG TPE Cable
Stainless Steel Couplers
Plastic Couplers



STRAIGHT PLUG



90° PLUG

MALE

PLUG ASSEMBLY PART NUMBERS						
Number of Poles	Male Face View	Wiring Color Code	AMP RTG. @ 600V	Cable Length	Straight	90°
6		1-Orange 2-Blue 3-Black 4-White 5-Red 6-Green	8A	3 FT	106BB0030AP	106BD0030AP
			8A	6 FT	106BB0060AP	106BD0060AP
			8A	12 FT	106BB0120AP	106BD0120AP
			8A	20 FT	106BB0200AP	106BD0200AP
7		1-Wht.blk. Tr. 2-Black 3-White 4-Red 5-Orange 6-Blue 7-Green	8A	3 FT	107B0030AP	107D0030AP
			8A	6 FT	107B0060AP	107D0060AP
			8A	12 FT	107B0120AP	107D0120AP
			8A	20 FT	107B0200AP	107D0200AP
8		1-Orange 2-Blue 3-Wht.blk. Tr. 4-Black 5-White 6-Red 7-Green 8-Red-Blk. Tr.	7A	3 FT	108B0030AP	108D0030AP
			7A	6 FT	108B0060AP	108D0060AP
			7A	12 FT	108B0120AP	108D0120AP
			7A	20 FT	108B0200AP	108D0200AP

FEMALE

PLUG ASSEMBLY PART NUMBERS						
Number of Poles	Female Face View	Wiring Color Code	AMP RTG. @ 600V	Cable Length	Straight	90°
6		1-Orange 2-Blue 3-Black 4-White 5-Red 6-Green	8A	3 FT	106BA0030AP	106BC0030AP
			8A	6 FT	106BA0060AP	106BC0060AP
			8A	12 FT	106BA0120AP	106BC0120AP
			8A	20 FT	106BA0200AP	106BC0200AP
7		1-Wht.blk. Tr. 2-Black 3-White 4-Red 5-Orange 6-Blue 7-Green	8A	3 FT	107A0030AP	107C0030AP
			8A	6 FT	107A0060AP	107C0060AP
			8A	12 FT	107A0120AP	107C0120AP
			8A	20 FT	107A0200AP	107C0200AP
8		1-Orange 2-Blue 3-Wht.blk. Tr. 4-Black 5-White 6-Red 7-Green 8-Red-Blk. Tr.	7A	3 FT	108A0030AP	108C0030AP
			7A	6 FT	108A0060AP	108C0060AP
			7A	12 FT	108A0120AP	108C0120AP
			7A	20 FT	108A0200AP	108C0200AP

CORD CONNECTORS

WIRE MESH GRIPS

PICO-LINK

MICRO-LINK

ETHERLINK

MINI-LINK

MULTI-PORT BOXES

BUS SYSTEM PRODUCTS

