


PolyStar™ Series Opaque Cover and Clear Cover Configuration Technical Drawings



PolyStar Series Enclosures - Opaque Cover and Clear Cover Configuration Dimensions

SIZE ID NUMBER	OVERALL H X W X D	INSIDE A X B X C	MOUNTING HOR. E X F	MOUNTING VER. E X F	MOUNTING 45 E X F	J	K	L	M	N	SHIPPING WEIGHT	PANEL NUMBER
PC606 PC606CC	7.41 x 8.68 x 5.84 (188 x 223 x 148)	5.94 x 5.94 x 5.02 (151 x 151 x 127)	3.64 x 8.40 (93 x 213)	8.04 x 3.64 (204 x 93)	6.75 x 6.74 (171 x 171)	4.50 (114)	4.25 (108)	4.25 (108)	8.89 (226)	8.89 (226)	2.50 lbs.	BP66*
PC806** PC806CC**	9.41 x 8.68 x 5.86 (239 x 223 x 149)	7.97 x 5.97 x 5.07 (202 x 152 x 129)	5.64 x 8.04 (143 x 213)	10.04 x 3.64 (255 x 93)	8.76 x 6.75 (223 x 171)	4.56 (116)	6.25 (159)	4.25 (108)	10.89 (277)	8.89 (226)	3.19 lbs.	BP86*
PC1008** PC1008CC**	11.41 x 10.68 x 6.36 (290 x 271 x 161)	9.96 x 7.96 x 5.57 (253 x 202 x 142)	7.64 x 10.04 (194 x 255)	12.04 x 5.64 (306 x 143)	10.76 x 8.75 (273 x 222)	5.05 (128)	8.25 (210)	6.25 (159)	12.89 (327)	10.89 (277)	4.31 lbs.	BP108*
PC1210** PC1210CC**	13.40 x 12.68 x 7.86 (340 x 322 x 200)	11.95 x 9.95 x 7.07 (304 x 253 x 180)	9.64 x 12.04 (245 x 306)	14.04 x 7.64 (357 x 194)	12.76 x 10.75 (324 x 273)	6.56 (167)	10.25 (260)	8.25 (210)	14.89 (378)	12.89 (327)	6.19 lbs.	BP1210*
PC1412** PC1412CC**	15.40 x 14.68 x 7.86 (391 x 373 x 200)	13.95 x 11.95 x 7.07 (354 x 304 x 180)	11.64 x 14.04 (296 x 357)	16.04 x 9.64 (407 x 245)	14.76 x 12.75 (375 x 324)	6.56 (167)	12.25 (311)	10.25 (260)	16.89 (429)	14.89 (378)	7.99 lbs.	BP1412*
PC1614** PC1614CC**	17.65 x 16.68 x 9.98 (448 x 424 x 253)	15.93 x 13.93 x 9.20 (405 x 354 x 234)	13.64 x 16.04 (347 x 407)	18.04 x 11.64 (458 x 296)	16.76 x 14.75 (426 x 375)	8.68 (220)	14.25 (362)	12.25 (311)	18.89 (480)	16.89 (429)	10.00 lbs.	BP1614*
PC1816 PC1816CC	19.41 x 18.68 x 11.90 (493 x 474 x 302)	17.83 x 15.83 x 11.08 (453 x 402 x 281)	15.64 x 18.04 (397 x 458)	20.04 x 13.64 (509 x 347)	18.75 x 16.74 (476 x 425)	10.56 (268)	16.25 (413)	14.25 (362)	20.89 (531)	18.89 (480)	11.25 lbs.	BP1816*

All measures are in inches, items in parentheses are in millimeters.

* Panel sold separately

** Domed covers available upon request, consult factory for details