




1) Sensing surface



Basic features

Approval/Conformity	CE
	UKCA
	WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Cable diameter D	3.00 mm
Cable length L	5 m
Conductor cross-section	0.14 mm ²
Connection type	Cable, 5.00 m, PVC
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	no
Short-circuit protection	no

Electrical data

Load capacitance max. at U _e	1 µF
Min. operating current I _m	0 mA
No-load current I ₀ max., damped	25 mA
No-load current I ₀ max., undamped	15 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	2.2 kOhm + LED
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	50 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	10 ms
Residual current I _r max.	80 µA
Ripple max. (% of U _e)	15 %
Switching frequency	1500 Hz
Utilization category	DC -13
Voltage drop static max.	0.5 V

Inductive Sensors
BES 516-300-S279
Order Code: BES033J

BALLUFF

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP65

Functional safety

MTTF (40 °C)	1620 a
--------------	--------

Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Material


Housing material	Aluminium
Material jacket	PVC
Material sensing surface	PBT

Remarks

Recommendation: After a short circuit check the device for proper function.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams



1) For SCP see electrical data

Mechanical data

Dimension	30 x 20 x 10 mm
Installation	for flush mounting
Size	30x20x10

Range/Distance

Assured operating distance Sa	1.6 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	2 mm
Real switching distance sr	2 mm
Repeat accuracy max. (% of Sr)	10.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %