

Electrical data

Load capacitance max. at Ue	1 µF
No-load current I _o max. at Ue	35 mA
Operating voltage U _b	10...30 VDC
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	200 mA
Rated operating voltage U _e DC	24 V
Ready delay t _v max.	200 ms
Residual current I _r max.	50 µA
Ripple max. (% of U _e)	10 %
Switching frequency	1500 Hz
Turn-off delay t _{off} max.	0.333 ms
Turn-on delay t _{on} max.	0.333 ms
Utilization category	DC -13
Voltage drop U _d max. at I _e	2.5 V

Environmental conditions

Ambient temperature	-10...60 °C
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms, 3x6
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

Interface

Switching output	NPN normally open/normally closed (NO/NC)
------------------	---

Material

Housing material	Zinc, Die casting, Painted
Material sensing surface	Glass
Surface protection	Painted

Mechanical data

Dimension	10 x 70 x 88 mm
Fork opening	50 mm
Mounting part	Screw M4

Optical features

Ambient light max.	5000 Lux
Beam characteristic	Divergent
Light spot size	Ø 1.5 mm Light exit
Light type	LED, red light
Principle of optical operation	Through-beam sensor
Smallest part typ.	0.40 mm
Switching function, optical	dark-on/light-on
Wave length	636 nm

Range/Distance

Hysteresis H max.	0.15 mm
Repeat accuracy lateral max.	40 µm


Remarks

Order accessories separately.
For additional information, refer to user's guide.
Factory default setting for switching output: Normally open.
Reference object (target): Steel plate, 50 x 50, thickness 0.5 mm, lateral approach.
The sensor is functional again after the overload has been eliminated.
Only for applications per NFPA 79 (machines with a supply voltage of maximum 600 V). Use an R/C (CYJV2) cable with suitable properties for attaching the device.

Connector Drawings



Wiring Diagrams



Opto Symbols

