




1) Optical axis, 2) Output function, 3) Stability, 4) Sn



Basic features

Approval/Conformity	CE cULus WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Reference emitter	BLS 18KW-XX-1P-...
Series	18KW
Style	Flat cylinder Optics 90°
Trademark	Global

Display/Operation

Adjuster	Potentiometer 270°
Display	Output function- LED yellow Stability - LED green
Setting	Sensitivity (Sn)

Electrical connection

Cable diameter D	4.00 mm
Cable length L	2 m
Conductor cross-section	0.14 mm ²
Connection	Cable, 2.00 m, PVC
Number of conductors	4
Polarity reversal protected	yes
Short-circuit protection	yes

Electrical data

No-load current I ₀ max. at U _e	30 mA
Operating voltage U _b	10...30 VDC
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	100 mA
Rated operating voltage U _e DC	24 V
Ripple max. (% of U _e)	8 %
Switching frequency	250 Hz
Turn-off delay t _{off} max.	1.67 ms
Turn-on delay t _{on} max.	1.67 ms
Voltage drop U _d max. at I _e	2 V

Environmental conditions

Ambient temperature	-25...55 °C
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms, 3x6
EN 60068-2-6, Vibration	10...55 Hz, amplitude 0.5 mm, 3x30 min
IP rating	IP67

Functional safety

MTTF (40 °C)	855 a
--------------	-------

Interface

Switching output	PNP normally closed (NC) PNP normally open (NO) Pins 4-2
------------------	---

Photoelectric Sensors
BLE 18KW-PA-1PP-C-02
Order Code: BOS00CU



Material

Housing material	PBT
Material jacket	PVC
Material sensing surface	PMMA

Mechanical data

Dimension	Ø 18 x 89 mm
Mounting part	Nut M18x1
	Screw M3
Tightening torque max.	1.5 Nm

Optical features

Ambient light max.	5000 Lux
Light type	Infrared
Principle of optical operation	Through-beam sensor (receiver)
Switching function, optical	Light-on
	dark-on

Range/Distance


Range	0...15 m
Rated operating distance Sn	15 m Adjustable

Remarks

For additional information, refer to user's guide.
Order accessories separately.
The sensor is functional again after the overload has been eliminated.
Actuation object (target): gray card, 200 x 200, lateral approach.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams



Opto Symbols

