




1) Output function/Error, 2) Operating voltage, 3) Sn, 4) Bar display for switching distance, 5) Optical axis receiver, 6) Optical axis emitter, 7) rotatable 270°



Basic features

Approval/Conformity	CE Ecolab cULus WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Series	23K
Style	Square Connection can be rotated

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Display/Operation

Adjuster	Adjusting screw
Display	Output function- LED yellow LED green: Power Error - LED yellow, flashing Switching distance - bar display
Setting	Rated switching distance (Sn)

Photoelectric Sensors
BOS 23K-PA-RH10-S4
Order Code: BOS01FL

BALLUFF

Electrical data

Border range energetic	1200 mm
No-load current I_0 max. at U_e	30 mA
Operating voltage U_b	10...30 VDC
Protection class	II
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ready delay t_v max.	300 ms
Residual current I_r max.	50 μ A
Ripple max. (% of U_e)	10 %
Switching frequency	600 Hz
Turn-off delay t_{off} max.	0.83 ms
Turn-on delay t_{on} max.	0.83 ms
Utilization category	DC -13
Voltage drop U_d max. at I_e	2 V

Environmental conditions

Ambient temperature	-20...60 °C
EN 60068-2-27, Shock	Half-sinus, 30 g_n , 11 ms, 3x6
EN 60068-2-6, Vibration	10...55 Hz, amplitude 0.5 mm, 3x30 min
IP rating	IP6x
IP rating per DIN 40050	IPx9K

Functional safety

MTTF (40 °C)	441 a
--------------	-------

Interface

Switching output	PNP normally closed (NC) PNP normally open (NO) Pins 4-2
------------------	---

Material

Housing material	PC
	ABS
Material sensing surface	PMMA

Mechanical data

Dimension	23 x 51 x 52.4 mm
Mounting part	Screw M4
Tightening torque max.	1.5 Nm

Optical features

Ambient light max.	5000 Lux
Beam characteristic	Focus, typical at 500 mm
LED group per IEC 62471	Exempt Group
Light spot size	15 x 15 mm at focal point
Light type	LED, red light
Principle of optical operation	Diffuse sensor, triangulation
Special optical feature	Background suppression
Switching function, optical	Light-on dark-on
Wave length	640 nm

Range/Distance

Distance deviation 18 % max. (% of S_r)	15 %
Hysteresis H max. (% of S_r)	4.0 %
Range	3...800 mm
Rated operating distance S_n	800 mm Adjustable

Remarks


The sensor is functional again after the overload has been eliminated.
Order accessories separately.
For additional information, refer to user's guide.
Reference object (target): gray card, 200 x 200, 90 % remission, axial approach.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams



Opto Symbols

