


Class H Fuseblocks

250 Volts

H250 Series



Catalog Symbol: H250 Series

Ampere Rating: $\frac{1}{10}$ to 600A

Voltage Rating: 250V

Agency Information:

UL Listed, UL 512, Guide IZLT, File 14853

CSA Certified, C22.2 No. 39, Class 6225-01, File 47235

Withstand Rating: 10,000A RMS Sym.

For use with Class H Fuses (NON and REN)

UL Flammability: 94VO

Materials: Thermoplastic

Class H Fuseblocks (250V) Catalog Data (for NON and REN Fuses)

Amps	Poles	Basic Catalog Number	Terminal Type (Suffix No.)								Dimensions (Inches) – See Next Page For Figures												Wire Range		
			Screw				Box Lug w/				Fig. No.	A	B	C	D	E	F	G	H	J Dia. x C' Bore	K				
			Clip with Reinforced Spring	Pressure Plate	Pressure Plate & Clip with Reinforced Spring	Clip with Reinforced Spring	Clip w/ Reinforced Spring (Copper Only)	Copper Only	0.25" Quick Connect																
1/10 to 30	1	H25030-1	S	SR	P	PR	C	CR	COR	CO	Q	1	(See Figures)												C, CR #2-14 CU, #2-12 AL CO, COR #6-14 CU ONLY P, PR #10-18 CU ONLY Q N/A S, SR #10-18 CU ONLY
	2	H25030-2	S	SR	P	PR	C	CR	COR	CO	Q	2													
	3	H25030-3	S	SR	P	PR	C	CR	COR	CO	Q	3													
31 to 60	1	H25060-1	—	—	—	—	C	CR	COR	CO	—	4	4.25	1.73	1.5	1.5	0.5	0.5	1.25	—	0.22 × 0.41	0.27	C, CR #2-14 CU, #2-8 AL CO, COR #2-14 CU ONLY		
	2	H25060-2	—	—	—	—	C	CR	COR	CO	—	5			2.81					1.94					
	3	H25060-3	—	—	—	—	C	CR	COR	CO	—	6			4.125					1.31					
61 to 100	1	H25100-1	—	SR	—	—	—	CR	COR	—	—	7	(See Figures)												COR #1/0-8 CU ONLY
	2	H25100-2	—	SR	—	—	—	CR	COR	—	—	8													CR #1/0-8 CU/AL
	3	H25100-3	—	SR	—	—	—	CR	COR	—	—	9													SR #8W/ Ring Terminal
101 to 200	1	H25200-1	—	—	—	—	—	CR	—	—	—	10	7.125	3.09	3.0	2.06	0.5	2.0	3.0	0.75	—	0.31	CR 250kcmil-6 CU/AL		
	3	H25200-3	—	—	—	—	—	CR	—	—	—	11	(See Figures)												
201 to 400	1	H25400-1	—	—	—	—	—	CR*	—	—	—	10	9.06	4.0	3.0	3.02	0.63	1.75	3.0	1.0	—	0.31	CR 500kcmil-4 CU/AL		
	3	H25400-3	—	—	—	—	—	CR†	—	—	—	12	9.06	4.0	4.0	2.50	0.82	9.25	10.88	1.0					
401 to 600	1	H25600-1	—	—	—	—	—	CR	—	—	—	10	11.0	4.97	3.0	4.0	1.125	1.75	4.0	1.00	—	0.31	CR (2) 500kcmil-4/0 CU/AL		
	3	H25600-3	—	—	—	—	—	CR†	—	—	—	12	11.0	4.97	5.0	3.0	1.87	11.0	14.74	1.00					

*U.L. Recognized, CSA Certification.

†No UL, No CSA Certification.

CE CE logo denotes compliance with European Union Low Voltage Directive (50-1000Vac, 75-1500Vdc). Refer to Data Sheet: 8002 or contact Bussmann Application Engineering at 314-527-1270 for more information.


Class H Fuseblocks

250 Volts


H250 Series

Dimensional Data


250V, 1/10A to 30A



250V, 31A to 60A




250V, 61A to 100A



250V, 101A to 600A

250V, 101A to 200A

250V, 201A to 600A



The only controlled copy of this Data Sheet is the electronic read-only version located on the Bussmann Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.