

Proximity Sensors Inductive High Temperature Types IA, M12, NAMUR



- Nickel-plated brass housing
- Sensing distance: 2 mm
- Power supply: 8 VDC
- Output: NAMUR
- For flush mounting
- 2 m silicone cable

Product Description

Inductive proximity sensor with NAMUR output in M12 housing for flush mounting. Connection with 2 m silicone cable.

Ordering Key

IA 12 ASF 02 UHT-K

- Type
- Housing style
- Housing size
- Housing material
- Housing length
- Detection principle
- Sensing distance
- Output type
- High temperature

Type Selection

Rated operating dist. (S _n)	Connection type	Housing dimensions	Ordering no. Namur output
2.0 mm	Cable, 2 m	M12	IA 12 ASF 02 UHT-K


For flush mounting in metal

Specifications


Rated operational volt. (U _B)	8 VDC	Ambient temperature	
Ripple	≤ 10%	Operating	-25° to +120°C (-13° to +248°F)
Rated operational current (I _e)		Storage	-30° to +125°C (-22° to +257°F)
Continuous	Activated: < 1.1 mA Not activated: > 2.2 mA	Degree of protection	IP 67 (Nema 1, 3, 4, 6, 13)
Frequency of op. cycles (f)	2 kHz	Housing material	Nickel-plated brass
Effective operating dist. (S _r)	0.9 x S _n ≤ S _r ≤ 1.1 x S _n	CE-marking	Yes
Usable operating dist. (S _u)	0.85 x S _r ≤ S _u ≤ 1.15 x S _r	Connection	Cable, silicone, 2 m, AWG 26



Dimensions



Wiring Diagram



Installation Hints

<i>To avoid interference from inductive voltage/current peaks, separate the prox. switch power cables from any other power cables, e.g. motor, contactor or solenoid cables</i>	<i>Relief of cable strain</i> Incorrect Correct The cable should not be pulled	<i>Protection of the sensing face</i> A proximity switch should not serve as mechanical stop	<i>Switch mounted on mobile carrier</i> Any repetitive flexing of the cable should be avoided
--	--	--	---