



Sub-bases for logic elements



Also available in **ATEX** version for use in potentially explosive atmospheres in accordance with 94/9/EC Directive



	81 532 104	81 532 102	
Two-hand start module	● 1	● 1	
Manostats - vacuostats	● 1	● 1	
Leak sensor and amplifier relays	● 1	● 1	
Logic elements AND Timers	● 1	● 1	
Regulator accessories	● 1	● 1	
Memory element	—	—	
Operating temperature °C	-5 → +50	-5 → +50	
Electro-pneumatic miniature solenoid	● 1	● 1	


NB: The number indicates the number of components mounted on the sub-base

Characteristics

Push-in connection for semi-rigid tubing Ø 4 mm (NFE 49100)	rotatable	rotatable	
Fixation	DIN rail 35 mm	DIN rail 35 mm	
Weight g	56	52	

Connections elements and relays


Front connecting




- A - Single sub-base or end base
- B - Associable sub-base
- 1 - Input port (green port 1)
- 2 - Output port (red port 3)
- 3 - Input/supply port (yellow port 2) Ø 4
- 4 - Input port integral to sub-base
- 5 - Input indicator (green)
- 6 - Output indicator (red)
- 7 - 1/4 turn screws
- 8 - Marking tag
- 9 - Arrow indicating flow direction
- 10 - Mounting tongue
- 11 - Mounting groove
- 12 - Selector


Dimensions

81 532 104 3 x 81532102






81 542 002



81 532 001



81 531 001

Two-hand start module	
Manostats - vacuostats	
Leak sensor and amplifier relays	
Logic elements AND Timers	
Regulator accessories	
Memory element	● 1
Operating temperature °C	-5 → +50
Electro-pneumatic miniature solenoid	—

—
—
—
—
—
—
—
—
—

● 1
● 1
● 1
● 1
● 1
—
-5 → +50
● 1

● 2
● 2
● 2
● 2
● 2
● 1
-5 → +50
● 2

Caractéristiques

Push-in connection for semi-rigid tubing
 Ø 4 mm (NFE 49100)
 Fixation

rotatable

DIN rail 35 mm

rear

2 M4 screws

rear

Clips for rails
 Ø 8 mm

Weight


g

95


10

35

Memory element sub-base, front and rear connecting



Rear connection



The modular system elements are fixed with two screws on the sub-base.

A locating device on each logic element prevents incorrect assembly.

The logic element is connected via the sub-base. This sub-base has 3 instant connections for connecting semi-rigid tubes with outer Ø 4.

- 1 - Input signal
- 2 - Signal port for passive logic elements, air supply for active logic elements.
- 3 - Output signal

81 542 002 (for memory 81523201/601)

81 531 001

81 532 001

