

Eaton 5778C

Catalog Number: 5778C

Eaton Arrow Hart straight blade flanged inlet , #14 AWG, 20A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-20P, Two-pole, three-wire, grounding, Clamp, Nylon, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart straight blade flanged inlet	5778C
	UPC
	040893014166
Product Length/Depth	Product Height
3.783 in	2.439 in
Product Width	Product Weight
2.512 in	0.17 lb
Certifications	
cULus Listed	
Federal Specification Classification 6221 02	

defaultTaxonomyAttributeLabel

Device type

Flanged inlet

Type

Flanged inlet

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Two-pole

Style type

Flanged

Material

Nylon

Packaging type

Core pack

Color

Black

White

Connection type

Clamp

Allowable wire size

#14 AWG

NEMA configuration

5-20P

Resources

Catalogs

[Arrow Hart Buyers Guide B-11](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5778C](#)

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia